

MODEL 8

Current Transformer

Window Diameter 3.25"

Application

Metering.

Frequency

50-400 Hz.

Insulation Level

600 Volt, 10 kV BIL full wave.

Terminal are brass studs No. 8-32 with one flatwasher, lockwasher and regular nut.



Model 7ASHT

REGULATORY AGENCY APPROVALS



E93779



LR89403

Manufactured to meet the requirements of ANSI/IEEE C57.13.
Classified by U.L. in accordance with IEC 44-1

Flexible leads are UL 1015, 105°C, CSA approved, #16 AWG, 24" long. Nonstandard, lead length can be specified.

Model 8SHT also available as 8SHL with leads.

Order mounting bracket kit 0221B00183 separately for model 8SHT.

Order bus bar mounting kit 0221A26074 separately, factory installed.

Approximate weight 2.5 lbs.



GE VERNOVA




Data Table: Model 8

CATALOG NUMBER	CURRENT RATIO	V.A. ±1% CLASS	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75°C)	CONTINUOUS THERMAL RATING FACTOR	
			B0.1	B0.2	B0.5	B0.9	B1.8		@ 30°C	@ 55°C
8**—201	200:5	5.0	1.2	1.2	2.4	4.8	4.8	0.030	2.0	2.0
8**—251	250:5*	7.5	0.6	0.6	1.2	2.4	4.8	0.044	2.0	2.0
8**—301	300:5*	15.0	0.6	0.6	1.2	2.4	2.4	0.049	2.0	2.0
8**—401	400:5*	25.0	0.3	0.3	0.6	1.2	2.4	0.079	2.0	1.5
8**—501	500:5*	35.0	0.3	0.3	0.6	0.6	1.2	0.102	2.0	1.5
8**—601	600:5*	50.0	0.3	0.3	0.6	0.6	1.2	0.147	1.5	1.33
8**—751	750:5*	50.0	0.3	0.3	0.6	0.6	1.2	0.184	1.5	1.0
8**—801	800:5*	60.0	0.3	0.3	0.3	0.6	0.6	0.197	1.5	1.0
8**—102	1,000:5*	75.0	0.3	0.3	0.3	0.6	0.6	0.246	1.33	1.0
8**—122	1,200:5*	75.0	0.3	0.3	0.3	0.3	0.6	0.169	1.5	1.0
8**—152	1,500:5*	90.0	0.3	0.3	0.3	0.3	0.6	0.316	1.33	1.0
8**—162	1,600:5*	100.0	0.3	0.3	0.3	0.3	0.6	0.337	1.33	0.8
8**—202	2,000:5*	120.0	0.3	0.3	0.3	0.3	—	0.422	1.0	0.8
8**—252	2,500:5*	50.0	0.3	0.3	0.3	0.3	—	0.438	1.0	0.8
8**—302	3,000:5	60.0	0.3	0.3	0.3	0.3	—	0.526	1.0	0.8
8**—322	3,200:5	70.0	0.3	0.3	0.3	0.3	—	0.561	1.0	0.8
8**—402	4,000:5	80.0	0.3	0.3	0.3	0.3	—	0.973	0.8	0.8


**Note: When ordering, prefix Cat No. with model designation required i.e. 8SHT-201, 8RL-301, etc.

*Approved for revenue metering by Industry Canada No. T-188


Model 8



Model 8SHT



Model 8RL



For more information, visit
[gevernova.com/grid-solutions](https://www.gevernova.com/grid-solutions)

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50294
English
251010