

MODEL 389MR

Current Transformer Multi-Ratio

Window Diameter 5.75"



Application

Relaying.

Frequency

50-400 Hz.

Insulation Level


600 Volt, 10 kV BIL full wave.

Terminals are brass screws No. 10-32 with one flatwasher and lockwasher.


Approximate weight 70 lbs.

Model 389MR




CATALOG NUMBER	RELAY CLASS	CONTINUOUS THERMAL RATING FACTOR	
		@ 30°C	@ 55°C
389-601MR	C200	2.0	2.0
389-122MR	C400	2.0	1.5
389-202MR	C400	1.5	1.33



Model 389-601MR



Model 389MR



For more information, visit
gevernova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.

