

MODELS 567TL, 567TS

Current Transformers

Window Size 4.75" x 3.75"



REGULATORY AGENCY APPROVALS
 E93779 LR89403
 Manufactured to meet the requirements of ANSI/IEEE C57.13.
 Classified by U.L. in accordance with IEC 44-1

Application

Metering

Frequency

50-400 Hz

Insulation Level

600 Volts, 10 kV BIL full wave

Continuous Thermal Current Rating Factor

1.33 at 30°C. amb., 1.0 at 55°C. amb.

TL-Terminals are brass studs No. 10-32 with one flatwasher, lockwasher and regular nut.

TS-Terminals are brass screws No. 10-32 with one flatwasher, lockwasher and regular nut.

Approximate weight 4 lbs.

Model 567TL, 567TS

CATALOG NUMBER	CURRENT RATIO	ANSI METERING CLASS AT 60 Hz				
		B0.1	B0.2	B0.5	B0.9	B1.8
567**201	200:5	2.4	2.4	—	—	—
567**251	250:5	1.2	2.4	—	—	—
567**301	300:5	1.2	1.2	2.4	—	—
567**401	400:5	0.6	1.2	2.4	2.4	—
567**501	500:5	0.6	0.6	1.2	2.4	—
567**601	600:5	0.6	0.6	1.2	1.2	2.4
567**751	750:5	0.3	0.6	0.6	1.2	2.4
567**801	800:5	0.3	0.6	0.6	1.2	1.2
567**102	1,000:5	0.3	0.3	0.6	0.6	1.2
567**122	1,200:5	0.3	0.3	0.3	0.6	0.6
567**152	1,500:5	0.3	0.3	0.3	0.3	0.6
567**162	1,600:5	0.3	0.3	0.3	0.6	0.6
567**202	2,000:5	0.3	0.3	0.3	0.3	0.6
567**252	2,500:5	0.3	0.3	0.3	0.3	0.3
567**302	3,000:5	0.3	0.3	0.3	0.3	0.3
567**322	3,200:5	0.3	0.3	0.3	0.3	0.3

**Note: When ordering, prefix Cat No. with model designation required i.e. 567TL-201, or 567TS-201, etc.




GE VERNOVA




Models 567TL, 567TS

TL Style



TS Style



For more information, visit
governova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50338
English
250917