

MODEL 574

Current Transformer

Window Size 0.75" x 2.25"



REGULATORY AGENCY APPROVALS
UL E93779 **SP** LR89403
Manufactured to meet the requirements of ANSI/IEEE C57.13.
Classified by U.L. in accordance with IEC 44-1

Application

Metering.

Frequency

50-400 Hz.

Insulation Level

600 Volts, 10 kV BIL full wave.

Continuous Thermal Current Rating Factor

1.33 at 30°C. amb., 1.0 at 55°C. amb.



Terminals are brass studs No. 10-32 with one flatwasher, lockwasher and regular nut.

Approximate weight 2.5 lbs.

Model 574

CATALOG NUMBER	CURRENT RATIO	ANSI METERING CLASS AT 60 Hz		SECONDARY WINDING RESISTANCE (Ω @ 75°C)
		B0.1	B0.2	
574-101	100:5	2.4	2.4	0.032
574-151	150:5	1.2	2.4	0.055
574-201	200:5	1.2	1.2	0.067
574-251	250:5	0.6	1.2	0.094
574-301	300:5	0.6	0.6	0.101
574-401	400:5	0.6	0.6	0.212
574-501	500:5	0.6	0.6	0.265
574-601	600:5	0.6	0.6	0.319
574-801	800:5	0.3	0.3	0.425

Model 574



For more information, visit
governova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50757
 English
 251009