

MODELS 595 & 596

Zero Sequence Current Transformers

Window Sizes
4.56"x 13.44", 4.56"x 17.63"



Cast Resin Construction

Application

Zero-Sequence

Frequency

50-400 Hz.

Insulation Level

600 Volts, 10 kV BIL full wave.

Continuous Thermal Current Rating Factor

2.0 at 30 °C. amb.,

2.0 at 55 °C. amb.

Terminals are brass screws No. 8-32 with lockwashers.




4 holes mounting system also available with brackets. Consult factory for details.

Approximate weight 24-29 lbs.

Models 595 & 596

CATALOG NUMBER	CURRENT RATIO	SECONDARY WINDING RESISTANCE (Ω @ 75°C)
595—102—1	1,000:1	7.52
596—102—1	1,000:1	7.52

Model 595 & 596 Cast Resin Construction



Models 595 & 596

MODEL	"A"	"B"	"C"	"D"
595	13.44	16.50	17.50	2.00
596	17.63	20.63	21.63	2.13

For more information, visit
governova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50271
 English
 251009