

MODEL 125

Current Transformer

Window Diameter 6.31"



Shown with Bus Bar Mounting Kit

REGULATORY AGENCY APPROVALS



Manufactured to meet the requirements of ANSI/IEEE C57.13.
Classified by U.L. in accordance with IEC 44-1

Application

Metering.

Frequency

50-400 Hz.

Insulation Level

600 Volt, 10 kV BIL full wave.

Terminal are brass studs No. 8-32 with one flatwasher, lockwasher and regular nut.

Order mounting bracket kit 0221B00231 separately.




Order bus bar mounting kit 0221A26076 separately, factory installed.

Approximate weight 3 lbs.

Model 125

CATALOG NUMBER	CURRENT RATIO	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75°C)	CONTINUOUS THERMAL RATING FACTOR	
		B0.1	B0.2	B0.5	B0.9	B1.8		@ 30°C	@ 55°C
125-601	600:5	0.3	0.3	1.2	1.2	2.4	0.071	1.5	1.33
125-751	750:5	0.3	0.3	0.6	1.2	2.4	0.143	1.5	1.33
125-801	800:5	0.3	0.3	0.6	1.2	2.4	0.116	1.5	1.33
125-102	1,000:5	0.3	0.3	0.3	0.6	1.2	0.187	1.5	1.33
125-122	1,200:5	0.3	0.3	0.3	0.6	1.2	0.224	1.5	1.33
125-152	1,500:5	0.3	0.3	0.3	0.3	0.6	0.285	1.5	1.33
125-162	1,600:5	0.3	0.3	0.3	0.3	0.6	0.304	1.5	1.33
125-202	2,000:5	0.3	0.3	0.3	0.3	0.6	0.280	1.5	1.0
125-252	2,500:5	0.3	0.3	0.3	0.3	0.6	0.351	1.33	1.0
125-302	3,000:5	0.3	0.3	0.3	0.3	0.6	0.421	1.33	1.0
125-352	3,500:5	0.3	0.3	0.3	0.3	0.3	0.491	1.33	1.0
125-402	4,000:5	0.3	0.3	0.3	0.3	0.3	0.696	1.0	0.8

Model 125



Bus Bar Kit Shown

For more information, visit
gevernova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50317
 English
 251013