

MODEL 3P528

Current Transformer

Window Size 2.33" x 5.20"



REGULATORY AGENCY APPROVALS



Manufactured to meet the requirements of ANSI/IEEE C57.13.
Classified by U.L. in accordance with IEC 44-1

Application

3 phase metering.

Frequency

50-400 Hz.

Insulation Level

600 Volts, 10 kV BIL full wave.

Data Table: Model 3P528



CATALOG NUMBER	CURRENT RATIO	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ohms @ 75°C)
		B0.1	B0.2	B0.5	B0.9	B1.8	
3P528-101	100:5	4.8	-	-	-	-	0.020
3P528-201	200:5	1.2	2.4	4.8	-	-	0.035
3P528-251	250:5	1.2	2.4	4.8	-	-	0.043
3P528-301	300:5	0.6	1.2	2.4	4.8	-	0.062
3P528-401	400:5	0.3	0.6	1.2	2.4	-	0.079
3P528-501	500:5	0.3	0.3	1.2	2.4	-	0.104
3P528-601	600:5	0.3	0.3	0.6	1.2	2.4	0.125
3P528-751	750:5	0.3	0.3	0.6	0.6	1.2	0.163
3P528-801	800:5	0.3	0.6	0.6	0.6	1.2	0.209
3P528-102	1000:5	0.3	0.3	0.6	0.6	1.2	0.261
3P528-122	1200:5	0.3	0.3	0.3	0.6	0.6	0.313



GE VERNONA



Model 3P528



For more information, visit
gevernova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.