

**DATA SHEET**


# FLEXINVERTER 1.5kV Solar Power Station

The **FLEXINVERTER** Solar Power Station combines the technology of GE Vernova’s 1500 Vdc solar **FLEXINVERTER**, with a medium voltage power transformer, optional medium voltage switchgear and multiple selectable options for a reliable, plug & play, factory integrated power conversion solution for utility-scale solar installations.

The **FLEXINVERTER** is one of the industry’s leading 1500 Vdc inverter developments and is GE Vernova’s latest evolution in renewable power electronics. GE Vernova has a renewable energy inverter installed base of more than 30 GW globally.

**FLEXINVERTER Solar Power Station:**

- UL and IEC compliant configurations
- 3.7 – 4.7 MVA output power
- High efficiency power conversion
- Air-cooled system
- Plug & Play
- Direct outdoor installation
- Standard 20ft ISO high cube container for optimized logistics and installation
- Fiber-optic SCADA interface
- DC-coupling option




SPECIFICATIONS	UNITS	1560	1563	1566	1569
<b>INPUT DATA</b>					
MPPT Range <sup>1</sup>	Vdc	853 - 1150	895 - 1200	938 - 1300	980 - 1300
Max Permissible DC Voltage	Vdc	Standard 1500, Option 1550			
Max DC Current (up to 35°C / at 50°C)	Adc	5000 / 4500			
Number of MPPT		1			
Number of DC Inputs & cables		24 standard, up to 36 input pairs; 2 x 600 kcmil / 300 mm <sup>2</sup> or 1 x 750 kcmil / 400 mm <sup>2</sup> per DC input			
Max DC Fuse Rating per DC Input	A	up to 500, multiple fuse ratings available			
DC-coupling with battery energy storage systems		Option – compatible with or without PV optimizers including separate BESS input			
<b>OUTPUT DATA - MEDIUM VOLTAGE</b>					
Transformer HV / LV Connection		Δ (Delta) / Y (Wye)			
Medium Voltage Short Circuit Rating	kA	IEC MVSG - Standard 20kA 1s, (Option 20kA 3s, 25kA 1s) / UL Padmount Transformer - Standard 25kA, (Option 40kA)			
Rated Output Power (at 55°C & 0.92 PF)	MVA	3.36	3.52	3.69	3.86
Multi-tap Transformer Configuration (UL / NAM only)		Range covered by a single MV transformer for project flexibility			
AC Output Power (up to 35°C / at 50°C) <sup>2</sup>	MW	4.11 / 3.70	4.31 / 3.89	4.52 / 4.07	4.73 / 4.26
AC Output Voltage (+10% / -10%) <sup>3</sup>	kVac	22 / 33 / 34.5			
Max AC Current (up to 35°C)	Aac	108 / 72 / 69	113 / 75 / 72	119 / 79 / 76	124 / 83 / 79
Max AC Current (at 50°C)	Aac	97 / 65 / 62	102 / 68 / 65	107 / 71 / 68	112 / 74 / 71
Grid Frequency ±5%	Hz	50 / 60			
Power Factor (PF) Range <sup>3</sup>		0-1 leading & lagging			
Current Harmonic Distortion (TDD)	%	<3			
Medium Voltage Cable		Up to 1x 630 mm <sup>2</sup> (IEC) 630Aac / 1x 1500 kcmil (UL) 600 Aac, 900 Aac optional Separable connectors possible			
<b>EFFICIENCY &amp; AUXILIARY POWER</b>					
Power Station Efficiency at 40°C (Max / EU / CEC) <sup>4</sup>	%	98.4 / 97.6 / 97.9			
Inverter Efficiency at 40°C (Max / EU / CEC) <sup>5</sup>	%	99.1 / 98.7 / 98.7			
Power Station Nighttime Aux Power <sup>6</sup>	W	≤700, Excludes MV Transformer No-Load Losses			
<b>INTERFACES</b>					
Plant Control Interface / PLC		Modbus TCP, EGD			
Programming / Diagnostic Interface		Modbus TCP			
Extra Analog and Digital I/O		Option			
Power Station Connections		Internal: CAT7 <30m / External: Fiber Optic			
<b>FEATURES AND OPTIONS</b>					
Cooling		Air Cooled			
Local Shut Down Button		Included			
Mounting Options		Piers / Pad / Piles			
Array Configurations Supported		Negative Pole Grounded or Floating			
Ground Fault Monitoring		Standard for Grounded Arrays, Option for Floating Arrays			
Night-time VAR Function		Option			
Insulation Monitoring		Option			
Container Color Code		RAL 6026 (Dark Teal)			


SPECIFICATIONS	UNITS	1560	1563	1566	1569
<b>FEATURES AND OPTIONS</b>					
Disconnect Low Voltage AC Side				Motorized AC Circuit Breaker	
Disconnect DC Side				Motorized No-Load DC Switch	
Overvoltage Protection, DC and AC				Included – IEC 61643-1 Class II / UL 1449	
Main Power Transformer Oil Type				Mineral - ONAN (Standard) / Biodegradable - KNAN (Option)	
Oil Spill Management				Option 1: Collection & drainage   Option 2: Full oil containment up to 120% oil-volume	
Customer Aux Power Loads <sup>7</sup>	kVA			Standard 6, Option 40	
Revenue Grade Metering				Option	
GPS Enabled Fault Timestamping				Option (compliant to MISO App G and CAISO App H)	
Altitude <sup>3</sup>	m / ft			No derating ≤ 1000 / 3281, up to 4000 / 13124	
Noise at 1m <sup>8</sup>	dBA			Standard ≤79, Acoustic Hood Option ≤71	
Weight	kg / lbs			approximately 17000 / 37480	
Dimensions (L x W x H)	m / ft			6.1 x 2.4 x 2.9 / 20.0 x 8.0 x 9.5	
<b>PROTECTION RATING AND AMBIENT CONDITIONS</b>					
Operating Temperature Range	°C / °F			Standard -10 to +55 / +14 to +131 Option -25 to +55 / -13 to +131	
Cold Weather Option <sup>9</sup>	°C / °F			Down to -35 / -31	
Storage Temperature Range	°C / °F			-40 to +65 / -40 to +149	
Humidity	%			5-100 (rated for outdoor installation)	
Maximum Altitude without Derating <sup>10</sup>	m / ft			1000 / 3281	
Seismic				IBC 2018 / ASCE 7-10 Ss=2g for 0.2 Sec	
Maximum Wind Speed <sup>11</sup>	kph / mph			254 / 158	
Snow Load				ASCE 7	
NEMA Rating / IP Class				NEMA 3 / IP54 (Inverter & RMU), IP11 (IEC) IP00 UL (Transformer Area)	
<b>STANDARDS &amp; CERTIFICATIONS</b>					
Electromagnetic Compatibility (EMC)				EN 61000-6-2, 62920 / CISPR 11	
Certifications				IEC, CE, UL 1741 SA, CSA	

- At nominal grid voltage and PF=1, please refer to PQ curves for detailed MPPT voltage & temperature profiles
- AC Power is valid for grid voltage ≥ nominal voltage. Self-consumption (max ~16 kVA) and customer auxiliary loads not included
- Derating will apply according to PQ curves
- Preliminary measurements at 40°C for 660Vac, includes auxiliary power losses, EU Reg. No. 584/2014 available as option. 99.1% rated efficiency option available for IEEE transformer
- Preliminary measurements at 40°C for 660Vac, includes self-consumption for CEC & Max efficiencies and excludes self-consumption for EU efficiency
- No heating, no cooling, without environmental controls enabled, DC link de-energized and without transformer no load losses, no customer loads, for inverter only auxiliary needs
- Customer Aux Power demand reduces total AC output power, customer to specify circuit breaker configurations
- At 1m in front of enclosure and 1.5m up from the ground. Please respect the restricted areas described in the manual
- Cold weather option on request
- Higher altitudes (with derating) on request
- Maximum wind speed without derating 81 kph / 50 mph

## Power / Temperature Derating Curve <sup>12</sup> & Sample PQ Diagram <sup>13</sup>



12. Applicable for grid voltage ≥ nominal voltage, altitudes >1000m on request



13. Sample PQ diagram for FLEXINVERTER 1566 at nominal grid voltage, 1215 Vdc and 35°C ambient

[www.governova.com/power-conversion/solar-storage](http://www.governova.com/power-conversion/solar-storage)

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license. GE Vernova reserves the right to make technical changes or modify the contents of this document without prior notice. Agreed particulars within purchase order will prevail.