

PRELIMINARY DATA SHEET


FLEXINVERTER 1.5kV SiC BESS PCS

GE Vernova has accumulated more than 30 gigawatts for its renewable energy inverter technology and was one of the first to introduce 1500 Vdc to the market.

The **FLEXINVERTER** is one of the industry's leading 1500 Vdc developments and is GE Vernova's latest evolution in renewable power electronics. Building on expertise in the renewables industry, GE Vernova now offers its latest power conversion technology for efficient, cost effective and dispatchable power.

FLEXINVERTER BESS PCS:

- UL or IEC compliant configurations
- Up to 6.76 MVA output power
- High efficiency
- Air-cooled system
- Plug & play
- Advanced grid features
- Direct outdoor installation
- Standard 20ft ISO high cube container for optimized logistics and installation
- Digital ready




SPECIFICATIONS		UNITS	1569
INPUT DATA			
DC Input Range at Full Power Operation ¹	Vdc		1042 - 1450
Max DC Operating Voltage ¹	Vdc		1500
Max DC Current (up to 35°C / at 50°C)	Adc		6649 / 6115
Max DC Short-Circuit Withstand	kAdc		up to 290kA peak
Number of DC Inputs & cables			Standard 12, up to 24 inputs pairs, up to 400 mm ² / 750 kcmil per DC input
Max DC Fuse Rating per DC Input	Adc		up to 750, multiple fuse ratings available
OUTPUT DATA - MEDIUM VOLTAGE			
Transformer HV/LV Connection			Δ (Delta) / Y (Wye)
Medium Voltage Short Circuit Rating	kA		IEC MVSG - Standard 20kA 1s, (Option 20kA 3s, 25kA 1s) / UL Padmount Transformer - Standard 25kA, (Option 40kA)
Rated Output Power (at 55°C & 0.92 PF) ²	MVA		6.04
AC Output Voltage (+10% / -10%) ²	kVac		22 / 33 / 34.5
AC Power (up to 35°C / at 50°C) ³	MVA		6.76 / 6.22
Max AC Current (up to 35°C)	Aac		178 / 118 / 113
Max AC Current (at 50°C)	Aac		163 / 109 / 104
Grid Frequency ±5%	Hz		50 / 60
Power Factor (PF) Range ²			0 - 1 leading & lagging
Current Harmonic Distortion (TDD)	%		<3
Medium Voltage Cable			Up to 1x 630 mm ² (IEC) 630 Aac / 1x 1500 kcmil (UL) 600 Aac, 900Aac optional, separable connectors possible
EFFICIENCY AND AUXILIARY POWER			
System Efficiency (Average for one way) ⁴	%		97.9
Inverter Efficiency (Average for one way) ⁵	%		98.5
Idle-time Aux Power ⁶	W		≤700
INTERFACES			
Plant Control Interface / PLC			Modbus TCP, EGD
Diagnostic Interface			Modbus TCP
Extra Analog and Digital I/O			Option
Power Station Connections			Internal: CAT7 <30m / External: Fiber Optic
FEATURES AND OPTIONS			
Cooling			Air Cooled
Local Shut Down Button			Included
Mounting Options			Piers / Pad / Piles
DC Configuration Supported			Floating
Idle-time VAR Capability			Option
Insulation Monitoring			Option
Container Color Code			RAL 6026 (Dark Teal)
Disconnect Low Voltage AC Side			Motorized AC Circuit Breaker
Disconnect DC Side			Motorized No-Load DC Switch


SPECIFICATIONS		UNITS	1569
FEATURES AND OPTIONS			
Overvoltage Protection – DC and AC			Included – IEC 61643-1 Class II / UL 1449
Main Power Transformer Oil Type			Mineral - ONAN (Standard) / Biodegradable - KNAN (Option)
Oil Spill Management			Option 1: Collection & drainage Option 2: Full oil containment up to 120% oil-volume
Customer Aux Power Loads ⁷	kVA		Standard 6, Option up to 150 with up to 10 circuits
Revenue Grade Metering			Option
GPS Enabled Fault Timestamping			Option (compliant to MISO App G and CAISO App H)
Altitude ²	m / ft		No derating ≤ 1000 / 3281, up to 4000 / 13124
Noise at 1m ⁸	dBa		Standard ≤79, Acoustic Hood Option ≤71
Weight	kg / lbs		preliminary 21000 / 46297
Dimensions (L x W x H)	m / ft		6.1 x 2.4 x 2.9 / 20.0 x 8.0 x 9.5
PROTECTION RATING AND AMBIENT CONDITIONS			
Operating Temperature Range	°C / °F		Standard -10 to +55 / +14 to +131, Option -25 to +55 / -13 to +131
Cold Weather Option ⁹	°C / °F		Down to -35 / -31
Storage Temperature Range	°C / °F		-40 to +65 / -40 to +149
Humidity	%		5 to 100 (rated for outdoor installation)
Maximum Altitude Without Derating ¹⁰	m / ft		1000 / 3281
Seismic			IBC 2018 / ASCE 7-10 Ss=2g for 0.2 Sec
Maximum Wind Speed ¹¹	kph / mph		257 / 160
Snow Load			ASCE 7
NEMA Rating / IP Class			NEMA 3 / IP54 (Inverter & RMU), NEMA 1 / IP11 (IEC); NEMA 0 / IP00 UL (Transformer Area)
STANDARDS			
Electromagnetic Compatibility (EMC)			EN 61000-6-2, 62920 / CISPR 11
Certifications & Compatibility			IEC, CE & UL 1741 SA, CSA

- At nominal grid voltage, derating according to PQ curves
- Derating will apply according to PQ curves
- AC Power is valid for grid voltage ≥ nominal voltage. Self-consumption (max ~16 kVA) and customer auxiliary loads not included
- Preliminary efficiencies for round trip performance, includes auxiliary power losses, EU Reg. No. 584/2014 available as option
- Preliminary efficiencies round trip performance, includes self-consumption auxiliary power losses
- No heating, no cooling, without environmental controls enabled & DC link de-energized
- Customer Aux Power demand reduces total AC output power
- At 1m in front of enclosure and 1.5m up from the ground. Please respect the restricted areas described in the manual
- Cold weather option on request
- Higher altitudes (with derating) on request
- Maximum wind speed without derating 81 kph / 50 mph

Power / Temperature Derating Curve ¹² & Sample PQ Diagram ¹³



12. Applicable for grid voltage ≥ nominal voltage, altitudes >1000 m on request



13. Sample PQ diagram for FLEXINVERTER

www.governova.com/power-conversion/solar-storage

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license. GE Vernova reserves the right to make technical changes or modify the contents of this document without prior notice. Agreed particulars within purchase order will prevail.