



GE VERNOVA

# MiCOM P40 Agile

## P446

### MICS

Model Implementation Conformance Statement - IEC 61850 Edition 2

Software Version: AB

Publication Reference: P446-MC2-EN-AB-1.1





---

## CONTENTS

---

|            |                                                          |           |
|------------|----------------------------------------------------------|-----------|
| <b>1</b>   | <b>Model Implementation Conformance Statement (MICS)</b> | <b>3</b>  |
| <b>1.1</b> | <b>Introduction</b>                                      | <b>3</b>  |
| <b>1.2</b> | <b>Objective</b>                                         | <b>3</b>  |
| <b>1.3</b> | <b>Logical Device Definitions</b>                        | <b>3</b>  |
| <b>1.4</b> | <b>Logical Node Definitions</b>                          | <b>11</b> |
| <b>1.5</b> | <b>Common Data Class Definitions</b>                     | <b>41</b> |
| <b>1.6</b> | <b>Common Data Attribute Type Definitions</b>            | <b>65</b> |
| <b>1.7</b> | <b>Enumerated Type Definitions</b>                       | <b>68</b> |
| <b>1.8</b> | <b>MMS Data-Type Conversions</b>                         | <b>77</b> |



# 1 MODEL IMPLEMENTATION CONFORMANCE STATEMENT (MICS)

## 1.1 INTRODUCTION

This specification is the Model Implementation Conformance Statement (MICS) and presents the top-level IEC 61850 data model that has been implemented. The definitions of all used Logical Nodes and their associated Common Data Classes, components and associated enumerated values are also included for completeness.

The reader is expected to be conversant with the terminology presented within the IEC 61850 part 7 series of specifications.

## 1.2 OBJECTIVE

To provide comprehensive details of the standard data object model elements supported by the device. The MICS is conformant to the devices associated ICD (Substation Configuration Language) file, according to part 6 of the IEC 61850 standards. The layout of the presented tables within this document are conformant to the part 7 series of the IEC 61850 standard specifications with the following exceptions:

- The "Trigger Options" field is not presented
- The "M/O" field is not present as the definitions are as deployed within the model
- An additional column "X" is used to signify GE custom attributes

## 1.3 LOGICAL DEVICE DEFINITIONS

The MiCOM relay implements an IEC 61850 server that can contain one or more Logical Devices. Each Logical Device contains a data model built from instances of specific Logical Nodes and must consist of at least an instance of the LPHD Logical Node (which is responsible for providing physical device information) and an instance of the LLN0 Logical Node (for addressing common issues across the Logical Device).

The IEC 61850 data model is contained within the Logical Devices detailed in the table below. All MiCOM devices will name the supported Logical Devices consistently to ensure that data model variables with the same purpose will have the same name within each MiCOM server.

| Logical Device | Comment/Usage                                           |
|----------------|---------------------------------------------------------|
| AutoControl    | Command and controls used for Automatic Control         |
| AutoRec1       | Auto Reclose Control Domain for CB 1                    |
| AutoRec2       | Auto Reclose Control Domain for CB 2                    |
| AutoSynChk1    | Automatically Synchronism Check Control Domain for CB 1 |
| AutoSynChk2    | Automatically Synchronism Check Control Domain for CB 2 |
| CBControl      | Commands and controls for CB                            |
| CtlCB1         | Control CB 1                                            |
| CtlCB1Fail     | CBFail Control Domain for CB 1                          |
| CtlCB2         | Control CB 2                                            |
| CtlCB2Fail     | CBFail Control Domain for CB 2                          |
| CtlSw          | Switch Control                                          |
| Measurements   | Power System Measurements                               |
| PloCnt         | Programmable Logic Counters                             |
| ProtDis        | Distance Protection Domain                              |
| Protection     | Protection Elements                                     |
| ProtEfd        | Derived Earth Fault Protection Domain                   |
| ProtEft        | Transient Ground Fault Detection                        |
| ProtFrq        | Frequency Protection                                    |
| ProtNegSeq     | Negative Sequence Protection Domain                     |
| ProtNvd        | Residual Voltage Protection Domain                      |

| Logical Device | Comment/Usage                            |
|----------------|------------------------------------------|
| ProtOST        | Out of Step Tripping Protection Domain   |
| ProtOvCur      | Overcurrent Control Domain               |
| ProtOvThm      | Over Thermal Protection Domain           |
| ProtPsof       | Switch onto Fault Protection Domain      |
| ProtPwr        | Directional Power Protection             |
| ProtPwrSwgBlk  | Power Swing Block Protection Domain      |
| ProtRteChgFrq  | Frequency Change Ratio Protection Domain |
| ProtSchem      | Distance Protection Scheme Domain        |
| ProtSenEF      | Sensitive Earth Fault Protection         |
| ProtVtp        | Time-voltage Protection Domain           |
| Records        | Records Domain                           |
| System         | Global System Data                       |

### 1.3.1 IEC 61850 LOGICAL DEVICE DATA MODEL

The IEC 61850 Logical Device top-level data model consists of instances of Logical Nodes. The data model name for a Logical Node instance is constructed from an optional prefix (known as the wrapper), the Logical Node name, and an instance ID (or suffix).

The presented data model is in an alphabetically sorted order, rather than a logical order, because this is the natural order of the data when presented by a native MMS browser. (Higher level browsers can of course impart any ordering that they desire).

| LD          | LN Instance | LN Type                    | Description                                                |
|-------------|-------------|----------------------------|------------------------------------------------------------|
| AutoControl |             |                            |                                                            |
|             | LLN0        | LLN0_STANDARD              | AutoControl Logical Device                                 |
|             | LPHD1       | LPHD_STANDARD              | Px40 Physical Device Information                           |
| AutoRec1    |             |                            |                                                            |
|             | ArcPTRC16   | PTRC_INDIVID_NO_SEG        | Protection Trip for CB 1 Auto Reclose                      |
|             | ArcRREC1    | RREC_NO_SEG                | Auto Reclose Control Domain for CB 1                       |
|             | LLN0        | LLN0_STANDARD_WITH_CTRLMOD | Logical Device for Auto Reclose Control in CB1             |
| AutoRec2    |             |                            |                                                            |
|             | ArcPTRC17   | PTRC_INDIVID_NO_SEG        | Protection Trip for CB 2 Auto Reclose                      |
|             | ArcRREC2    | RREC_NO_SEG                | Auto Reclose Control Domain for CB 2                       |
|             | LLN0        | LLN0_STANDARD_WITH_CTRLMOD | Logical Device for Auto Reclose Control in CB2             |
| AutoSynChk1 |             |                            |                                                            |
|             | AscRSYN1    | RSYN_DIFCLC_ENH            | System Checks (CB 1) - Check Sync 1                        |
|             | AscRSYN2    | RSYN_DIFCLC_ENH            | System Checks (CB 1) - Check Sync 2                        |
|             | LLN0        | LLN0_STANDARD_WITH_CTRLMOD | Logical Device for CB1 Automatic Synchronism Check Control |
| AutoSynChk2 |             |                            |                                                            |
|             | AscRSYN3    | RSYN_DIFCLC_ENH            | System Checks (CB 2) - Check Sync 1                        |
|             | AscRSYN4    | RSYN_DIFCLC_ENH            | System Checks (CB 2) - Check Sync 2                        |
|             | LLN0        | LLN0_STANDARD_WITH_CTRLMOD | Logical Device for CB2 Automatic Synchronism Check Control |
| CBControl   |             |                            |                                                            |
|             | LLN0        | LLN0_STANDARD              | CBControl Logical Device                                   |
|             | LPHD1       | LPHD_STANDARD              | Px40 Physical Device Information                           |
| CtCB1       |             |                            |                                                            |
|             | CB1CILO1    | CILO_INTERLOCK             | Circuit Breaker Interlocking for CB1                       |
|             | CB1CSWI1    | CSWI_PRIV                  | Switch Controller for CB1                                  |
|             | CB1PTRC1    | PTRC_GLOBAL                | Protection trip for CB 1 Control                           |
|             | CB1XCBR1    | XCBR_BASIC                 | Circuit Breaker 1 Monitoring (Pole 1)                      |

| LD           | LN Instance | LN Type              | Description                             |
|--------------|-------------|----------------------|-----------------------------------------|
|              | CB1XCBR2    | XCBR_BASIC           | Circuit Breaker 1 Monitoring (Pole 2)   |
|              | CB1XCBR3    | XCBR_BASIC           | Circuit Breaker 1 Monitoring (Pole 3)   |
|              | CB1XCBR4    | XCBR_BASIC           | Circuit Breaker 1 Monitoring for 3-pole |
|              | LLN0        | LLN0_STANDARD        | Logical Device for CB 1 Control         |
| CtlCB1Fail   |             |                      |                                         |
|              | Cb1fPTRC18  | PTRC_INDIVID_NO_SEG  | Protection trip for CB1 Fail            |
|              | CbfRBRF1    | RBRF_EXTTRIP         | CB1 Fail 1                              |
|              | CbfRBRF2    | RBRF_EXTTRIP         | CB1 Fail 2                              |
|              | LLN0        | LLN0_STANDARD_CBFAIL | Logical Device for CB1 Fail Control     |
| CtlCB2       |             |                      |                                         |
|              | CB2CILO1    | CILO_INTERLOCK       | Circuit Breaker Interlocking for CB2    |
|              | CB2CSWI1    | CSWI_PRIV            |                                         |
|              | CB2PTRC2    | PTRC_GLOBAL          | Protection trip for CB 2 Control        |
|              | CB2XCBR1    | XCBR_BASIC           | Circuit Breaker 2 Monitoring (Pole 1)   |
|              | CB2XCBR2    | XCBR_BASIC           | Circuit Breaker 2 Monitoring (Pole 2)   |
|              | CB2XCBR3    | XCBR_BASIC           | Circuit Breaker 2 Monitoring (Pole 3)   |
|              | CB2XCBR4    | XCBR_BASIC           | Circuit Breaker 2 Monitoring for 3-pole |
|              | LLN0        | LLN0_STANDARD        | Logical Device for CB 2 Control         |
|              | Cb2fPTRC19  | PTRC_INDIVID_NO_SEG  | Protection trip for CB2 Fail            |
|              | CbfRBRF3    | RBRF_EXTTRIP         | CB2 Fail 1                              |
|              | CbfRBRF4    | RBRF_EXTTRIP         | CB2 Fail 2                              |
|              | LLN0        | LLN0_STANDARD_CBFAIL | Logical Device for CB1 Fail Control     |
| CtlSw        |             |                      |                                         |
|              | LLN0        | LLN0_STANDARD        | Switch Control Logical Device           |
|              | SwCILO1     | CILO_INTERLOCK       | XSWI1 Interlocking                      |
|              | SwCILO2     | CILO_INTERLOCK       | XSWI2 Interlocking                      |
|              | SwCILO3     | CILO_INTERLOCK       | XSWI3 Interlocking                      |
|              | SwCILO4     | CILO_INTERLOCK       | XSWI4 Interlocking                      |
|              | SwCILO5     | CILO_INTERLOCK       | XSWI5 Interlocking                      |
|              | SwCILO6     | CILO_INTERLOCK       | XSWI6 Interlocking                      |
|              | SwCILO7     | CILO_INTERLOCK       | XSWI7 Interlocking                      |
|              | SwCILO8     | CILO_INTERLOCK       | XSWI8 Interlocking                      |
|              | SwCSWI1     | CSWI_PRIV            | Control Sw 1                            |
|              | SwCSWI2     | CSWI_PRIV            | Control Sw 2                            |
|              | SwCSWI3     | CSWI_PRIV            | Control Sw 3                            |
|              | SwCSWI4     | CSWI_PRIV            | Control Sw 4                            |
|              | SwCSWI5     | CSWI_PRIV            | Control Sw 5                            |
|              | SwCSWI6     | CSWI_PRIV            | Control Sw 6                            |
|              | SwCSWI7     | CSWI_PRIV            | Control Sw 7                            |
|              | SwCSWI8     | CSWI_PRIV            | Control Sw 8                            |
|              | SwXSWI1     | XSWI_BASIC           | Switch Monitoring and Control           |
|              | SwXSWI2     | XSWI_BASIC           | Switch Monitoring and Control           |
|              | SwXSWI3     | XSWI_BASIC           | Switch Monitoring and Control           |
|              | SwXSWI4     | XSWI_BASIC           | Switch Monitoring and Control           |
|              | SwXSWI5     | XSWI_BASIC           | Switch Monitoring and Control           |
|              | SwXSWI6     | XSWI_BASIC           | Switch Monitoring and Control           |
|              | SwXSWI7     | XSWI_BASIC           | Switch Monitoring and Control           |
|              | SwXSWI8     | XSWI_BASIC           | Switch Monitoring and Control           |
| Measurements |             |                      |                                         |
|              | LLN0        | LLN0_STANDARD_MEA    | Measurements Logical Device             |
|              | LPHD1       | LPHD_STANDARD        | Physical Device Information             |

| LD     | LN Instance    | LN Type                     | Description                                                                             |
|--------|----------------|-----------------------------|-----------------------------------------------------------------------------------------|
|        | PriAvgMMXU1    | MMXU_METER_AV               | Primary Average Value of Fixed Measurements                                             |
|        | PriAvgMMXU2    | MMXU_METER_AV               | Primary Average Value of Rolled Measurements                                            |
|        | PriFitMLFR1    | MLFR_FAULT_RECORD_NODIF_CB2 | Measurements during the Latest Fault Record without Differential Protection for two CBs |
|        | PriFouMMXU1    | MMXU_FOURIER_CB2_EXT        | Primary Fourier Measurements including Df/Dt                                            |
|        | PriMaxMMXU1    | MMXU_METER_MAX              | Primary Maximum Value of Measurement                                                    |
|        | PriMMTR1       | MMTR_PRIV                   | Primary based metering quantities                                                       |
|        | PriMSQI1       | MSQI_ALL                    | Primary Sequence Measurements                                                           |
|        | PriPreFitMLFR1 | MLFR_PRE_FAULT              | Fault Record before fault                                                               |
|        | PriRmsMMXU1    | MMXU_RMS                    | Primary RMS Measurements                                                                |
|        | PriVcpMSQI1    | MSQI_VOLTAGE                | Primary Compensated Overvoltage Measurements                                            |
|        | SecAvgMMXU1    | MMXU_METER_AV               | Secondary Average Value of Fixed Measurements                                           |
|        | SecAvgMMXU2    | MMXU_METER_AV               | Secondary Average Value of Rolled Measurements                                          |
|        | SecFouMMXU1    | MMXU_FOURIER_CB2_EXT        | Secondary Fourier Measurements including Df/Dt                                          |
|        | SecMaxMMXU1    | MMXU_METER_MAX              | Secondary Maximum Value of Measurement                                                  |
|        | SecMMTR1       | MMTR_PRIV                   | Secondary based metering quantities                                                     |
|        | SecMSQI1       | MSQI_ALL                    | Secondary Sequence Measurements                                                         |
|        | SecRmsMMXU1    | MMXU_RMS                    | Secondary RMS Measurements                                                              |
|        | SecVcpMSQI1    | MSQI_VOLTAGE                | Secondary Compensated Overvoltage Measurements                                          |
| PloCnt |                |                             |                                                                                         |
|        | CntFCNT1       | FCNT_COUNTER                | PSL Settable Counter 1                                                                  |
|        | CntFCNT10      | FCNT_COUNTER                | PSL Settable Counter 10                                                                 |
|        | CntFCNT11      | FCNT_COUNTER                | PSL Settable Counter 11                                                                 |
|        | CntFCNT12      | FCNT_COUNTER                | PSL Settable Counter 12                                                                 |
|        | CntFCNT13      | FCNT_COUNTER                | PSL Settable Counter 13                                                                 |
|        | CntFCNT14      | FCNT_COUNTER                | PSL Settable Counter 14                                                                 |
|        | CntFCNT15      | FCNT_COUNTER                | PSL Settable Counter 15                                                                 |
|        | CntFCNT16      | FCNT_COUNTER                | PSL Settable Counter 16                                                                 |
|        | CntFCNT17      | FCNT_COUNTER                | PSL Settable Counter 17                                                                 |
|        | CntFCNT18      | FCNT_COUNTER                | PSL Settable Counter 18                                                                 |
|        | CntFCNT19      | FCNT_COUNTER                | PSL Settable Counter 19                                                                 |
|        | CntFCNT2       | FCNT_COUNTER                | PSL Settable Counter 2                                                                  |
|        | CntFCNT20      | FCNT_COUNTER                | PSL Settable Counter 20                                                                 |
|        | CntFCNT21      | FCNT_COUNTER                | PSL Settable Counter 21                                                                 |
|        | CntFCNT22      | FCNT_COUNTER                | PSL Settable Counter 22                                                                 |
|        | CntFCNT23      | FCNT_COUNTER                | PSL Settable Counter 23                                                                 |
|        | CntFCNT24      | FCNT_COUNTER                | PSL Settable Counter 24                                                                 |
|        | CntFCNT25      | FCNT_COUNTER                | PSL Settable Counter 25                                                                 |
|        | CntFCNT26      | FCNT_COUNTER                | PSL Settable Counter 26                                                                 |
|        | CntFCNT27      | FCNT_COUNTER                | PSL Settable Counter 27                                                                 |
|        | CntFCNT28      | FCNT_COUNTER                | PSL Settable Counter 28                                                                 |
|        | CntFCNT29      | FCNT_COUNTER                | PSL Settable Counter 29                                                                 |
|        | CntFCNT3       | FCNT_COUNTER                | PSL Settable Counter 3                                                                  |
|        | CntFCNT30      | FCNT_COUNTER                | PSL Settable Counter 30                                                                 |
|        | CntFCNT31      | FCNT_COUNTER                | PSL Settable Counter 31                                                                 |
|        | CntFCNT32      | FCNT_COUNTER                | PSL Settable Counter 32                                                                 |
|        | CntFCNT4       | FCNT_COUNTER                | PSL Settable Counter 4                                                                  |
|        | CntFCNT5       | FCNT_COUNTER                | PSL Settable Counter 5                                                                  |
|        | CntFCNT6       | FCNT_COUNTER                | PSL Settable Counter 6                                                                  |
|        | CntFCNT7       | FCNT_COUNTER                | PSL Settable Counter 7                                                                  |
|        | CntFCNT8       | FCNT_COUNTER                | PSL Settable Counter 8                                                                  |

| LD         | LN Instance  | LN Type                    | Description                                          |
|------------|--------------|----------------------------|------------------------------------------------------|
|            | CntFCNT9     | FCNT_COUNTER               | PSL Settable Counter 9                               |
|            | LLN0         | LLN0_STANDARD              | Programmable Logic Counters Logical Device           |
| ProtDis    |              |                            |                                                      |
|            | DisPDIS1     | PDIS_BASIC                 | Zone 1 Ph/Gnd Distance                               |
|            | DisPDIS2     | PDIS_BASIC                 | Zone 2 Ph/Gnd Distance                               |
|            | DisPDIS3     | PDIS_BASIC                 | Zone 3 Ph/Gnd Distance                               |
|            | DisPDIS4     | PDIS_BASIC                 | Zone 4 Ph/Gnd Distance                               |
|            | DisPDIS5     | PDIS_BASIC                 | Zone P Ph/Gnd Distance                               |
|            | DisPDIS6     | PDIS_BASIC                 | Zone Q Ph/Gnd Distance                               |
|            | DisPDIS7     | PDIS_BASIC                 | Zone R Ph/Gnd Distance                               |
|            | DisPDIS8     | PDIS_BASIC                 | Zone S Ph/Gnd Distance                               |
|            | DisPDIS9     | PDIS_BASIC                 | Zone 1e Ph/Gnd Distance                              |
|            | DisPTRC3     | PTRC_INDIVID_NO_SEG        | Protection trip for Distance Protection              |
|            | LLN0         | LLN0_STANDARD_WITH_CTRLMOD | Logical Device for Distance Protection               |
| Protection |              |                            |                                                      |
|            | LLN0         | LLN0_STANDARD              | Protection Logical Device with Standard Template     |
|            | LPHD1        | LPHD_STANDARD              | Physical Device Information                          |
| ProtEfd    |              |                            |                                                      |
|            | EfdPTOC1     | PTOC_NEU                   | IN1> 1 Earth Fault (Derived)                         |
|            | EfdPTOC2     | PTOC_NEU                   | IN1> 2 Earth Fault (Derived)                         |
|            | EfdPTOC3     | PTOC_NEU                   | IN1> 3 Earth Fault (Derived)                         |
|            | EfdPTOC4     | PTOC_NEU                   | IN1> 4 Earth Fault (Derived)                         |
|            | EfdPTRC9     | PTRC_INDIVID_NO_SEG        | Protection trip for Earth Fault (Derived) protection |
|            | LLN0         | LLN0_STANDARD_WITH_CTRLMOD | Logical Device for Efd Protection                    |
| ProtEft    |              |                            |                                                      |
|            | EftPTEF1     | PTEF_NEU                   | Transient Earth Fault Alarm                          |
|            | EftPTRC21    | PTRC_INDIVID_NO_SEG        | Transient Earth Fault Alarm                          |
|            | LLN0         | LLN0_STANDARD_WITH_CTRLMOD | Logical Node for Eft Protection                      |
| ProtFrq    |              |                            |                                                      |
|            | FrqPTOF1     | PTOF_NO_SEG                | F> 1 Overfrequency                                   |
|            | FrqPTOF2     | PTOF_NO_SEG                | F> 2 Overfrequency                                   |
|            | FrqPTRC10    | PTRC_INDIVID_NO_SEG        | Protection trip for Frequency Protection             |
|            | FrqPTUF1     | PTUF_NO_SEG                | F< 1 Underfrequency                                  |
|            | FrqPTUF2     | PTUF_NO_SEG                | F< 2 Underfrequency                                  |
|            | FrqPTUF3     | PTUF_NO_SEG                | F< 3 Underfrequency                                  |
|            | FrqPTUF4     | PTUF_NO_SEG                | F< 4 Underfrequency                                  |
|            | LLN0         | LLN0_STANDARD_WITH_CTRLMOD | Logical Device for Frequency Protection              |
| ProtNegSeq |              |                            |                                                      |
|            | LLN0         | LLN0_STANDARD_WITH_CTRLMOD | Logical Device for Negative Sequence Protection      |
|            | NgcPTOC1     | PTOC_NO_SEG                | I2> 1 Negative Sequence                              |
|            | NgcPTOC2     | PTOC_NO_SEG                | I2> 2 Negative Sequence                              |
|            | NgcPTOC3     | PTOC_NO_SEG                | I2> 3 Negative Sequence                              |
|            | NgcPTOC4     | PTOC_NO_SEG                | I2> 4 Negative Sequence                              |
|            | NgcPTRC11    | PTRC_INDIVID_NO_SEG        | Protection trip for Negative Sequence Protection     |
| ProtNvd    |              |                            |                                                      |
|            | LLN0         | LLN0_STANDARD_WITH_CTRLMOD | Logical Device for Nvd Protection                    |
|            | VtpResPTOV1  | PTOV_NEU                   | VN> 1 Residual Overvoltage                           |
|            | VtpResPTOV2  | PTOV_NEU                   | VN> 2 Residual Overvoltage                           |
|            | VtpResPTRC14 | PTRC_INDIVID_NO_SEG        | Protection trip for Nvd protection                   |
| ProtOST    |              |                            |                                                      |
|            | LLN0         | LLN0_STANDARD_WITH_CTRLMOD | Logical Device for OST Protection                    |

| LD            | LN Instance | LN Type                    | Description                                          |
|---------------|-------------|----------------------------|------------------------------------------------------|
|               | OstPTRC15   | PTRC_INDIVID_NO_SEG        | Protection trip for OST protection                   |
|               | OstRPSB1    | RPSB_OST                   | Out of Step Tripping (main trip)                     |
|               | OstRPSB2    | RPSB_OST                   | Out of Step Tripping (predictive )                   |
| ProtOvCur     |             |                            |                                                      |
|               | LLN0        | LLN0_STANDARD_WITH_CTRLMOD | Logical Device for Overcurrent Protection            |
|               | OcpPTOC1    | PTOC_SEG                   | I> 1 Overcurrent                                     |
|               | OcpPTOC2    | PTOC_SEG                   | I> 2 Overcurrent                                     |
|               | OcpPTOC3    | PTOC_SEG                   | I> 3 Overcurrent                                     |
|               | OcpPTOC4    | PTOC_SEG                   | I> 4 Overcurrent                                     |
|               | OcpPTRC7    | PTRC_INDIVID_NO_SEG        | Protection trip for Overcurrent Protection           |
| ProtOvThm     |             |                            |                                                      |
|               | LLN0        | LLN0_STANDARD_WITH_CTRLMOD | Logical Device for Thermal Overload Protection       |
|               | ThmPTRC20   | PTRC_INDIVID_NO_SEG        | Protection trip for thermal Overload                 |
|               | ThmPTTR1    | PTTR_NO_SEG                | Thermal Overload                                     |
| ProtPsof      |             |                            |                                                      |
|               | LLN0        | LLN0_STANDARD              | Logical Device for Switch onto Fault Protection      |
|               | PsofPTRC6   | PTRC_INDIVID_NO_SEG        | Protection trip for Switch onto Fault Protection     |
|               | SofPSOF1    | PSOF_SOTF_OP               | Switch onto Fault protection                         |
|               | TorPSOF1    | PSOF_TOR_OP                | Trip on Reclose Protection                           |
| ProtPwr       |             |                            |                                                      |
|               | LLN0        | LLN0_STANDARD_WITH_CTRLMOD | Logic device for directional power protection        |
|               | PdpPDOP1    | PDOP_BASIC                 | Directional overpower stage 1                        |
|               | PdpPDOP2    | PDOP_BASIC                 | Directional overpower stage 2                        |
|               | PdpPDOP3    | PDOP_BASIC                 | Directional overpower stage 3                        |
|               | PdpPDOP4    | PDOP_BASIC                 | Directional overpower stage 4                        |
|               | PdpPDUP1    | PDUP_BASIC                 | Directional underpower stage 1                       |
|               | PdpPDUP2    | PDUP_BASIC                 | Directional underpower stage 2                       |
|               | PdpPDUP3    | PDUP_BASIC                 | Directional underpower stage 3                       |
|               | PdpPDUP4    | PDUP_BASIC                 | Directional underpower stage 4                       |
|               | PdpPTRC22   | PTRC_INDIVID_NO_SEG        | Protection trip for directional power                |
| ProtPwrSwgBlk |             |                            |                                                      |
|               | LLN0        | LLN0_STANDARD_WITH_CTRLMOD | Logical Device for Power Swing                       |
|               | PsbRPSB1    | RPSB_PSB_MULT              | Zone 1 Ph/Gnd Power Swing                            |
|               | PsbRPSB2    | RPSB_PSB_MULT              | Zone 2 Ph/Gnd Power Swing                            |
|               | PsbRPSB3    | RPSB_PSB_MULT              | Zone 3 Ph/Gnd Power Swing                            |
|               | PsbRPSB4    | RPSB_PSB_MULT              | Zone 4 Ph/Gnd Power Swing                            |
|               | PsbRPSB5    | RPSB_PSB_MULT              | Zone 5 Ph/Gnd Power Swing                            |
|               | PsbRPSB6    | RPSB_PSB_MULT              | Zone Q Ph/Gnd Power Swing                            |
|               | PsbRPSB7    | RPSB_PSB_MULT              | Zone R Ph/Gnd Power Swing                            |
|               | PsbRPSB8    | RPSB_PSB_MULT              | Zone S Ph/Gnd Power Swing                            |
|               | PsbRPSB9    | RPSB_PSB_MULT              | Zone 1e Ph/Gnd Power Swing                           |
| ProtRteChgFrq |             |                            |                                                      |
|               | DfpPFRC1    | PFRC_NO_SEG                | df/dt> 1 Frequency Rate of Change                    |
|               | DfpPFRC2    | PFRC_NO_SEG                | df/dt> 2 Frequency Rate of Change                    |
|               | DfpPFRC3    | PFRC_NO_SEG                | df/dt> 3 Frequency Rate of Change                    |
|               | DfpPFRC4    | PFRC_NO_SEG                | df/dt> 4 Frequency Rate of Change                    |
|               | DfpPTRC8    | PTRC_INDIVID_NO_SEG        | Protection trip for Frequency Rate Change Protection |
|               | LLN0        | LLN0_STANDARD_WITH_CTRLMOD | Logical Device for Frequency Rate Change Protection  |
| ProtSchem     |             |                            |                                                      |
|               | DisPSCH1    | PSCH_EXTENSION             | Distance Protection Scheme 1                         |
|               | DisPSCH2    | PSCH_EXTENSION             | Distance Protection Scheme 2                         |

| LD        | LN Instance  | LN Type                    | Description                                            |
|-----------|--------------|----------------------------|--------------------------------------------------------|
|           | DisSchPTRC5  | PTRC_INDIVID_NO_SEG        | Protection trip for Distance Protection Scheme         |
|           | LLN0         | LLN0_STANDARD              | Logical Device for Distance Protection Scheme          |
| ProtSenEF |              |                            |                                                        |
|           | LLN0         | LLN0_STANDARD_WITH_CTRLMOD | Logical device for Sensitive Earth Fault protection    |
|           | SenEffPSDE1  | PSDE_NEU                   | ISEF>1 Sensitive Earth fault                           |
|           | SenEffPSDE2  | PSDE_NEU                   | ISEF>2 Sensitive Earth fault                           |
|           | SenEffPSDE3  | PSDE_NEU                   | ISEF>3 Sensitive Earth fault                           |
|           | SenEffPSDE4  | PSDE_NEU                   | ISEF>4 Sensitive Earth fault                           |
|           | SenEffPTRC13 | PTRC_INDIVID_NO_SEG        | Protection trip for Sensitive Earth Fault              |
|           | SenRefPDIF1  | PDIF_NEU                   | IREF> 1 Restricted Earth Fault                         |
| ProtVtp   |              |                            |                                                        |
|           | LLN0         | LLN0_STANDARD_WITH_CTRLMOD | Logical Device for Vtp Protection                      |
|           | VtpCmpPTOV1  | PTOV_NO_SEG                | Compensated V1> 1 Overvoltage                          |
|           | VtpCmpPTOV2  | PTOV_NO_SEG                | Compensated V1> 2 Overvoltage                          |
|           | VtpPhsPTOV1  | PTOV_SEG                   | V> 1 Overvoltage                                       |
|           | VtpPhsPTOV2  | PTOV_SEG                   | V> 2 Overvoltage                                       |
|           | VtpPhsPTRC12 | PTRC_INDIVID_NO_SEG        | Protection trip for Vtp Protection                     |
|           | VtpPhsPTUV1  | PTUV_SEG                   | V< 1 Undervoltage                                      |
|           | VtpPhsPTUV2  | PTUV_SEG                   | V< 2 Undervoltage                                      |
| Records   |              |                            |                                                        |
|           | LLN0         | LLN0_STANDARD              | Records Logical Device                                 |
|           | LPHD1        | LPHD_STANDARD              | Physical Device Information                            |
|           | RDRE1        | RDRE_BASIC                 | Disturbance Recorder                                   |
|           | RFLO1        | RFLO_BASIC                 | Fault Locator                                          |
| System    |              |                            |                                                        |
|           | AlmCALH1     | CALH_ALARM                 | CALH_Alarm                                             |
|           | AlmCALH2     | CALH_ALARM                 | CALH_Alarm                                             |
|           | AlmCALH3     | CALH_ALARM                 | CALH_Alarm                                             |
|           | AlmCALH4     | CALH_ALARM                 | CALH_Alarm                                             |
|           | AlmCALH5     | CALH_ALARM                 | CALH_Alarm                                             |
|           | AlmCALH6     | CALH_ALARM                 | CALH_Alarm                                             |
|           | AlmCALH7     | CALH_ALARM                 | CALH_Alarm                                             |
|           | AlmCALH8     | CALH_ALARM                 | CALH_Alarm                                             |
|           | AlmGGIO1     | GGIO_ALM_128               | Alarms                                                 |
|           | FnkGGIO1     | GGIO_IND_10                | Function Keys                                          |
|           | GosGGIO1     | GGIO_IND_128               | GOOSE Input Signals                                    |
|           | GosGGIO2     | GGIO_IND_128               | GOOSE Output Signals                                   |
|           | ImfInpGGIO1  | GGIO_IND_24                | InterMiCOM Fibre Inputs Status (CH1)                   |
|           | ImfInpGGIO2  | GGIO_IND_24                | InterMiCOM Fibre Inputs Status (CH2)                   |
|           | ImfOutGGIO1  | GGIO_IND_24                | InterMiCOM Fibre Outputs Status (CH1)                  |
|           | ImfOutGGIO2  | GGIO_IND_24                | InterMiCOM Fibre Outputs Status (CH2)                  |
|           | ITPC1        | ITPC_SYSTEM                | Teleprotection Communication Interfaces for Channel 1  |
|           | LedGGIO1     | GGIO_IND_23                | Red LED Signals                                        |
|           | LedGGIO2     | GGIO_IND_23                | Green LED Signals                                      |
|           | LGOS1        | LGOS_SYSTEM                | Monitoring of GOOSE Messages for External Publisher 1  |
|           | LGOS10       | LGOS_SYSTEM                | Monitoring of GOOSE Messages for External Publisher 10 |
|           | LGOS11       | LGOS_SYSTEM                | Monitoring of GOOSE Messages for External Publisher 11 |
|           | LGOS12       | LGOS_SYSTEM                | Monitoring of GOOSE Messages for External Publisher 12 |
|           | LGOS13       | LGOS_SYSTEM                | Monitoring of GOOSE Messages for External Publisher 13 |
|           | LGOS14       | LGOS_SYSTEM                | Monitoring of GOOSE Messages for External Publisher 14 |
|           | LGOS15       | LGOS_SYSTEM                | Monitoring of GOOSE Messages for External Publisher 15 |

[illegible]

| LD | LN Instance  | LN Type              | Description                                            |
|----|--------------|----------------------|--------------------------------------------------------|
|    | LGOS62       | LGOS_SYSTEM          | Monitoring of GOOSE Messages for External Publisher 62 |
|    | LGOS63       | LGOS_SYSTEM          | Monitoring of GOOSE Messages for External Publisher 63 |
|    | LGOS64       | LGOS_SYSTEM          | Monitoring of GOOSE Messages for External Publisher 64 |
|    | LGOS7        | LGOS_SYSTEM          | Monitoring of GOOSE Messages for External Publisher 7  |
|    | LGOS8        | LGOS_SYSTEM          | Monitoring of GOOSE Messages for External Publisher 8  |
|    | LGOS9        | LGOS_SYSTEM          | Monitoring of GOOSE Messages for External Publisher 9  |
|    | LLN0         | LLN0_SYSTEM          | System Logical Device                                  |
|    | LPHD1        | LPHD_SYSTEM          | Physical Device Information for System Logical Device  |
|    | LSVS1        | LSVS_SYSTEM          | Sampled Value Subscription for SV LN1                  |
|    | LSVS2        | LSVS_SYSTEM          | Sampled Value Subscription for SV LN2                  |
|    | LSVS3        | LSVS_SYSTEM          | Sampled Value Subscription for SV LN3                  |
|    | LSVS4        | LSVS_SYSTEM          | Sampled Value Subscription for SV LN4                  |
|    | LSVS5        | LSVS_SYSTEM          | Sampled Value Subscription for SV LN5                  |
|    | LSVS6        | LSVS_SYSTEM          | Sampled Value Subscription for SV LN6                  |
|    | LSVS7        | LSVS_SYSTEM          | Sampled Value Subscription for SV LN7                  |
|    | LSVS8        | LSVS_SYSTEM          | Sampled Value Subscription for SV LN8                  |
|    | LSVS9        | LSVS_SYSTEM          | Sampled Value Subscription for SV LN9                  |
|    | LTIM1        | LTIM_SYSTEM          | Time Management                                        |
|    | LTMS1        | LTMS_SYSTEM          | Time master supervision                                |
|    | NP1LCCH1     | LCCH_SYSTEM_ENG_PORT | Physical communication channel supervision             |
|    | NP2LCCH2     | LCCH_SYSTEM          | Physical communication channel supervision             |
|    | OptGGIO1     | GGIO_IND_40          | Opto (40) Inputs                                       |
|    | PloGGIO1     | GGIO_IND_32_CTRL     | Controllable Inputs                                    |
|    | RlyGGIO1     | GGIO_IND_43          | Output (43) Contacts                                   |
|    | TVTR1        | TVTR_SYSTEM          | Voltage transformer monitor                            |
|    | UstrAlmGGIO1 | GGIO_USER_ALM_32     | User Alarms                                            |
|    | UstrGGIO1    | GGIO_IND_DPS_8       | User Mapped (PSL) Double Point Status Indications      |

## 1.4 LOGICAL NODE DEFINITIONS

The definition tables for each of the Logical Nodes in the top-level data model are presented in the following sub-sections.

The following table presents a summary of the Logical Node templates used across the Logical Devices within the overall IEC 61850 product data model:

| LN Type          | (LN Class) | Description                                                         | Name Space          |
|------------------|------------|---------------------------------------------------------------------|---------------------|
| CALH_ALARM       | (CALH)     | Logical Node for Group Alarms, Group Warnings and Group Indications | IEC 61850-7-4:2007B |
| CILO_INTERLOCK   | (CILO)     | Control Interlocking                                                | IEC 61850-7-4:2007B |
| CSWI_PRIV        | (CSWI)     | Switch controller (with extended DO 'CtIEna')                       | IEC 61850-7-4:2007B |
| FCNT_COUNTER     | (FCNT)     | Counter                                                             | IEC 61850-7-4:2007B |
| GGIO_IND_23      | (GGIO)     | Generic process I/O (w.r.t 23 Indication Elements)                  | IEC 61850-7-4:2007B |
| GGIO_USER_ALM_32 | (GGIO)     | Generic process I/O                                                 | IEC 61850-7-4:2007B |
| GGIO_IND_DPS_8   | (GGIO)     | Generic process I/O (w.r.t 8 Dual Point Status Indication Elements) | IEC 61850-7-4:2007B |
| GGIO_IND_43      | (GGIO)     | Generic process I/O (w.r.t 43 Indication Elements)                  | IEC 61850-7-4:2007B |
| GGIO_IND_40      | (GGIO)     | Generic process I/O (w.r.t 40 Indication Elements)                  | IEC 61850-7-4:2007B |
| GGIO_IND_24      | (GGIO)     | Generic process I/O (w.r.t 24 Indication Elements)                  | IEC 61850-7-4:2007B |
| GGIO_IND_128     | (GGIO)     | Generic process I/O (w.r.t 128 indications)                         | IEC 61850-7-4:2007B |
| GGIO_IND_10      | (GGIO)     | Generic Process I/O (w.r.t 10 Indication Elements)                  | IEC 61850-7-4:2007B |
| GGIO_ALM_128     | (GGIO)     | Generic process I/O (w.r.t 128 Alarm Elements)                      | IEC 61850-7-4:2007B |

| LN Type                     | (LN Class) | Description                                                                 | Name Space          |
|-----------------------------|------------|-----------------------------------------------------------------------------|---------------------|
| GGIO_IND_32_CTRL            | (GGIO)     | Generic process I/O (w.r.t 32 Indications Ctrl i/p)                         | IEC 61850-7-4:2007B |
| ITPC_SYSTEM                 | (ITPC)     | Teleprotection communication interfaces                                     | IEC 61850-7-4:2007B |
| LCCH_SYSTEM_ENG_PORT        | (LCCH)     | Physical communication channel supervision                                  | IEC 61850-7-4:2007B |
| LCCH_SYSTEM                 | (LCCH)     | Physical communication channel supervision                                  | IEC 61850-7-4:2007B |
| LGOS_SYSTEM                 | (LGOS)     | Monitoring of GOOSE messages                                                | IEC 61850-7-4:2007B |
| LLN0_STANDARD               | (LLN0)     | General Logical Node 0                                                      | IEC 61850-7-4:2007B |
| LLN0_STANDARD_CBFAIL        | (LLN0)     | Logical Node 0 in CBFail                                                    | IEC 61850-7-4:2007B |
| LLN0_STANDARD_MEA           | (LLN0)     | Measurements Logical Node 0                                                 | IEC 61850-7-4:2007B |
| LLN0_STANDARD_WITH_CTRLMOD  | (LLN0)     | Logical Node 0                                                              | IEC 61850-7-4:2007B |
| LLN0_SYSTEM                 | (LLN0)     | System Logical Node 0                                                       | IEC 61850-7-4:2007B |
| LPHD_SYSTEM                 | (LPHD)     | Px40 Physical Device Information (used for Logical Device System only)      | IEC 61850-7-4:2007B |
| LPHD_STANDARD               | (LPHD)     | Px40 Physical Device Information                                            | IEC 61850-7-4:2007B |
| LSVS_SYSTEM                 | (LSVS)     | Sampled value subscription                                                  | IEC 61850-7-4:2007B |
| LTIM_SYSTEM                 | (LTIM)     | Time management                                                             | IEC 61850-7-4:2007B |
| LTMS_SYSTEM                 | (LTMS)     | Time master supervision                                                     | IEC 61850-7-4:2007B |
| MLFR_FAULT_RECORD_NODIF_CB2 | (MLFR)     | Measurements of Fault Record without Differential Protection                | GE-SII:Px40:2013A   |
| MLFR_PRE_FAULT              | (MLFR)     | Measurements of Fault Record                                                | GE-SII:Px40:2013A   |
| MMTR_PRIV                   | (MMTR)     | Metering                                                                    | IEC 61850-7-4:2007B |
| MMXU_RMS                    | (MMXU)     | Standard Measurements (w.r.t RMS Values)                                    | IEC 61850-7-4:2007B |
| MMXU_FOURIER_CB2_EXT        | (MMXU)     | Standard measurements for CB2 (w.r.t Fourier Values Including Df/Dt)        | IEC 61850-7-4:2007B |
| MMXU_METER_AV               | (MMXU)     | Metering Statistics (w.r.t Current, Real + Reactive Power - Average values) | IEC 61850-7-4:2007B |
| MMXU_METER_MAX              | (MMXU)     | Standard measurements (w.r.t Current, Real + Reactive Power - Max values)   | IEC 61850-7-4:2007B |
| MSQI_VOLTAGE                | (MSQI)     | Sequence and imbalance (w.r.t Pos, Neg, Zero Voltage Only)                  | IEC 61850-7-4:2007B |
| MSQI_ALL                    | (MSQI)     | Sequence and imbalance (w.r.t Pos, Neg, Zero)                               | IEC 61850-7-4:2007B |
| PDIF_NEU                    | (PDIF)     | Differential (w.r.t Neutral)                                                | IEC 61850-7-4:2007B |
| PDIS_BASIC                  | (PDIS)     | Distance (w.r.t Mandatory Attributes only)                                  | IEC 61850-7-4:2007B |
| PDOP_BASIC                  | (PDOP)     | Directional overpower                                                       | IEC 61850-7-4:2007B |
| PDUP_BASIC                  | (PDUP)     | Directional underpower                                                      | IEC 61850-7-4:2007B |
| PFRC_NO_SEG                 | (PFRC)     | Rate of change of frequency (w.r.t No Phase Segregation)                    | IEC 61850-7-4:2007B |
| PSCH_EXTENSION              | (PSCH)     | Protection scheme extensions for ed2                                        | IEC 61850-7-4:2007B |
| PSDE_NEU                    | (PSDE)     | Sensitive directional earthfault                                            | IEC 61850-7-4:2007B |
| PSOF_TOR_OP                 | (PSOF)     | Trip-on-Reclose Protection                                                  | IEC 61850-7-4:2007B |
| PSOF_SOTF_OP                | (PSOF)     | Switch-onto-Fault Protection (w.r.t Multiple Zone Operate)                  | IEC 61850-7-4:2007B |
| PTEF_NEU                    | (PTEF)     | Transient earth fault (w.r.t Neutral)                                       | IEC 61850-7-4:2007B |
| PTOC_NEU                    | (PTOC)     | Timed Overcurrent (w.r.t Neutral)                                           | IEC 61850-7-4:2007B |
| PTOC_NO_SEG                 | (PTOC)     | Timed Overcurrent (w.r.t No Phase Segregation)                              | IEC 61850-7-4:2007B |
| PTOC_SEG                    | (PTOC)     | Timed Overcurrent (w.r.t Phase Segregation)                                 | IEC 61850-7-4:2007B |
| PTOF_NO_SEG                 | (PTOF)     | Overfrequency (w.r.t No Phase Segregation)                                  | IEC 61850-7-4:2007B |
| PTOV_SEG                    | (PTOV)     | Overvoltage (w.r.t Phase Segregation)                                       | IEC 61850-7-4:2007B |
| PTOV_NO_SEG                 | (PTOV)     | Overvoltage (w.r.t No Phase Segregation)                                    | IEC 61850-7-4:2007B |
| PTOV_NEU                    | (PTOV)     | Overvoltage (w.r.t Neutral)                                                 | IEC 61850-7-4:2007B |
| PTRC_GLOBAL                 | (PTRC)     | Protection trip for global protection conditioning                          | IEC 61850-7-4:2007B |
| PTRC_INDIVID_NO_SEG         | (PTRC)     | Protection trip for individual protection conditioning                      | IEC 61850-7-4:2007B |
| PTTR_NO_SEG                 | (PTTR)     | Thermal overload (w.r.t No Phase Segregation)                               | IEC 61850-7-4:2007B |
| PTUF_NO_SEG                 | (PTUF)     | Underfrequency (w.r.t No Phase Segregation)                                 | IEC 61850-7-4:2007B |
| PTUV_SEG                    | (PTUV)     | Undervoltage (w.r.t Phase Segregation)                                      | IEC 61850-7-4:2007B |
| RBRF_EXTTRIP                | (RBRF)     | Breaker Failure (w.r.t External Tripping)                                   | IEC 61850-7-4:2007B |

| LN Type         | (LN Class) | Description                                                                        | Name Space          |
|-----------------|------------|------------------------------------------------------------------------------------|---------------------|
| RDRE_BASIC      | (RDRE)     | Disturbance Recorder function (w.r.t Mandatory Attributes only)                    | IEC 61850-7-4:2007B |
| RFLO_BASIC      | (RFLO)     | Fault Locator (w.r.t Mandatory Attributes only)                                    | IEC 61850-7-4:2007B |
| RPSB_OST        | (RPSB)     | Power Swing Blocking (w.r.t Out of Step Tripping)                                  | IEC 61850-7-4:2007B |
| RPSB_PSB_MULT   | (RPSB)     | Power swing detection/blocking (w.r.t Mandatory Attributes only + Multiple Starts) | IEC 61850-7-4:2007B |
| RREC_NO_SEG     | (RREC)     | Autoreclosing (w.r.t No Phase Segregation)                                         | IEC 61850-7-4:2007B |
| RSYN_DIFCLC_ENH | (RSYN)     | Synchronism-check/Synchronising (w.r.t Calculated Differential Measurements)       | IEC 61850-7-4:2007B |
| TVTR_SYSTEM     | (TVTR)     | Voltage transformer                                                                | IEC 61850-7-4:2007B |
| XCBR_BASIC      | (XCBR)     | Circuit Breaker (w.r.t Mandatory Attributes Only)                                  | IEC 61850-7-4:2007B |
| XSWI_BASIC      | (XSWI)     | Circuit Switch (w.r.t Switch Status and Control)                                   | IEC 61850-7-4:2007B |

#### 1.4.1 LOGICAL NODE: CALH\_ALARM

Description: Logical Node for Group Alarms, Group Warnings and Group Indications

LN Class: CALH

| Attribute | Attr. Type           | Explanation                                                                                                | T | X |
|-----------|----------------------|------------------------------------------------------------------------------------------------------------|---|---|
| NamPlt    | LPL_LN               | Name Plate                                                                                                 |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour                                                                                                  |   |   |
| Health    | ENS_HEALTH           | Health                                                                                                     |   |   |
| GrAlm     | SPS_WD               | If true, a new group alarm trigger status has been activated by one of individual alarm trigger states.    |   |   |
| GrInd     | SPS_WD               | If true, a new group indication has been activated by one of individual indications                        |   |   |
| GrWrn     | SPS_WD               | If true, a new group warning trigger status has been activated by one of individual warning trigger states |   |   |

#### 1.4.2 LOGICAL NODE: CILO\_INTERLOCK

Description: Control Interlocking

LN Class: CILO

| Attribute | Attr. Type           | Explanation           | T | X |
|-----------|----------------------|-----------------------|---|---|
| NamPlt    | LPL_LN               | Name Plate            |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour             |   |   |
| Health    | ENS_HEALTH           | Health                |   |   |
| EnaOpn    | SPS_WD               | Enable OPEN Commands  |   |   |
| EnaCls    | SPS_WD               | Enable CLOSE Commands |   |   |

#### 1.4.3 LOGICAL NODE: CSWI\_PRIV

Description: Switch Controller (with Extended DO 'CtlEna')

LN Class: CSWI

| Attribute | Attr. Type           | Explanation                  | T | X |
|-----------|----------------------|------------------------------|---|---|
| NamPlt    | LPL_LN               | Name Plate                   |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour                    |   |   |
| Health    | ENS_HEALTH           | Health                       |   |   |
| Loc       | SPS_WD               | Local control behaviour      |   |   |
| OpOpn     | ACT_NO_SEG           | Operation "open switch"      | T |   |
| OpCls     | ACT_NO_SEG           | Operation "close switch"     | T |   |
| OpCntRs   | INC_MOD_STD          | Resettable operation counter |   |   |

| Attribute | Attr. Type  | Explanation     | T | X |
|-----------|-------------|-----------------|---|---|
| Pos       | DPC_CTRL    | Switch, general |   |   |
| CtlEna    | SPS_WD_PRIV | Control By      |   | X |

#### 1.4.4 LOGICAL NODE: FCNT\_COUNTER

Description: Counter

LN Class: FCNT

| Attribute | Attr. Type           | Explanation   | T | X |
|-----------|----------------------|---------------|---|---|
| NamPlt    | LPL_LN               | Name Plate    |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour     |   |   |
| Health    | ENS_HEALTH           | Health        |   |   |
| CntVal    | BCR_PRIV             | Counter       |   |   |
| RsCnt     | SPC_CTRL_PRIV        | Counter Reset |   | X |

#### 1.4.5 LOGICAL NODE: GGIO\_ALM\_128

Description: Generic Process I/O (w.r.t 128 Alarm Elements)

LN Class: GGIO

| Attribute | Attr. Type           | Explanation          | T | X |
|-----------|----------------------|----------------------|---|---|
| NamPlt    | LPL_LN               | Name Plate           |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour            |   |   |
| Health    | ENS_HEALTH           | Health               |   |   |
| Alm1      | SPS_D                | General single alarm |   |   |
| Alm2      | SPS_D                | General single alarm |   |   |
| Alm3      | SPS_D                | General single alarm |   |   |
| Alm4      | SPS_D                | General single alarm |   |   |
| Alm5      | SPS_D                | General single alarm |   |   |
| Alm6      | SPS_D                | General single alarm |   |   |
| Alm7      | SPS_D                | General single alarm |   |   |
| Alm8      | SPS_D                | General single alarm |   |   |
| Alm9      | SPS_D                | General single alarm |   |   |
| Alm10     | SPS_D                | General single alarm |   |   |
| Alm11     | SPS_D                | General single alarm |   |   |
| Alm12     | SPS_D                | General single alarm |   |   |
| Alm13     | SPS_D                | General single alarm |   |   |
| Alm14     | SPS_D                | General single alarm |   |   |
| Alm15     | SPS_D                | General single alarm |   |   |
| Alm16     | SPS_D                | General single alarm |   |   |
| Alm17     | SPS_D                | General single alarm |   |   |
| Alm18     | SPS_D                | General single alarm |   |   |
| Alm19     | SPS_D                | General single alarm |   |   |
| Alm20     | SPS_D                | General single alarm |   |   |
| Alm21     | SPS_D                | General single alarm |   |   |
| Alm22     | SPS_D                | General single alarm |   |   |
| Alm23     | SPS_D                | General single alarm |   |   |
| Alm24     | SPS_D                | General single alarm |   |   |
| Alm25     | SPS_D                | General single alarm |   |   |
| Alm26     | SPS_D                | General single alarm |   |   |
| Alm27     | SPS_D                | General single alarm |   |   |
| Alm28     | SPS_D                | General single alarm |   |   |

| Attribute | Attr. Type | Explanation          | T | X |
|-----------|------------|----------------------|---|---|
| Alm29     | SPS_D      | General single alarm |   |   |
| Alm30     | SPS_D      | General single alarm |   |   |
| Alm31     | SPS_D      | General single alarm |   |   |
| Alm32     | SPS_D      | General single alarm |   |   |
| Alm33     | SPS_D      | General single alarm |   |   |
| Alm34     | SPS_D      | General single alarm |   |   |
| Alm35     | SPS_D      | General single alarm |   |   |
| Alm36     | SPS_D      | General single alarm |   |   |
| Alm37     | SPS_D      | General single alarm |   |   |
| Alm38     | SPS_D      | General single alarm |   |   |
| Alm39     | SPS_D      | General single alarm |   |   |
| Alm40     | SPS_D      | General single alarm |   |   |
| Alm41     | SPS_D      | General single alarm |   |   |
| Alm42     | SPS_D      | General single alarm |   |   |
| Alm43     | SPS_D      | General single alarm |   |   |
| Alm44     | SPS_D      | General single alarm |   |   |
| Alm45     | SPS_D      | General single alarm |   |   |
| Alm46     | SPS_D      | General single alarm |   |   |
| Alm47     | SPS_D      | General single alarm |   |   |
| Alm48     | SPS_D      | General single alarm |   |   |
| Alm49     | SPS_D      | General single alarm |   |   |
| Alm50     | SPS_D      | General single alarm |   |   |
| Alm51     | SPS_D      | General single alarm |   |   |
| Alm52     | SPS_D      | General single alarm |   |   |
| Alm53     | SPS_D      | General single alarm |   |   |
| Alm54     | SPS_D      | General single alarm |   |   |
| Alm55     | SPS_D      | General single alarm |   |   |
| Alm56     | SPS_D      | General single alarm |   |   |
| Alm57     | SPS_D      | General single alarm |   |   |
| Alm58     | SPS_D      | General single alarm |   |   |
| Alm59     | SPS_D      | General single alarm |   |   |
| Alm60     | SPS_D      | General single alarm |   |   |
| Alm61     | SPS_D      | General single alarm |   |   |
| Alm62     | SPS_D      | General single alarm |   |   |
| Alm63     | SPS_D      | General single alarm |   |   |
| Alm64     | SPS_D      | General single alarm |   |   |
| Alm65     | SPS_D      | General single alarm |   |   |
| Alm66     | SPS_D      | General single alarm |   |   |
| Alm67     | SPS_D      | General single alarm |   |   |
| Alm68     | SPS_D      | General single alarm |   |   |
| Alm69     | SPS_D      | General single alarm |   |   |
| Alm70     | SPS_D      | General single alarm |   |   |
| Alm71     | SPS_D      | General single alarm |   |   |
| Alm72     | SPS_D      | General single alarm |   |   |
| Alm73     | SPS_D      | General single alarm |   |   |
| Alm74     | SPS_D      | General single alarm |   |   |
| Alm75     | SPS_D      | General single alarm |   |   |
| Alm76     | SPS_D      | General single alarm |   |   |
| Alm77     | SPS_D      | General single alarm |   |   |
| Alm78     | SPS_D      | General single alarm |   |   |
| Alm79     | SPS_D      | General single alarm |   |   |

| Attribute | Attr. Type | Explanation          | T | X |
|-----------|------------|----------------------|---|---|
| Alm80     | SPS_D      | General single alarm |   |   |
| Alm81     | SPS_D      | General single alarm |   |   |
| Alm82     | SPS_D      | General single alarm |   |   |
| Alm83     | SPS_D      | General single alarm |   |   |
| Alm84     | SPS_D      | General single alarm |   |   |
| Alm85     | SPS_D      | General single alarm |   |   |
| Alm86     | SPS_D      | General single alarm |   |   |
| Alm87     | SPS_D      | General single alarm |   |   |
| Alm88     | SPS_D      | General single alarm |   |   |
| Alm89     | SPS_D      | General single alarm |   |   |
| Alm90     | SPS_D      | General single alarm |   |   |
| Alm91     | SPS_D      | General single alarm |   |   |
| Alm92     | SPS_D      | General single alarm |   |   |
| Alm93     | SPS_D      | General single alarm |   |   |
| Alm94     | SPS_D      | General single alarm |   |   |
| Alm95     | SPS_D      | General single alarm |   |   |
| Alm96     | SPS_D      | General single alarm |   |   |
| Alm97     | SPS_D      | General single alarm |   |   |
| Alm98     | SPS_D      | General single alarm |   |   |
| Alm99     | SPS_D      | General single alarm |   |   |
| Alm100    | SPS_D      | General single alarm |   |   |
| Alm101    | SPS_D      | General single alarm |   |   |
| Alm102    | SPS_D      | General single alarm |   |   |
| Alm103    | SPS_D      | General single alarm |   |   |
| Alm104    | SPS_D      | General single alarm |   |   |
| Alm105    | SPS_D      | General single alarm |   |   |
| Alm106    | SPS_D      | General single alarm |   |   |
| Alm107    | SPS_D      | General single alarm |   |   |
| Alm108    | SPS_D      | General single alarm |   |   |
| Alm109    | SPS_D      | General single alarm |   |   |
| Alm110    | SPS_D      | General single alarm |   |   |
| Alm111    | SPS_D      | General single alarm |   |   |
| Alm112    | SPS_D      | General single alarm |   |   |
| Alm113    | SPS_D      | General single alarm |   |   |
| Alm114    | SPS_D      | General single alarm |   |   |
| Alm115    | SPS_D      | General single alarm |   |   |
| Alm116    | SPS_D      | General single alarm |   |   |
| Alm117    | SPS_D      | General single alarm |   |   |
| Alm118    | SPS_D      | General single alarm |   |   |
| Alm119    | SPS_D      | General single alarm |   |   |
| Alm120    | SPS_D      | General single alarm |   |   |
| Alm121    | SPS_D      | General single alarm |   |   |
| Alm122    | SPS_D      | General single alarm |   |   |
| Alm123    | SPS_D      | General single alarm |   |   |
| Alm124    | SPS_D      | General single alarm |   |   |
| Alm125    | SPS_D      | General single alarm |   |   |
| Alm126    | SPS_D      | General single alarm |   |   |
| Alm127    | SPS_D      | General single alarm |   |   |
| Alm128    | SPS_D      | General single alarm |   |   |

#### 1.4.6 LOGICAL NODE: GGIO\_IND\_10

Description: Generic Process I/O (w.r.t 10 Indication Elements)

LN Class: GGIO

| Attribute | Attr. Type           | Explanation        | T | X |
|-----------|----------------------|--------------------|---|---|
| NamPlt    | LPL_LN               | Name Plate         |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour          |   |   |
| Health    | ENS_HEALTH           | Health             |   |   |
| Ind1      | SPS_D                | General Indication |   |   |
| Ind2      | SPS_D                | General Indication |   |   |
| Ind3      | SPS_D                | General Indication |   |   |
| Ind4      | SPS_D                | General Indication |   |   |
| Ind5      | SPS_D                | General Indication |   |   |
| Ind6      | SPS_D                | General Indication |   |   |
| Ind7      | SPS_D                | General Indication |   |   |
| Ind8      | SPS_D                | General Indication |   |   |
| Ind9      | SPS_D                | General Indication |   |   |
| Ind10     | SPS_D                | General Indication |   |   |

#### 1.4.7 LOGICAL NODE: GGIO\_IND\_128

Description: Generic Process I/O (w.r.t 128 indications)

LN Class: GGIO

| Attribute | Attr. Type           | Explanation        | T | X |
|-----------|----------------------|--------------------|---|---|
| NamPlt    | LPL_LN               | Name Plate         |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour          |   |   |
| Health    | ENS_HEALTH           | Health             |   |   |
| Ind1      | SPS_D                | General Indication |   |   |
| Ind2      | SPS_D                | General Indication |   |   |
| Ind3      | SPS_D                | General Indication |   |   |
| Ind4      | SPS_D                | General Indication |   |   |
| Ind5      | SPS_D                | General Indication |   |   |
| Ind6      | SPS_D                | General Indication |   |   |
| Ind7      | SPS_D                | General Indication |   |   |
| Ind8      | SPS_D                | General Indication |   |   |
| Ind9      | SPS_D                | General Indication |   |   |
| Ind10     | SPS_D                | General Indication |   |   |
| Ind11     | SPS_D                | General Indication |   |   |
| Ind12     | SPS_D                | General Indication |   |   |
| Ind13     | SPS_D                | General Indication |   |   |
| Ind14     | SPS_D                | General Indication |   |   |
| Ind15     | SPS_D                | General Indication |   |   |
| Ind16     | SPS_D                | General Indication |   |   |
| Ind17     | SPS_D                | General Indication |   |   |
| Ind18     | SPS_D                | General Indication |   |   |
| Ind19     | SPS_D                | General Indication |   |   |
| Ind20     | SPS_D                | General Indication |   |   |
| Ind21     | SPS_D                | General Indication |   |   |
| Ind22     | SPS_D                | General Indication |   |   |
| Ind23     | SPS_D                | General Indication |   |   |
| Ind24     | SPS_D                | General Indication |   |   |

| Attribute | Attr. Type | Explanation        | T | X |
|-----------|------------|--------------------|---|---|
| Ind25     | SPS_D      | General Indication |   |   |
| Ind26     | SPS_D      | General Indication |   |   |
| Ind27     | SPS_D      | General Indication |   |   |
| Ind28     | SPS_D      | General Indication |   |   |
| Ind29     | SPS_D      | General Indication |   |   |
| Ind30     | SPS_D      | General Indication |   |   |
| Ind31     | SPS_D      | General Indication |   |   |
| Ind32     | SPS_D      | General Indication |   |   |
| Ind33     | SPS_D      | General Indication |   |   |
| Ind34     | SPS_D      | General Indication |   |   |
| Ind35     | SPS_D      | General Indication |   |   |
| Ind36     | SPS_D      | General Indication |   |   |
| Ind37     | SPS_D      | General Indication |   |   |
| Ind38     | SPS_D      | General Indication |   |   |
| Ind39     | SPS_D      | General Indication |   |   |
| Ind40     | SPS_D      | General Indication |   |   |
| Ind41     | SPS_D      | General Indication |   |   |
| Ind42     | SPS_D      | General Indication |   |   |
| Ind43     | SPS_D      | General Indication |   |   |
| Ind44     | SPS_D      | General Indication |   |   |
| Ind45     | SPS_D      | General Indication |   |   |
| Ind46     | SPS_D      | General Indication |   |   |
| Ind47     | SPS_D      | General Indication |   |   |
| Ind48     | SPS_D      | General Indication |   |   |
| Ind49     | SPS_D      | General Indication |   |   |
| Ind50     | SPS_D      | General Indication |   |   |
| Ind51     | SPS_D      | General Indication |   |   |
| Ind52     | SPS_D      | General Indication |   |   |
| Ind53     | SPS_D      | General Indication |   |   |
| Ind54     | SPS_D      | General Indication |   |   |
| Ind55     | SPS_D      | General Indication |   |   |
| Ind56     | SPS_D      | General Indication |   |   |
| Ind57     | SPS_D      | General Indication |   |   |
| Ind58     | SPS_D      | General Indication |   |   |
| Ind59     | SPS_D      | General Indication |   |   |
| Ind60     | SPS_D      | General Indication |   |   |
| Ind61     | SPS_D      | General Indication |   |   |
| Ind62     | SPS_D      | General Indication |   |   |
| Ind63     | SPS_D      | General Indication |   |   |
| Ind64     | SPS_D      | General Indication |   |   |
| Ind65     | SPS_D      | General Indication |   |   |
| Ind66     | SPS_D      | General Indication |   |   |
| Ind67     | SPS_D      | General Indication |   |   |
| Ind68     | SPS_D      | General Indication |   |   |
| Ind69     | SPS_D      | General Indication |   |   |
| Ind70     | SPS_D      | General Indication |   |   |
| Ind71     | SPS_D      | General Indication |   |   |
| Ind72     | SPS_D      | General Indication |   |   |
| Ind73     | SPS_D      | General Indication |   |   |
| Ind74     | SPS_D      | General Indication |   |   |
| Ind75     | SPS_D      | General Indication |   |   |

| Attribute | Attr. Type | Explanation        | T | X |
|-----------|------------|--------------------|---|---|
| Ind76     | SPS_D      | General Indication |   |   |
| Ind77     | SPS_D      | General Indication |   |   |
| Ind78     | SPS_D      | General Indication |   |   |
| Ind79     | SPS_D      | General Indication |   |   |
| Ind80     | SPS_D      | General Indication |   |   |
| Ind81     | SPS_D      | General Indication |   |   |
| Ind82     | SPS_D      | General Indication |   |   |
| Ind83     | SPS_D      | General Indication |   |   |
| Ind84     | SPS_D      | General Indication |   |   |
| Ind85     | SPS_D      | General Indication |   |   |
| Ind86     | SPS_D      | General Indication |   |   |
| Ind87     | SPS_D      | General Indication |   |   |
| Ind88     | SPS_D      | General Indication |   |   |
| Ind89     | SPS_D      | General Indication |   |   |
| Ind90     | SPS_D      | General Indication |   |   |
| Ind91     | SPS_D      | General Indication |   |   |
| Ind92     | SPS_D      | General Indication |   |   |
| Ind93     | SPS_D      | General Indication |   |   |
| Ind94     | SPS_D      | General Indication |   |   |
| Ind95     | SPS_D      | General Indication |   |   |
| Ind96     | SPS_D      | General Indication |   |   |
| Ind97     | SPS_D      | General Indication |   |   |
| Ind98     | SPS_D      | General Indication |   |   |
| Ind99     | SPS_D      | General Indication |   |   |
| Ind100    | SPS_D      | General Indication |   |   |
| Ind101    | SPS_D      | General Indication |   |   |
| Ind102    | SPS_D      | General Indication |   |   |
| Ind103    | SPS_D      | General Indication |   |   |
| Ind104    | SPS_D      | General Indication |   |   |
| Ind105    | SPS_D      | General Indication |   |   |
| Ind106    | SPS_D      | General Indication |   |   |
| Ind107    | SPS_D      | General Indication |   |   |
| Ind108    | SPS_D      | General Indication |   |   |
| Ind109    | SPS_D      | General Indication |   |   |
| Ind110    | SPS_D      | General Indication |   |   |
| Ind111    | SPS_D      | General Indication |   |   |
| Ind112    | SPS_D      | General Indication |   |   |
| Ind113    | SPS_D      | General Indication |   |   |
| Ind114    | SPS_D      | General Indication |   |   |
| Ind115    | SPS_D      | General Indication |   |   |
| Ind116    | SPS_D      | General Indication |   |   |
| Ind117    | SPS_D      | General Indication |   |   |
| Ind118    | SPS_D      | General Indication |   |   |
| Ind119    | SPS_D      | General Indication |   |   |
| Ind120    | SPS_D      | General Indication |   |   |
| Ind121    | SPS_D      | General Indication |   |   |
| Ind122    | SPS_D      | General Indication |   |   |
| Ind123    | SPS_D      | General Indication |   |   |
| Ind124    | SPS_D      | General Indication |   |   |
| Ind125    | SPS_D      | General Indication |   |   |
| Ind126    | SPS_D      | General Indication |   |   |

| Attribute | Attr. Type | Explanation        | T | X |
|-----------|------------|--------------------|---|---|
| Ind127    | SPS_D      | General Indication |   |   |
| Ind128    | SPS_D      | General Indication |   |   |

#### 1.4.8 LOGICAL NODE: GGIO\_IND\_23

Description: Generic Process I/O (w.r.t 23 Indication Elements)

LN Class: GGIO

| Attribute | Attr. Type           | Explanation                       | T | X |
|-----------|----------------------|-----------------------------------|---|---|
| NamPlt    | LPL_LN               | Name Plate                        |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour                         |   |   |
| Health    | ENS_HEALTH           | Health                            |   |   |
| Ind1      | SPS_D                | General indication (binary input) |   |   |
| Ind2      | SPS_D                | General indication (binary input) |   |   |
| Ind3      | SPS_D                | General indication (binary input) |   |   |
| Ind4      | SPS_D                | General indication (binary input) |   |   |
| Ind5      | SPS_D                | General indication (binary input) |   |   |
| Ind6      | SPS_D                | General indication (binary input) |   |   |
| Ind7      | SPS_D                | General indication (binary input) |   |   |
| Ind8      | SPS_D                | General indication (binary input) |   |   |
| Ind9      | SPS_D                | General indication (binary input) |   |   |
| Ind10     | SPS_D                | General indication (binary input) |   |   |
| Ind11     | SPS_D                | General indication (binary input) |   |   |
| Ind12     | SPS_D                | General indication (binary input) |   |   |
| Ind13     | SPS_D                | General indication (binary input) |   |   |
| Ind14     | SPS_D                | General indication (binary input) |   |   |
| Ind15     | SPS_D                | General indication (binary input) |   |   |
| Ind16     | SPS_D                | General indication (binary input) |   |   |
| Ind17     | SPS_D                | General indication (binary input) |   |   |
| Ind18     | SPS_D                | General indication (binary input) |   |   |
| Ind19     | SPS_D                | General indication (binary input) |   |   |
| Ind20     | SPS_D                | General indication (binary input) |   |   |
| Ind21     | SPS_D                | General indication (binary input) |   |   |
| Ind22     | SPS_D                | General indication (binary input) |   |   |
| Ind23     | SPS_D                | General indication (binary input) |   |   |

#### 1.4.9 LOGICAL NODE: GGIO\_IND\_24

Description: Generic Process I/O (w.r.t 24 Indication Elements)

LN Class: GGIO

| Attribute | Attr. Type           | Explanation        | T | X |
|-----------|----------------------|--------------------|---|---|
| NamPlt    | LPL_LN               | Name Plate         |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour          |   |   |
| Health    | ENS_HEALTH           | Health             |   |   |
| Ind1      | SPS_D                | General Indication |   |   |
| Ind2      | SPS_D                | General Indication |   |   |
| Ind3      | SPS_D                | General Indication |   |   |
| Ind4      | SPS_D                | General Indication |   |   |
| Ind5      | SPS_D                | General Indication |   |   |
| Ind6      | SPS_D                | General Indication |   |   |
| Ind7      | SPS_D                | General Indication |   |   |

| Attribute | Attr. Type | Explanation        | T | X |
|-----------|------------|--------------------|---|---|
| Ind8      | SPS_D      | General Indication |   |   |
| Ind9      | SPS_D      | General Indication |   |   |
| Ind10     | SPS_D      | General Indication |   |   |
| Ind11     | SPS_D      | General Indication |   |   |
| Ind12     | SPS_D      | General Indication |   |   |
| Ind13     | SPS_D      | General Indication |   |   |
| Ind14     | SPS_D      | General Indication |   |   |
| Ind15     | SPS_D      | General Indication |   |   |
| Ind16     | SPS_D      | General Indication |   |   |
| Ind17     | SPS_D      | General Indication |   |   |
| Ind18     | SPS_D      | General Indication |   |   |
| Ind19     | SPS_D      | General Indication |   |   |
| Ind20     | SPS_D      | General Indication |   |   |
| Ind21     | SPS_D      | General Indication |   |   |
| Ind22     | SPS_D      | General Indication |   |   |
| Ind23     | SPS_D      | General Indication |   |   |
| Ind24     | SPS_D      | General Indication |   |   |

#### 1.4.10 LOGICAL NODE: GGIO\_IND\_32\_CTRL

Description: Generic Process I/O (w.r.t 32 Indications Ctrl i/p)

LN Class: GGIO

| Attribute | Attr. Type           | Explanation                             | T | X |
|-----------|----------------------|-----------------------------------------|---|---|
| NamPlt    | LPL_LN               | Name Plate                              |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour                               |   |   |
| Health    | ENS_HEALTH           | Health                                  |   |   |
| SPCSO1    | SPC_CONTROL          | Single point controllable status output |   |   |
| SPCSO2    | SPC_CONTROL          | Single point controllable status output |   |   |
| SPCSO3    | SPC_CONTROL          | Single point controllable status output |   |   |
| SPCSO4    | SPC_CONTROL          | Single point controllable status output |   |   |
| SPCSO5    | SPC_CONTROL          | Single point controllable status output |   |   |
| SPCSO6    | SPC_CONTROL          | Single point controllable status output |   |   |
| SPCSO7    | SPC_CONTROL          | Single point controllable status output |   |   |
| SPCSO8    | SPC_CONTROL          | Single point controllable status output |   |   |
| SPCSO9    | SPC_CONTROL          | Single point controllable status output |   |   |
| SPCSO10   | SPC_CONTROL          | Single point controllable status output |   |   |
| SPCSO11   | SPC_CONTROL          | Single point controllable status output |   |   |
| SPCSO12   | SPC_CONTROL          | Single point controllable status output |   |   |
| SPCSO13   | SPC_CONTROL          | Single point controllable status output |   |   |
| SPCSO14   | SPC_CONTROL          | Single point controllable status output |   |   |
| SPCSO15   | SPC_CONTROL          | Single point controllable status output |   |   |
| SPCSO16   | SPC_CONTROL          | Single point controllable status output |   |   |
| SPCSO17   | SPC_CONTROL          | Single point controllable status output |   |   |
| SPCSO18   | SPC_CONTROL          | Single point controllable status output |   |   |
| SPCSO19   | SPC_CONTROL          | Single point controllable status output |   |   |
| SPCSO20   | SPC_CONTROL          | Single point controllable status output |   |   |
| SPCSO21   | SPC_CONTROL          | Single point controllable status output |   |   |
| SPCSO22   | SPC_CONTROL          | Single point controllable status output |   |   |
| SPCSO23   | SPC_CONTROL          | Single point controllable status output |   |   |
| SPCSO24   | SPC_CONTROL          | Single point controllable status output |   |   |

| Attribute | Attr. Type  | Explanation                             | T | X |
|-----------|-------------|-----------------------------------------|---|---|
| SPCSO25   | SPC_CONTROL | Single point controllable status output |   |   |
| SPCSO26   | SPC_CONTROL | Single point controllable status output |   |   |
| SPCSO27   | SPC_CONTROL | Single point controllable status output |   |   |
| SPCSO28   | SPC_CONTROL | Single point controllable status output |   |   |
| SPCSO29   | SPC_CONTROL | Single point controllable status output |   |   |
| SPCSO30   | SPC_CONTROL | Single point controllable status output |   |   |
| SPCSO31   | SPC_CONTROL | Single point controllable status output |   |   |
| SPCSO32   | SPC_CONTROL | Single point controllable status output |   |   |

#### 1.4.11 LOGICAL NODE: GGIO\_IND\_40

Description: Generic Process I/O (w.r.t 40 Indication Elements)

LN Class: GGIO

| Attribute | Attr. Type           | Explanation        | T | X |
|-----------|----------------------|--------------------|---|---|
| NamPlt    | LPL_LN               | Name Plate         |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour          |   |   |
| Health    | ENS_HEALTH           | Health             |   |   |
| Ind1      | SPS_D                | General Indication |   |   |
| Ind2      | SPS_D                | General Indication |   |   |
| Ind3      | SPS_D                | General Indication |   |   |
| Ind4      | SPS_D                | General Indication |   |   |
| Ind5      | SPS_D                | General Indication |   |   |
| Ind6      | SPS_D                | General Indication |   |   |
| Ind7      | SPS_D                | General Indication |   |   |
| Ind8      | SPS_D                | General Indication |   |   |
| Ind9      | SPS_D                | General Indication |   |   |
| Ind10     | SPS_D                | General Indication |   |   |
| Ind11     | SPS_D                | General Indication |   |   |
| Ind12     | SPS_D                | General Indication |   |   |
| Ind13     | SPS_D                | General Indication |   |   |
| Ind14     | SPS_D                | General Indication |   |   |
| Ind15     | SPS_D                | General Indication |   |   |
| Ind16     | SPS_D                | General Indication |   |   |
| Ind17     | SPS_D                | General Indication |   |   |
| Ind18     | SPS_D                | General Indication |   |   |
| Ind19     | SPS_D                | General Indication |   |   |
| Ind20     | SPS_D                | General Indication |   |   |
| Ind21     | SPS_D                | General Indication |   |   |
| Ind22     | SPS_D                | General Indication |   |   |
| Ind23     | SPS_D                | General Indication |   |   |
| Ind24     | SPS_D                | General Indication |   |   |
| Ind25     | SPS_D                | General Indication |   |   |
| Ind26     | SPS_D                | General Indication |   |   |
| Ind27     | SPS_D                | General Indication |   |   |
| Ind28     | SPS_D                | General Indication |   |   |
| Ind29     | SPS_D                | General Indication |   |   |
| Ind30     | SPS_D                | General Indication |   |   |
| Ind31     | SPS_D                | General Indication |   |   |
| Ind32     | SPS_D                | General Indication |   |   |
| Ind33     | SPS_D                | General Indication |   |   |

| Attribute | Attr. Type | Explanation        | T | X |
|-----------|------------|--------------------|---|---|
| Ind34     | SPS_D      | General Indication |   |   |
| Ind35     | SPS_D      | General Indication |   |   |
| Ind36     | SPS_D      | General Indication |   |   |
| Ind37     | SPS_D      | General Indication |   |   |
| Ind38     | SPS_D      | General Indication |   |   |
| Ind39     | SPS_D      | General Indication |   |   |
| Ind40     | SPS_D      | General Indication |   |   |

#### 1.4.12 LOGICAL NODE: GGIO\_IND\_43

Description: Generic Process I/O (w.r.t 43 Indication Elements)

LN Class: GGIO

| Attribute | Attr. Type           | Explanation        | T | X |
|-----------|----------------------|--------------------|---|---|
| NamPlt    | LPL_LN               | Name Plate         |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour          |   |   |
| Health    | ENS_HEALTH           | Health             |   |   |
| Ind1      | SPS_D                | General Indication |   |   |
| Ind2      | SPS_D                | General Indication |   |   |
| Ind3      | SPS_D                | General Indication |   |   |
| Ind4      | SPS_D                | General Indication |   |   |
| Ind5      | SPS_D                | General Indication |   |   |
| Ind6      | SPS_D                | General Indication |   |   |
| Ind7      | SPS_D                | General Indication |   |   |
| Ind8      | SPS_D                | General Indication |   |   |
| Ind9      | SPS_D                | General Indication |   |   |
| Ind10     | SPS_D                | General Indication |   |   |
| Ind11     | SPS_D                | General Indication |   |   |
| Ind12     | SPS_D                | General Indication |   |   |
| Ind13     | SPS_D                | General Indication |   |   |
| Ind14     | SPS_D                | General Indication |   |   |
| Ind15     | SPS_D                | General Indication |   |   |
| Ind16     | SPS_D                | General Indication |   |   |
| Ind17     | SPS_D                | General Indication |   |   |
| Ind18     | SPS_D                | General Indication |   |   |
| Ind19     | SPS_D                | General Indication |   |   |
| Ind20     | SPS_D                | General Indication |   |   |
| Ind21     | SPS_D                | General Indication |   |   |
| Ind22     | SPS_D                | General Indication |   |   |
| Ind23     | SPS_D                | General Indication |   |   |
| Ind24     | SPS_D                | General Indication |   |   |
| Ind25     | SPS_D                | General Indication |   |   |
| Ind26     | SPS_D                | General Indication |   |   |
| Ind27     | SPS_D                | General Indication |   |   |
| Ind28     | SPS_D                | General Indication |   |   |
| Ind29     | SPS_D                | General Indication |   |   |
| Ind30     | SPS_D                | General Indication |   |   |
| Ind31     | SPS_D                | General Indication |   |   |
| Ind32     | SPS_D                | General Indication |   |   |
| Ind33     | SPS_D                | General Indication |   |   |
| Ind34     | SPS_D                | General Indication |   |   |

| Attribute | Attr. Type | Explanation        | T | X |
|-----------|------------|--------------------|---|---|
| Ind35     | SPS_D      | General Indication |   |   |
| Ind36     | SPS_D      | General Indication |   |   |
| Ind37     | SPS_D      | General Indication |   |   |
| Ind38     | SPS_D      | General Indication |   |   |
| Ind39     | SPS_D      | General Indication |   |   |
| Ind40     | SPS_D      | General Indication |   |   |
| Ind41     | SPS_D      | General Indication |   |   |
| Ind42     | SPS_D      | General Indication |   |   |
| Ind43     | SPS_D      | General Indication |   |   |

#### 1.4.13 LOGICAL NODE: GGIO\_IND\_DPS\_8

Description: Generic Process I/O (w.r.t 8 Dual Point Status Indication Elements)

LN Class: GGIO

| Attribute | Attr. Type           | Explanation         | T | X |
|-----------|----------------------|---------------------|---|---|
| NamPlt    | LPL_LN               | Name Plate          |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour           |   |   |
| Health    | ENS_HEALTH           | Health              |   |   |
| DPCSO1    | DPC_STATUS_D         | Double Point Status |   |   |
| DPCSO2    | DPC_STATUS_D         | Double Point Status |   |   |
| DPCSO3    | DPC_STATUS_D         | Double Point Status |   |   |
| DPCSO4    | DPC_STATUS_D         | Double Point Status |   |   |
| DPCSO5    | DPC_STATUS_D         | Double Point Status |   |   |
| DPCSO6    | DPC_STATUS_D         | Double Point Status |   |   |
| DPCSO7    | DPC_STATUS_D         | Double Point Status |   |   |
| DPCSO8    | DPC_STATUS_D         | Double Point Status |   |   |

#### 1.4.14 LOGICAL NODE: GGIO\_USER\_ALM\_32

Description: Generic Process I/O

LN Class: GGIO

| Attribute | Attr. Type           | Explanation          | T | X |
|-----------|----------------------|----------------------|---|---|
| NamPlt    | LPL_LN               | Name Plate           |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour            |   |   |
| Health    | ENS_HEALTH           | Health               |   |   |
| Alm1      | SPS_D                | General single alarm |   |   |
| Alm2      | SPS_D                | General single alarm |   |   |
| Alm3      | SPS_D                | General single alarm |   |   |
| Alm4      | SPS_D                | General single alarm |   |   |
| Alm5      | SPS_D                | General single alarm |   |   |
| Alm6      | SPS_D                | General single alarm |   |   |
| Alm7      | SPS_D                | General single alarm |   |   |
| Alm8      | SPS_D                | General single alarm |   |   |
| Alm9      | SPS_D                | General single alarm |   |   |
| Alm10     | SPS_D                | General single alarm |   |   |
| Alm11     | SPS_D                | General single alarm |   |   |
| Alm12     | SPS_D                | General single alarm |   |   |
| Alm13     | SPS_D                | General single alarm |   |   |
| Alm14     | SPS_D                | General single alarm |   |   |
| Alm15     | SPS_D                | General single alarm |   |   |

| Attribute | Attr. Type | Explanation          | T | X |
|-----------|------------|----------------------|---|---|
| Alm16     | SPS_D      | General single alarm |   |   |
| Alm17     | SPS_D      | General single alarm |   |   |
| Alm18     | SPS_D      | General single alarm |   |   |
| Alm19     | SPS_D      | General single alarm |   |   |
| Alm20     | SPS_D      | General single alarm |   |   |
| Alm21     | SPS_D      | General single alarm |   |   |
| Alm22     | SPS_D      | General single alarm |   |   |
| Alm23     | SPS_D      | General single alarm |   |   |
| Alm24     | SPS_D      | General single alarm |   |   |
| Alm25     | SPS_D      | General single alarm |   |   |
| Alm26     | SPS_D      | General single alarm |   |   |
| Alm27     | SPS_D      | General single alarm |   |   |
| Alm28     | SPS_D      | General single alarm |   |   |
| Alm29     | SPS_D      | General single alarm |   |   |
| Alm30     | SPS_D      | General single alarm |   |   |
| Alm31     | SPS_D      | General single alarm |   |   |
| Alm32     | SPS_D      | General single alarm |   |   |

#### 1.4.15 LOGICAL NODE: ITPC\_SYSTEM

Description: Teleprotection Communication Interfaces

LN Class: ITPC

| Attribute | Attr. Type           | Explanation                                                      | T | X |
|-----------|----------------------|------------------------------------------------------------------|---|---|
| NamPlt    | LPL_LN               | Name Plate                                                       |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour                                                        |   |   |
| Health    | ENS_HEALTH           | Health                                                           |   |   |
| EENam     | DPL_PRIV             | External equipment nameplate                                     |   |   |
| EEHealth  | ENS_HEALTH           | External equipment health                                        |   |   |
| LosSig    | SPS_WD               | Alarm situation: No signal received, indicates a channel problem |   |   |

#### 1.4.16 LOGICAL NODE: LCCH\_SYSTEM

Description: Physical Communication Channel Supervision

LN Class: LCCH

| Attribute | Attr. Type           | Explanation                                                                                                                                                                               | T | X |
|-----------|----------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---|---|
| NamPlt    | LPL_LN               | Name Plate                                                                                                                                                                                |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour                                                                                                                                                                                 |   |   |
| Health    | ENS_HEALTH           | Health                                                                                                                                                                                    |   |   |
| ChLiv     | SPS_D                | If true, channel is receiving telegrams within a specified time interval 'ChLivTms'. In case of a redundancy protocol this refers to channel A.                                           |   |   |
| RedChLiv  | SPS_D                | If true, redundant channel is receiving telegrams within a specified time interval 'ChLivTms' or determined by other criteria. In case of a redundancy protocol this refers to channel B. |   |   |

**1.4.17 LOGICAL NODE: LCCH\_SYSTEM\_ENG\_PORT**

Description: Physical Communication Channel Supervision

LN Class: LCCH

| Attribute | Attr. Type           | Explanation                                                                                                                                     | T | X |
|-----------|----------------------|-------------------------------------------------------------------------------------------------------------------------------------------------|---|---|
| NamPlt    | LPL_LN               | Name Plate                                                                                                                                      |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour                                                                                                                                       |   |   |
| Health    | ENS_HEALTH           | Health                                                                                                                                          |   |   |
| ChLiv     | SPS_D                | If true, channel is receiving telegrams within a specified time interval 'ChLivTms'. In case of a redundancy protocol this refers to channel A. |   |   |

**1.4.18 LOGICAL NODE: LGOS\_SYSTEM**

Description: Monitoring of GOOSE Messages

LN Class: LGOS

| Attribute    | Attr. Type           | Explanation                                                                                                                        | T | X |
|--------------|----------------------|------------------------------------------------------------------------------------------------------------------------------------|---|---|
| NamPlt       | LPL_LN               | Name Plate                                                                                                                         |   |   |
| Beh          | ENS_BEH_THREE_STATUS | Behaviour                                                                                                                          |   |   |
| Health       | ENS_HEALTH           | Health                                                                                                                             |   |   |
| St           | SPS_WD               | Status of the subscription (True = active, False=not active)                                                                       |   |   |
| SimSt        | SPS_WD               | Status showing that really Sim messages are received and accepted                                                                  |   |   |
| ConfRevNum   | INS_BASIC_PRIV       | Expected configuration revision number                                                                                             |   |   |
| RxConfRevNum | INS_BASIC_PRIV       | Configuration revision number of the received messages. If no telegram is received, the attribute 'q.validity' is set to 'invalid' |   |   |
| GoCBRef      | ORG_SRC_REF          | Reference to the subscribed GOOSE control block                                                                                    |   |   |
| OoSeqGo      | SPS_WD_PRIV          | Out of order GOOSE indication                                                                                                      |   | X |

**1.4.19 LOGICAL NODE: LLN0\_STANDARD**

Description: General Logical Node 0

LN Class: LLN0

| Attribute | Attr. Type           | Explanation                                | T | X |
|-----------|----------------------|--------------------------------------------|---|---|
| NamPlt    | LPL_LLNO             | Name Plate                                 |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour                                  |   |   |
| Health    | ENS_HEALTH           | Health                                     |   |   |
| GrRef     | ORG_SRC_REF          | Reference to a higher level logical device |   |   |

**1.4.20 LOGICAL NODE: LLN0\_STANDARD\_CBFAIL**

Description: Logical Node 0 in CBFail

LN Class: LLN0

| Attribute | Attr. Type          | Explanation                                | T | X |
|-----------|---------------------|--------------------------------------------|---|---|
| NamPlt    | LPL_LLNO            | Name Plate                                 |   |   |
| Beh       | ENS_BEH_FOUR_STATUS | Behaviour                                  |   |   |
| Health    | ENS_HEALTH          | Health                                     |   |   |
| GrRef     | ORG_SRC_REF         | Reference to a higher level logical device |   |   |

#### 1.4.21 LOGICAL NODE: LLN0\_STANDARD\_MEA

Description: Measurements Logical Node 0

LN Class: LLN0

| Attribute | Attr. Type           | Explanation                                | T | X |
|-----------|----------------------|--------------------------------------------|---|---|
| NamPlt    | LPL_LLNO_MEA         | Name Plate                                 |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour                                  |   |   |
| Health    | ENS_HEALTH           | Health                                     |   |   |
| GrRef     | ORG_SRC_REF          | Reference to a higher level logical device |   |   |

#### 1.4.22 LOGICAL NODE: LLN0\_STANDARD\_WITH\_CTRLMOD

Description: Logical Node 0

LN Class: LLN0

| Attribute | Attr. Type          | Explanation                                | T | X |
|-----------|---------------------|--------------------------------------------|---|---|
| NamPlt    | LPL_LLNO            | Name Plate                                 |   |   |
| Beh       | ENS_BEH_FOUR_STATUS | Behaviour                                  |   |   |
| Health    | ENS_HEALTH          | Health                                     |   |   |
| Mod       | ENC_CTRL_LD_MOD_2   | Mode                                       |   |   |
| GrRef     | ORG_SRC_REF         | Reference to a higher level logical device |   |   |

#### 1.4.23 LOGICAL NODE: LLN0\_SYSTEM

Description: System Logical Node 0

LN Class: LLN0

| Attribute | Attr. Type           | Explanation                                                 | T | X |
|-----------|----------------------|-------------------------------------------------------------|---|---|
| NamPlt    | LPL_LLNO             | Name Plate                                                  |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour                                                   |   |   |
| Health    | ENS_HEALTH           | Health                                                      |   |   |
| Mod       | ENC_CTRL_LD_MOD      | Mode                                                        |   |   |
| LocKey    | SPS_WD               | Local operation for complete logical device                 |   |   |
| Loc       | SPS_WD               | Local control behaviour                                     |   |   |
| LocSta    | SPC_CONTROL          | Switching authority at station level                        |   |   |
| LEDRs     | SPC_CONTROL          | LED reset                                                   | T |   |
| MltLev    | SPG_WD               | Select mode of authority for local control                  |   |   |
| OrdRun    | SPS_WD_PRIV          | Indicate IED is operating a Control Object                  |   | X |
| SyncSt    | SPS_WD_PRIV          | Indicate time synchronisation in the IED is active/inactive |   | X |
| MltLevEna | SPS_WD_PRIV          | Multi-level enabled                                         |   | X |

#### 1.4.24 LOGICAL NODE: LPHD\_STANDARD

Description: Px40 Physical Device Information

LN Class: LPHD

| Attribute | Attr. Type   | Explanation                     | T | X |
|-----------|--------------|---------------------------------|---|---|
| PhyNam    | DPL_STANDARD | Physical device name plate      |   |   |
| PhyHealth | ENS_HEALTH   | Physical device health          |   |   |
| Proxy     | SPS_D        | Indicates if this LN is a proxy |   |   |
| PwrUp     | SPS_D        | Power up detected               |   |   |

**1.4.25 LOGICAL NODE: LPHD\_SYSTEM**

Description: Px40 Physical Device Information (Used for Logical Device System Only)

LN Class: LPHD

| Attribute | Attr. Type   | Explanation                             | T | X |
|-----------|--------------|-----------------------------------------|---|---|
| PhyNam    | DPL_STANDARD | Physical device name plate              |   |   |
| PhyHealth | ENS_HEALTH   | Physical device health                  |   |   |
| Proxy     | SPS_D        | Indicates if this LN is a proxy         |   |   |
| PwrUp     | SPS_D        | Power up detected                       |   |   |
| Sim       | SPC_CONTROL  | Receive simulated GOOSE or simulated SV |   |   |

**1.4.26 LOGICAL NODE: LSVS\_SYSTEM**

Description: Sampled Value Subscription

LN Class: LSVS

| Attribute | Attr. Type           | Explanation                                                    | T | X |
|-----------|----------------------|----------------------------------------------------------------|---|---|
| NamPlt    | LPL_LN               | Name Plate                                                     |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour                                                      |   |   |
| Health    | ENS_HEALTH           | Health                                                         |   |   |
| St        | SPS_WD               | Status of the subscription (True = active, False = not active) |   |   |
| SvCRef    | ORG_SRC_REF          | Reference to the subscribed SV control block                   |   |   |

**1.4.27 LOGICAL NODE: LTIM\_SYSTEM**

Description: Time Management

LN Class: LTIM

| Attribute | Attr. Type           | Explanation                                                 | T | X |
|-----------|----------------------|-------------------------------------------------------------|---|---|
| NamPlt    | LPL_LN               | Name Plate                                                  |   |   |
| TmDT      | SPS_WD               | the daylight saving time is in effect now for this location |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour                                                   |   |   |
| Health    | ENS_HEALTH           | Health                                                      |   |   |
| TmOfsTmm  | ING_SET_TM           | Offset of local time from UTC                               |   |   |
| TmUseDT   | SPG_SP               | location is using daylight saving time                      |   |   |
| TmChgDT   | TSG_SP               | Local time of next change to daylight saving time           |   |   |
| TmChgST   | TSG_SP               | Local time of next change to standard time                  |   |   |

**1.4.28 LOGICAL NODE: LTMS\_SYSTEM**

Description: Time Master Supervision

LN Class: LTMS

| Attribute | Attr. Type        | Explanation                                                                                      | T | X |
|-----------|-------------------|--------------------------------------------------------------------------------------------------|---|---|
| NamPlt    | LPL_LN            | Name Plate                                                                                       |   |   |
| TmAcc     | INS_BASIC         | Number of significant bits in the Fraction of Second in the time accuracy part of the time stamp |   |   |
| TmSrc     | VSS_WD            | Current time source                                                                              |   |   |
| TmSrcTyp  | ENS_CLK_SRC_KIND  | Type of the clock source                                                                         |   |   |
| TmSyn     | ENS_CLK_SYNC_KIND | Time synchronized according to IEC 61850-9-2                                                     |   |   |
| TmChSt1   | SPS_WD            | If true, time channel n is receiving time msgs within a specified time interval                  |   |   |

| Attribute | Attr. Type           | Explanation                             | T | X |
|-----------|----------------------|-----------------------------------------|---|---|
| TmSynLkd  | ENS_CLK_SYNC_LK      | Locked status of clock synchronisation. |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour                               |   |   |
| Health    | ENS_HEALTH           | Health                                  |   |   |

#### 1.4.29 LOGICAL NODE: MLFR\_FAULT\_RECORD\_NODIF\_CB2

Description: Measurements of Fault Record without Differential Protection

LN Class: MLFR

| Attribute | Attr. Type               | Explanation          | T | X |
|-----------|--------------------------|----------------------|---|---|
| NamPlt    | LPL_LN_PRIV              | Name Plate           |   |   |
| Beh       | ENS_BEH_THREE_STATUS_DN  | Behaviour            |   |   |
| Health    | ENS_HEALTH_DN            | Health               |   |   |
| AFIt      | WYE_SEG_ANG_NEU_D_PRIV   | Fault current        |   | X |
| AmFIt     | CMV_MAG_ANG_FLOAT        | Fault mutual current |   | X |
| CB1OpTim  | MV_FLOAT_PRIV            | CB1 operate Time     |   | X |
| CB2OpTim  | MV_FLOAT_PRIV            | CB2 operate Time     |   | X |
| FltDur    | MV_FLOAT_PRIV            | Fault duration       |   | X |
| PhVFlt    | WYE_SEG_ANG_NEU_D_PRIV_1 | Fault voltage        |   | X |
| RlyTrTim  | MV_FLOAT_PRIV            | Relay trip time      |   | X |
| V1Rem     | CMV_MAG_ANG_FLOAT        | Remote end V1        |   | X |

#### 1.4.30 LOGICAL NODE: MLFR\_PRE\_FAULT

Description: Measurements of Fault Record

LN Class: MLFR

| Attribute | Attr. Type              | Explanation             | T | X |
|-----------|-------------------------|-------------------------|---|---|
| NamPlt    | LPL_LN_PRIV             | Name Plate              |   |   |
| Beh       | ENS_BEH_THREE_STATUS_DN | Behaviour               |   |   |
| Health    | ENS_HEALTH_DN           | Health                  |   |   |
| Hz        | MV_FLOAT_PRIV           | System frequency        |   | X |
| AmPreFlt  | CMV_MAG_ANG_FLOAT_PRIV  | Prefault mutual current |   | X |
| APreFlt   | WYE_SEG_ANG_RES_D_PRIV  | Prefault current        |   | X |
| PhVPreFlt | WYE_SEG_ANG_RES_D_PRIV  | Prefault voltage        |   | X |

#### 1.4.31 LOGICAL NODE: MMTR\_PRIV

Description: Metering

LN Class: MMTR

| Attribute | Attr. Type           | Explanation                                          | T | X |
|-----------|----------------------|------------------------------------------------------|---|---|
| NamPlt    | LPL_LN               | Name Plate                                           |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour                                            |   |   |
| Health    | ENS_HEALTH           | Health                                               |   |   |
| TotWh     | BCR_PRIV             | Net real energy since last reset                     |   |   |
| TotVArh   | BCR_PRIV             | Net reactive energy since last reset                 |   |   |
| SupWh     | BCR_PRIV             | Real energy supply (Energy flow towards bus bar)     |   |   |
| SupVArh   | BCR_PRIV             | Reactive energy supply (Energy flow towards bus bar) |   |   |
| DmdWh     | BCR_PRIV             | Real energy demand (Energy flow from bus bar)        |   |   |
| DmdVArh   | BCR_PRIV             | Reactive energy demand (Energy flow from bus bar)    |   |   |
| MTRRs     | SPC_CTRL_PRIV        | Reset Energy Meters                                  |   | X |

### 1.4.32 LOGICAL NODE: MMXU\_FOURIER\_CB2\_EXT

Description: Standard Measurements for CB2 (w.r.t Fourier Values Including Df/Dt)

LN Class: MMXU

| Attribute  | Attr. Type            | Explanation                       | T | X |
|------------|-----------------------|-----------------------------------|---|---|
| NamPlt     | LPL_LN                | Name Plate                        |   |   |
| Beh        | ENS_BEH_THREE_STATUS  | Behaviour                         |   |   |
| Health     | ENS_HEALTH            | Health                            |   |   |
| TotW       | MV_FLOAT              | Total active power (Total P)      |   |   |
| TotVAr     | MV_FLOAT              | Total reactive power (Total Q)    |   |   |
| TotVA      | MV_FLOAT              | Total apparent power (Total S)    |   |   |
| TotPF      | MV_FLOAT              | Average power factor (Total PF)   |   |   |
| Hz         | MV_FLOAT              | Frequency                         |   |   |
| PPV        | DEL_SEG_ANG           | Phase to Phase voltages           |   |   |
| PhV        | WYE_SEG_ANG_D         | Phase to Ground voltages          |   |   |
| A          | WYE_SEG_ANG_NEU_RES_D | Phase currents                    |   |   |
| W          | WYE_SEG               | Phase active power (P)            |   |   |
| VAr        | WYE_SEG               | Phase reactive power (Q)          |   |   |
| VA         | WYE_SEG               | Phase apparent power (S)          |   |   |
| PF         | WYE_SEG               | Phase power factor                |   |   |
| ACurTrans1 | WYE_SEG_ANG_D_PRIV    | Phase Currents (CT1)              |   | X |
| ACurTrans2 | WYE_SEG_ANG_D_PRIV    | Phase Currents (CT2)              |   | X |
| AMut       | WYE_NEU_ANG_D_PRIV    | Phase currents (Mutual Magnitude) |   | X |
| ASef       | WYE_NEU_ANG_D_PRIV    | Phase currents (ISEF Magnitude)   |   | X |
| DfDt       | MV_FLOAT_PRIV         | The measurement for Df/Dt         |   | X |
| V1         | WYE_RES_ANG_D_NS      | VN Derived Magnitude Angle        |   | X |
| V2         | WYE_RES_ANG_D_NS      | VN Measured Magnitude Angle       |   | X |

### 1.4.33 LOGICAL NODE: MMXU\_METER\_AV

Description: Metering Statistics (w.r.t Current, Real + Reactive Power - Average Values)

LN Class: MMXU

| Attribute  | Attr. Type            | Explanation                                                                | T | X |
|------------|-----------------------|----------------------------------------------------------------------------|---|---|
| NamPlt     | LPL_LN                | Name Plate                                                                 |   |   |
| Beh        | ENS_BEH_THREE_STATUS  | Behaviour                                                                  |   |   |
| Health     | ENS_HEALTH            | Health                                                                     |   |   |
| ClcExp     | SPS_WD                | Calculation period expired                                                 | T |   |
| ClcMth     | ENG_SET_WD_CLCMTH     | Calculation method of statistical data objects                             |   |   |
| ClcMod     | ENG_SET_WD_CLCMOD     | Calculation mode                                                           |   |   |
| ClcIntvTyp | ENG_SET_WD_CLCINTVTYP | Calculation interval type                                                  |   |   |
| ClcIntvPer | ING_SET_WD            | Number of units to consider to calculate the calculation interval duration |   |   |
| AvWPhs     | MV_FLOAT_D            | Arithmetic average of the magnitude of active power of the 3 phases        |   |   |
| AvVArPhs   | MV_FLOAT_D            | Arithmetic average of the magnitude of reactive power of the 3 phases      |   |   |
| AvAPhsA    | MV_FLOAT_D_PRIV       | Arithmetic average of the magnitude of Ia current                          |   | X |
| AvAPhsB    | MV_FLOAT_D_PRIV       | Arithmetic average of the magnitude of Ib current                          |   | X |
| AvAPhsC    | MV_FLOAT_D_PRIV       | Arithmetic average of the magnitude of Ic current                          |   | X |

**1.4.34 LOGICAL NODE: MMXU\_METER\_MAX**

Description: Standard Measurements (w.r.t Current, Real + Reactive Power - Max Values)

LN Class: MMXU

| Attribute | Attr. Type           | Explanation                                         | T | X |
|-----------|----------------------|-----------------------------------------------------|---|---|
| NamPlt    | LPL_LN               | Name Plate                                          |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour                                           |   |   |
| Health    | ENS_HEALTH           | Health                                              |   |   |
| ClcExp    | SPS_WD               | Calculation period expired                          | T |   |
| ClcMth    | ENG_SET_WD_CLCMTH    | Calculation method of statistical data objects      |   |   |
| ClcMod    | ENG_SET_WD_CLCMOD    | Calculation mode                                    |   |   |
| MaxWPhs   | MV_FLOAT_D           | Maximum magnitude of active power of the 3 phases   |   |   |
| MaxVArPhs | MV_FLOAT_D           | Maximum magnitude of reactive power of the 3 phases |   |   |
| MaxAPhsA  | MV_FLOAT_D_PRIV      | Maximum magnitude of Ia current                     |   | X |
| MaxAPhsB  | MV_FLOAT_D_PRIV      | Maximum magnitude of Ib current                     |   | X |
| MaxAPhsC  | MV_FLOAT_D_PRIV      | Maximum magnitude of Ic current                     |   | X |

**1.4.35 LOGICAL NODE: MMXU\_RMS**

Description: Standard Measurements (w.r.t RMS Values)

LN Class: MMXU

| Attribute | Attr. Type           | Explanation                                    | T | X |
|-----------|----------------------|------------------------------------------------|---|---|
| NamPlt    | LPL_LN               | Name Plate                                     |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour                                      |   |   |
| Health    | ENS_HEALTH           | Health                                         |   |   |
| ClcMth    | ENG_SET_WD_CLCMTH    | Calculation method of statistical data objects |   |   |
| PhV       | WYE_SEG_D            | Phase to Ground voltages                       |   |   |
| A         | WYE_SEG_D            | Phase currents                                 |   |   |

**1.4.36 LOGICAL NODE: MSQI\_ALL**

Description: Sequence and Imbalance (w.r.t Pos, Neg, Zero)

LN Class: MSQI

| Attribute | Attr. Type           | Explanation                                  | T | X |
|-----------|----------------------|----------------------------------------------|---|---|
| NamPlt    | LPL_LN               | Name Plate                                   |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour                                    |   |   |
| Health    | ENS_HEALTH           | Health                                       |   |   |
| SeqA      | SEQ_MAG_ANG          | Positive, Negative and Zero sequence current |   |   |
| SeqV      | SEQ_MAG_ANG          | Positive, Negative and Zero sequence voltage |   |   |

**1.4.37 LOGICAL NODE: MSQI\_VOLTAGE**

Description: Sequence and Imbalance (w.r.t Pos, Neg, Zero Voltage Only)

LN Class: MSQI

| Attribute | Attr. Type           | Explanation                                  | T | X |
|-----------|----------------------|----------------------------------------------|---|---|
| NamPlt    | LPL_LN               | Name Plate                                   |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour                                    |   |   |
| Health    | ENS_HEALTH           | Health                                       | T |   |
| SeqV      | SEQ_MAG_ANG          | Positive, Negative and Zero sequence voltage |   |   |

**1.4.38 LOGICAL NODE: PDIF\_NEU**

Description: Differential (w.r.t Neutral)

LN Class: PDIF

| Attribute | Attr. Type          | Explanation | T | X |
|-----------|---------------------|-------------|---|---|
| NamPlt    | LPL_LN              | Name Plate  |   |   |
| Beh       | ENS_BEH_FOUR_STATUS | Behaviour   |   |   |
| Health    | ENS_HEALTH          | Health      |   |   |
| Op        | ACT_NEU             | Operate     | T |   |

**1.4.39 LOGICAL NODE: PDIS\_BASIC**

Description: Distance (w.r.t Mandatory Attributes Only)

LN Class: PDIS

| Attribute | Attr. Type          | Explanation | T | X |
|-----------|---------------------|-------------|---|---|
| NamPlt    | LPL_LN              | Name Plate  |   |   |
| Beh       | ENS_BEH_FOUR_STATUS | Behaviour   |   |   |
| Health    | ENS_HEALTH          | Health      |   |   |
| Str       | ACD_SEG_NEU         | Start       |   |   |
| Op        | ACT_SEG_NEU         | Operate     | T |   |

**1.4.40 LOGICAL NODE: PDOP\_BASIC**

Description: Directional Overpower

LN Class: PDOP

| Attribute | Attr. Type          | Explanation | T | X |
|-----------|---------------------|-------------|---|---|
| NamPlt    | LPL_LN              | Name Plate  |   |   |
| Beh       | ENS_BEH_FOUR_STATUS | Behaviour   |   |   |
| Health    | ENS_HEALTH          | Health      |   |   |
| Mod       | ENC_MOD_TWO_STATUS  | Mode        |   |   |
| Str       | ACD_SEG             | Start       |   |   |
| Op        | ACT_SEG             | Operate     | T |   |

**1.4.41 LOGICAL NODE: PDUP\_BASIC**

Description: Directional Underpower

LN Class: PDUP

| Attribute | Attr. Type          | Explanation | T | X |
|-----------|---------------------|-------------|---|---|
| NamPlt    | LPL_LN              | Name Plate  |   |   |
| Beh       | ENS_BEH_FOUR_STATUS | Behaviour   |   |   |
| Health    | ENS_HEALTH          | Health      |   |   |
| Str       | ACD_SEG             | Start       |   |   |
| Op        | ACT_SEG             | Operate     | T |   |

**1.4.42 LOGICAL NODE: PFRC\_NO\_SEG**

Description: Rate of Change of Frequency (w.r.t No Phase Segregation)

LN Class: PFRC

| Attribute | Attr. Type          | Explanation | T | X |
|-----------|---------------------|-------------|---|---|
| NamPlt    | LPL_LN              | Name Plate  |   |   |
| Beh       | ENS_BEH_FOUR_STATUS | Behaviour   |   |   |
| Health    | ENS_HEALTH          | Health      |   |   |
| Str       | ACD_NO_SEG          | Start       |   |   |
| Op        | ACT_NO_SEG          | Operate     | T |   |

**1.4.43 LOGICAL NODE: PSCH\_EXTENSION**

Description: Protection Scheme Extensions for Ed2

LN Class: PSCH

| Attribute | Attr. Type           | Explanation                                                                                                                     | T | X |
|-----------|----------------------|---------------------------------------------------------------------------------------------------------------------------------|---|---|
| NamPlt    | LPL_LN               | Name Plate                                                                                                                      |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour                                                                                                                       |   |   |
| Health    | ENS_HEALTH           | Health                                                                                                                          |   |   |
| TxPrm     | ACT_NO_SEG           | Permissive information to be transmitted to the other side (teleprotection permissive signal)                                   | T |   |
| TxBlk     | ACT_NO_SEG           | Blocking information to be transmitted to the other side (teleprotection blocking signal)                                       | T |   |
| RxPrm1    | ACT_NO_SEG           | Activation information RxPrm1 received from the other side(s), for logging purposes (teleprotection permissive signal received) | T |   |
| RxBlk1    | ACT_NO_SEG           | Activation information RxBlk1 received from the other side(s), for logging purposes (teleprotection blocking signal received)   | T |   |
| Op        | ACT_SEG_NEU          | Operate                                                                                                                         | T |   |
| EchoWei   | SPS_WD               | TxPrm is being sent as echo signal or in case of weak end infeed                                                                | T |   |
| EchoWeiOp | SPS_WD               | Additional indication that Op is the operate from the weak end infeed or echo function (typically with undervoltage control)    | T |   |

**1.4.44 LOGICAL NODE: PSDE\_NEU**

Description: Sensitive Directional Earthfault

LN Class: PSDE

| Attribute | Attr. Type          | Explanation | T | X |
|-----------|---------------------|-------------|---|---|
| NamPlt    | LPL_LN              | Name Plate  |   |   |
| Beh       | ENS_BEH_FOUR_STATUS | Behaviour   |   |   |
| Health    | ENS_HEALTH          | Health      |   |   |
| Str       | ACD_NEU             | Start       |   |   |
| Op        | ACT_NEU             | Operate     | T |   |

**1.4.45 LOGICAL NODE: PSOF\_SOTF\_OP**

Description: Switch-onto-Fault Protection (w.r.t Multiple Zone Operate)

LN Class: PSOF

| Attribute | Attr. Type             | Explanation         | T | X |
|-----------|------------------------|---------------------|---|---|
| NamPlt    | LPL_LN_PRIV            | Name Plate          |   |   |
| Beh       | ENS_BEH_FOUR_STATUS_DN | Behaviour           |   |   |
| Health    | ENS_HEALTH_DN          | Health              |   |   |
| Str       | ACD_NO_SEG_DN          | Start               |   |   |
| SofOp1    | ACT_NO_SEG_D_DN        | Zone 1 Operate      | T | X |
| SofOp2    | ACT_NO_SEG_D_DN        | Zone 2 Operate      | T | X |
| SofOp3    | ACT_NO_SEG_D_DN        | Zone 3 Operate      | T | X |
| SofOp4    | ACT_NO_SEG_D_DN        | Zone 4 Operate      | T | X |
| SofOp5    | ACT_NO_SEG_D_DN        | Zone P Operate      | T | X |
| SofOp6    | ACT_NO_SEG_D_DN        | Zone Q Operate      | T | X |
| SofOp7    | ACT_NO_SEG_D_DN        | CNV Operate         | T | X |
| SofOp8    | ACT_NO_SEG_D_DN        | Zone R Operate      | T | X |
| SofOp9    | ACT_NO_SEG_D_DN        | Zone S Operate      | T | X |
| SofOp10   | ACT_NO_SEG_D_DN        | Aid Zone 1e Operate | T | X |
| Op        | ACT_NO_SEG             | Operate             | T |   |

**1.4.46 LOGICAL NODE: PSOF\_TOR\_OP**

Description: Trip-on-Reclose Protection

LN Class: PSOF

| Attribute | Attr. Type             | Explanation         | T | X |
|-----------|------------------------|---------------------|---|---|
| NamPlt    | LPL_LN_PRIV            | Name Plate          |   |   |
| Beh       | ENS_BEH_FOUR_STATUS_DN | Behaviour           |   |   |
| Health    | ENS_HEALTH_DN          | Health              |   |   |
| Str       | ACD_NO_SEG_DN          | Start               |   |   |
| TorOp1    | ACT_NO_SEG_D_DN        | Zone 1 Operate      | T | X |
| TorOp2    | ACT_NO_SEG_D_DN        | Zone 2 Operate      | T | X |
| TorOp3    | ACT_NO_SEG_D_DN        | Zone 3 Operate      | T | X |
| TorOp4    | ACT_NO_SEG_D_DN        | Zone 4 Operate      | T | X |
| TorOp5    | ACT_NO_SEG_D_DN        | Zone P Operate      | T | X |
| TorOp6    | ACT_NO_SEG_D_DN        | Zone Q Operate      | T | X |
| TorOp7    | ACT_NO_SEG_D_DN        | CNV Operate         | T | X |
| TorOp8    | ACT_NO_SEG_D_DN        | Zone R Operate      | T | X |
| TorOp9    | ACT_NO_SEG_D_DN        | Zone S Operate      | T | X |
| TorOp10   | ACT_NO_SEG_D_DN        | Aid Zone 1e Operate | T | X |
| Op        | ACT_NO_SEG             | Operate             | T |   |

**1.4.47 LOGICAL NODE: PTEF\_NEU**

Description: Transient Earth Fault (w.r.t Neutral)

LN Class: PTEF

| Attribute | Attr. Type          | Explanation | T | X |
|-----------|---------------------|-------------|---|---|
| NamPlt    | LPL_LN              | Name Plate  |   |   |
| Beh       | ENS_BEH_FOUR_STATUS | Behaviour   |   |   |
| Health    | ENS_HEALTH          | Health      |   |   |

| Attribute | Attr. Type | Explanation                     | T | X |
|-----------|------------|---------------------------------|---|---|
| Str       | ACD_NEU    | Start (transient earth fault)   |   |   |
| Op        | ACT_NEU    | Operate (transient earth fault) | T |   |

#### 1.4.48 LOGICAL NODE: PTOC\_NEU

Description: Timed Overcurrent (w.r.t Neutral)

LN Class: PTOC

| Attribute | Attr. Type          | Explanation | T | X |
|-----------|---------------------|-------------|---|---|
| NamPlt    | LPL_LN              | Name Plate  |   |   |
| Beh       | ENS_BEH_FOUR_STATUS | Behaviour   |   |   |
| Health    | ENS_HEALTH          | Health      |   |   |
| Str       | ACD_NEU             | Start       |   |   |
| Op        | ACT_NEU             | Operate     | T |   |

#### 1.4.49 LOGICAL NODE: PTOC\_NO\_SEG

Description: Timed Overcurrent (w.r.t No Phase Segregation)

LN Class: PTOC

| Attribute | Attr. Type          | Explanation | T | X |
|-----------|---------------------|-------------|---|---|
| NamPlt    | LPL_LN              | Name Plate  |   |   |
| Beh       | ENS_BEH_FOUR_STATUS | Behaviour   |   |   |
| Health    | ENS_HEALTH          | Health      |   |   |
| Str       | ACD_NO_SEG          | Start       |   |   |
| Op        | ACT_NO_SEG          | Operate     | T |   |

#### 1.4.50 LOGICAL NODE: PTOC\_SEG

Description: Timed Overcurrent (w.r.t Phase Segregation)

LN Class: PTOC

| Attribute | Attr. Type          | Explanation | T | X |
|-----------|---------------------|-------------|---|---|
| NamPlt    | LPL_LN              | Name Plate  |   |   |
| Beh       | ENS_BEH_FOUR_STATUS | Behaviour   |   |   |
| Health    | ENS_HEALTH          | Health      |   |   |
| Str       | ACD_SEG             | Start       |   |   |
| Op        | ACT_SEG             | Operate     | T |   |

#### 1.4.51 LOGICAL NODE: PTOF\_NO\_SEG

Description: Overfrequency (w.r.t No Phase Segregation)

LN Class: PTOF

| Attribute | Attr. Type          | Explanation | T | X |
|-----------|---------------------|-------------|---|---|
| NamPlt    | LPL_LN              | Name Plate  |   |   |
| Beh       | ENS_BEH_FOUR_STATUS | Behaviour   |   |   |
| Health    | ENS_HEALTH          | Health      |   |   |
| Str       | ACD_NO_SEG          | Start       |   |   |
| Op        | ACT_NO_SEG          | Operate     | T |   |

**1.4.52 LOGICAL NODE: PTOV\_NEU**

Description: Overvoltage (w.r.t Neutral)

LN Class: PTOV

| Attribute | Attr. Type          | Explanation | T | X |
|-----------|---------------------|-------------|---|---|
| NamPlt    | LPL_LN              | Name Plate  |   |   |
| Beh       | ENS_BEH_FOUR_STATUS | Behaviour   |   |   |
| Health    | ENS_HEALTH          | Health      |   |   |
| Str       | ACD_NO_SEG          | Start       |   |   |
| Op        | ACT_NO_SEG          | Operate     | T |   |

**1.4.53 LOGICAL NODE: PTOV\_NO\_SEG**

Description: Overvoltage (w.r.t No Phase Segregation)

LN Class: PTOV

| Attribute | Attr. Type          | Explanation | T | X |
|-----------|---------------------|-------------|---|---|
| NamPlt    | LPL_LN              | Name Plate  |   |   |
| Beh       | ENS_BEH_FOUR_STATUS | Behaviour   |   |   |
| Health    | ENS_HEALTH          | Health      |   |   |
| Str       | ACD_NO_SEG          | Start       |   |   |
| Op        | ACT_NO_SEG          | Operate     | T |   |

**1.4.54 LOGICAL NODE: PTOV\_SEG**

Description: Overvoltage (w.r.t Phase Segregation)

LN Class: PTOV

| Attribute | Attr. Type          | Explanation | T | X |
|-----------|---------------------|-------------|---|---|
| NamPlt    | LPL_LN              | Name Plate  |   |   |
| Beh       | ENS_BEH_FOUR_STATUS | Behaviour   |   |   |
| Health    | ENS_HEALTH          | Health      |   |   |
| Str       | ACD_SEG             | Start       |   |   |
| Op        | ACT_SEG             | Operate     | T |   |

**1.4.55 LOGICAL NODE: PTRC\_GLOBAL**

Description: Protection Trip for Global Protection Conditioning

LN Class: PTRC

| Attribute | Attr. Type           | Explanation                                                      | T | X |
|-----------|----------------------|------------------------------------------------------------------|---|---|
| NamPlt    | LPL_LN               | Name Plate                                                       |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour                                                        |   |   |
| Health    | ENS_HEALTH           | Health                                                           |   |   |
| Tr        | ACT_SEG              | Trip                                                             |   |   |
| Op        | ACT_SEG_NEU          | Operate (combination of subscribed Op from protection functions) |   |   |
| Str       | ACD_SEG_NEU          | Sum of all starts of all connected Logical Nodes                 |   |   |

**1.4.56 LOGICAL NODE: PTRC\_INDIVID\_NO\_SEG**

Description: Protection Trip for Individual Protection Conditioning

LN Class: PTRC

| Attribute | Attr. Type           | Explanation                                                      | T | X |
|-----------|----------------------|------------------------------------------------------------------|---|---|
| NamPlt    | LPL_LN               | Name Plate                                                       |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour                                                        |   |   |
| Health    | ENS_HEALTH           | Health                                                           |   |   |
| Op        | ACT_NO_SEG           | Operate (combination of subscribed Op from protection functions) |   |   |
| Str       | ACD_NO_SEG           | Sum of all starts of all connected Logical Nodes                 |   |   |

**1.4.57 LOGICAL NODE: PTTR\_NO\_SEG**

Description: Thermal Overload (w.r.t No Phase Segregation)

LN Class: PTTR

| Attribute | Attr. Type          | Explanation                                          | T | X |
|-----------|---------------------|------------------------------------------------------|---|---|
| NamPlt    | LPL_LN              | Name Plate                                           |   |   |
| Beh       | ENS_BEH_FOUR_STATUS | Behaviour                                            |   |   |
| Health    | ENS_HEALTH          | Health                                               |   |   |
| Op        | ACT_NO_SEG          | Operate                                              | T |   |
| AlmThm    | SPS_WD              | Thermal alarm                                        |   |   |
| Amp       | MV_FLOAT            | Current for thermal load model                       |   |   |
| TmpRl     | MV_FLOAT            | Relation between temperature and maximum temperature |   |   |
| MTRRs     | SPC_CTRL_PRIV       | Reset Thermal State                                  |   | X |

**1.4.58 LOGICAL NODE: PTUF\_NO\_SEG**

Description: Underfrequency (w.r.t No Phase Segregation)

LN Class: PTUF

| Attribute | Attr. Type          | Explanation | T | X |
|-----------|---------------------|-------------|---|---|
| NamPlt    | LPL_LN              | Name Plate  |   |   |
| Beh       | ENS_BEH_FOUR_STATUS | Behaviour   |   |   |
| Health    | ENS_HEALTH          | Health      |   |   |
| Str       | ACD_NO_SEG          | Start       |   |   |
| Op        | ACT_NO_SEG          | Operate     | T |   |

**1.4.59 LOGICAL NODE: PTUV\_SEG**

Description: Undervoltage (w.r.t Phase Segregation)

LN Class: PTUV

| Attribute | Attr. Type          | Explanation | T | X |
|-----------|---------------------|-------------|---|---|
| NamPlt    | LPL_LN              | Name Plate  |   |   |
| Beh       | ENS_BEH_FOUR_STATUS | Behaviour   |   |   |
| Health    | ENS_HEALTH          | Health      |   |   |
| Str       | ACD_SEG             | Start       |   |   |
| Op        | ACT_SEG             | Operate     | T |   |

**1.4.60 LOGICAL NODE: RBRF\_EXTTRIP**

Description: Breaker Failure (w.r.t External Tripping)

LN Class: RBRF

| Attribute | Attr. Type          | Explanation                            | T | X |
|-----------|---------------------|----------------------------------------|---|---|
| NamPlt    | LPL_LN              | Name Plate                             |   |   |
| Beh       | ENS_BEH_FOUR_STATUS | Behaviour                              |   |   |
| Health    | ENS_HEALTH          | Health                                 |   |   |
| OpEx      | ACT_NO_SEG          | Breaker failure trip ("External trip") | T |   |

**1.4.61 LOGICAL NODE: RDRE\_BASIC**

Description: Disturbance Recorder Function (w.r.t Mandatory Attributes Only)

LN Class: RDRE

| Attribute | Attr. Type           | Explanation       | T | X |
|-----------|----------------------|-------------------|---|---|
| NamPlt    | LPL_LN               | Name Plate        |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour         |   |   |
| Health    | ENS_HEALTH           | Health            |   |   |
| RcdMade   | SPS_WD               | Recording made    |   |   |
| FltNum    | INS_BASIC            | Fault number      |   |   |
| RcdStr    | SPS_WD               | Recording started |   |   |
| RcdTrg    | SPC_CONTROL          | Trigger recorder  |   |   |
| MemClr    | SPC_CONTROL          | Clear memory      | T |   |

**1.4.62 LOGICAL NODE: RFLO\_BASIC**

Description: Fault Locator (w.r.t Mandatory Attributes Only)

LN Class: RFLO

| Attribute | Attr. Type           | Explanation          | T | X |
|-----------|----------------------|----------------------|---|---|
| NamPlt    | LPL_LN               | Name Plate           |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour            |   |   |
| Health    | ENS_HEALTH           | Health               |   |   |
| FltLoop   | ENS_PHASE_SEL        | Fault loop           |   |   |
| FltZ      | CMV_MAG_FLOAT        | Fault impedance      |   |   |
| FltDiskm  | MV_FLOAT             | Fault distance in km |   |   |

**1.4.63 LOGICAL NODE: RPSB\_OST**

Description: Power Swing Blocking (w.r.t Out of Step Tripping)

LN Class: RPSB

| Attribute | Attr. Type          | Explanation                    | T | X |
|-----------|---------------------|--------------------------------|---|---|
| NamPlt    | LPL_LN              | Name Plate                     |   |   |
| Beh       | ENS_BEH_FOUR_STATUS | Behaviour                      |   |   |
| Health    | ENS_HEALTH          | Health                         |   |   |
| Op        | ACT_NO_SEG          | Operate (Out of step Tripping) | T |   |

**1.4.64 LOGICAL NODE: RPSB\_PSB\_MULTI**

Description: Power Swing Detection/Blocking (w.r.t Mandatory Attributes Only + Multiple Starts)

LN Class: RPSB

| Attribute | Attr. Type          | Explanation                       | T | X |
|-----------|---------------------|-----------------------------------|---|---|
| NamPlt    | LPL_LN              | Name Plate                        |   |   |
| Beh       | ENS_BEH_FOUR_STATUS | Behaviour                         |   |   |
| Health    | ENS_HEALTH          | Health                            |   |   |
| BlkZn     | SPS_WD              | Blocking of correlated PDIS zone  |   |   |
| Str       | ACD_NO_SEG_D        | Start (Power Swing Detected)      |   |   |
| SwgAlm    | ACD_NO_SEG_D_DN     | Start (Slow Power Swing Detected) |   | X |

**1.4.65 LOGICAL NODE: RREC\_NO\_SEG**

Description: Autoreclosing (w.r.t No Phase Segregation)

LN Class: RREC

| Attribute | Attr. Type           | Explanation                                              | T | X |
|-----------|----------------------|----------------------------------------------------------|---|---|
| NamPlt    | LPL_LN               | Name Plate                                               |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour                                                |   |   |
| Health    | ENS_HEALTH           | Health                                                   |   |   |
| RecCyc    | INS_BASIC            | Actual Reclose Cycle                                     |   |   |
| OpCls     | ACT_NO_SEG           | Operation "Close Switch" issued to close circuit breaker |   |   |
| AutoRecSt | ENS_AUTORECST        | Auto reclosing status                                    |   |   |
| MaxCyc    | ING_SET_TM           | Max number of reclose cycles                             |   |   |

**1.4.66 LOGICAL NODE: RSYN\_DIFCLC\_ENH**

Description: Synchronism-check/Synchronising (w.r.t Calculated Differential Measurements)

LN Class: RSYN

| Attribute | Attr. Type           | Explanation                          | T | X |
|-----------|----------------------|--------------------------------------|---|---|
| NamPlt    | LPL_LN               | Name Plate                           |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour                            |   |   |
| Health    | ENS_HEALTH           | Health                               |   |   |
| Rel       | SPS_WD               | Release                              |   |   |
| VInd      | SPS_WD               | Voltage difference indicator         |   |   |
| AngInd    | SPS_WD               | Angle difference indicator           |   |   |
| HzInd     | SPS_WD               | Frequency difference indicator       |   |   |
| DifVClc   | MV_FLOAT             | Calculated difference in voltage     |   |   |
| DifHzClc  | MV_FLOAT             | Calculated difference in frequency   |   |   |
| DifAngClc | MV_FLOAT             | Calculated difference of phase angle |   |   |

**1.4.67 LOGICAL NODE: TVTR\_SYSTEM**

Description: Voltage Transformer

LN Class: TVTR

| Attribute | Attr. Type           | Explanation                   | T | X |
|-----------|----------------------|-------------------------------|---|---|
| NamPlt    | LPL_LN               | Name Plate                    |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour                     |   |   |
| Health    | ENS_HEALTH           | Health                        |   |   |
| EEName    | DPL_PRIV             | External equipment name plate |   |   |

| Attribute | Attr. Type   | Explanation                                                              | T | X |
|-----------|--------------|--------------------------------------------------------------------------|---|---|
| EEHealth  | ENS_HEALTH   | External equipment health                                                |   |   |
| FuFail    | SPS_WD       | TVTR fuse failure                                                        |   |   |
| VRtg      | ASG_SP_FLOAT | Rated Voltage                                                            |   |   |
| HzRtg     | ASG_SP_INT   | Rated frequency                                                          |   |   |
| Rat       | ASG_SP_RAT   | Winding ratio of external voltage transformer (transducer) if applicable |   |   |

#### 1.4.68 LOGICAL NODE: XCBR\_BASIC

Description: Circuit Breaker (w.r.t Mandatory Attributes Only)

LN Class: XCBR

| Attribute | Attr. Type           | Explanation                          | T | X |
|-----------|----------------------|--------------------------------------|---|---|
| NamPlt    | LPL_LN               | Name Plate                           |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour                            |   |   |
| Health    | ENS_HEALTH           | Health                               |   |   |
| EEHealth  | ENS_HEALTH           | External equipment health            |   |   |
| Loc       | SPS_WD               | Local operation                      |   |   |
| OpCnt     | INS_BASIC            | Operation counter                    |   |   |
| CBOpCap   | ENS_CBCAP            | Circuit Breaker operating capability |   |   |
| SumSwARs  | BCR_PRIV             | Sum of switched amperes, resettable  |   |   |
| Pos       | DPC_STATUS           | Switch position                      |   |   |
| BlkOpn    | SPC_STATUS           | Block opening                        |   |   |
| BlkCls    | SPC_STATUS           | Block closing                        |   |   |

#### 1.4.69 LOGICAL NODE: XSWI\_BASIC

Description: Circuit Switch (w.r.t Switch Status and Control)

LN Class: XSWI

| Attribute | Attr. Type           | Explanation                 | T | X |
|-----------|----------------------|-----------------------------|---|---|
| NamPlt    | LPL_LN               | Name Plate                  |   |   |
| Beh       | ENS_BEH_THREE_STATUS | Behaviour                   |   |   |
| Health    | ENS_HEALTH           | Health                      |   |   |
| EEHealth  | ENS_HEALTH           | External equipment health   |   |   |
| Loc       | SPS_WD               | Local control behaviour     |   |   |
| OpCnt     | INS_BASIC            | Operation counter           |   |   |
| SwTyp     | ENS_SWI_TYPE         | Switch type                 |   |   |
| SwOpCap   | ENS_SWOPCAP          | Switch operating capability |   |   |
| Pos       | DPC_STATUS           | Switch position             |   |   |
| BlkOpn    | SPC_STATUS           | Block opening               |   |   |
| BlkCls    | SPC_STATUS           | Block closing               |   |   |

## 1.5 COMMON DATA CLASS DEFINITIONS

The definition tables for each of the Common Data Classes used in the Logical Node definitions are presented in the following sub-sections.

From an application point-of-view the data attributes of a Common Data Class are classified according to their specific use. The characterization of data attributes, and the services that they support/provide, will be through the use of 'Functional Constraints'. The Functional Constraints are specified by the table below:

| FC Name | Semantic                          | Source Definition |
|---------|-----------------------------------|-------------------|
| BL      | Blocking                          | IEC61850-7-2-2010 |
| BR      | Buffered reports                  | IEC61850-7-2      |
| CF      | Configuration                     | IEC61850-7-2      |
| CO      | Control                           | IEC61850-7-2      |
| DC      | Description                       | IEC61850-7-2      |
| EX      | Extended Definition               | IEC61850-7-2      |
| GO      | GOOSE Control                     | IEC61850-7-2      |
| GS      | GSSE Control (UCA2 GOOSE)         | IEC61850-7-2      |
| LG      | Logging                           | IEC61850-7-2      |
| MS      | Multicast sampled value control   | IEC61850-7-2      |
| MX      | Measurands (Analogue values)      | IEC61850-7-2      |
| OR      | Operate received                  | IEC61850-7-2-2010 |
| RP      | Unbuffered reports                | IEC61850-7-2      |
| SE      | Setting Group Editable            | IEC61850-7-2      |
| SG      | Setting Group                     | IEC61850-7-2      |
| SP      | Set Point                         | IEC61850-7-2      |
| SR      | Service response                  | IEC61850-7-2-2010 |
| ST      | Status Information                | IEC61850-7-2      |
| SV      | Substitution Values               | IEC61850-7-2      |
| US      | Unicast sampled value control     | IEC61850-7-2      |
| XX      | Data attribute service parameters | IEC61850-7-2      |

### 1.5.1 COMMON DATA CLASS: ACD\_NEU

Description: Directional Protection Activation Information (w.r.t Neutral)

CDC Class: ACD

| Attribute  | Type                            | FC | Enumeration            | Comment                                                                    | X          |
|------------|---------------------------------|----|------------------------|----------------------------------------------------------------------------|------------|
| general    | BOOLEAN                         | ST |                        | Trip or start has happened                                                 | general    |
| dirGeneral | ENUMERATED8<br>(MMS Type: INT8) | ST | FaultDirectionKind     | General direction (unknown, forward, backward or both)                     | dirGeneral |
| neut       | BOOLEAN                         | ST |                        | Trip or start event with earth current has happened                        | neut       |
| dirNeut    | ENUMERATED8<br>(MMS Type: INT8) | ST | PhaseFaultDirectionKin | Earth current direction (unknown, forward or backward)                     | dirNeut    |
| dq         | Quality                         | ST |                        | Quality of the protection activation information                           | dq         |
| t          | TimeStamp                       | ST |                        | Timestamp of the last change in state of protection activation information | t          |

### 1.5.2 COMMON DATA CLASS: ACD\_NO\_SEG

Description: Directional Protection Activation Information (w.r.t No Phase Segregation)

CDC Class: ACD

| Attribute  | Type                            | FC | Enumeration | Comment                                                                    | X |
|------------|---------------------------------|----|-------------|----------------------------------------------------------------------------|---|
| general    | BOOLEAN                         | ST |             | Trip or start has happened                                                 |   |
| dirGeneral | ENUMERATED8<br>(MMS Type: INT8) | ST | dir         | General direction (unknown, forward, backward or both)                     |   |
| q          | Quality                         | ST |             | Quality of the protection activation information                           |   |
| t          | TimeStamp                       | ST |             | Timestamp of the last change in state of protection activation information |   |

### 1.5.3 COMMON DATA CLASS: ACD\_NO\_SEG\_D

Description: Directional Protection Activation Information (w.r.t No Phase Segregation + Description)

CDC Class: ACD

| Attribute  | Type                            | FC | Enumeration | Comment                                                                    | X |
|------------|---------------------------------|----|-------------|----------------------------------------------------------------------------|---|
| general    | BOOLEAN                         | ST |             | Trip or start has happened                                                 |   |
| dirGeneral | ENUMERATED8<br>(MMS Type: INT8) | ST | dir         | General direction (unknown, forward, backward or both)                     |   |
| q          | Quality                         | ST |             | Quality of the protection activation information                           |   |
| t          | TimeStamp                       | ST |             | Timestamp of the last change in state of protection activation information |   |
| d          | VISIBLE_STRING255               | DC |             | Description of the status element                                          |   |

### 1.5.4 COMMON DATA CLASS: ACD\_NO\_SEG\_D\_DN

Description: Directional Protection Activation Information (w.r.t No Phase Segregation, with Description and dataNs Used for the Standard DO in the Extended LN)

CDC Class: ACD

| Attribute  | Type                            | FC | Enumeration | Comment                                                                    | X |
|------------|---------------------------------|----|-------------|----------------------------------------------------------------------------|---|
| general    | BOOLEAN                         | ST |             | Trip or start has happened                                                 |   |
| dirGeneral | ENUMERATED8<br>(MMS Type: INT8) | ST | dir         | General direction (unknown, forward, backward or both)                     |   |
| q          | Quality                         | ST |             | Quality of the protection activation information                           |   |
| t          | TimeStamp                       | ST |             | Timestamp of the last change in state of protection activation information |   |
| d          | VISIBLE_STRING255               | DC |             | Description of the status element                                          |   |
| dataNs     | VISIBLE_STRING255               | EX |             | Data name space                                                            |   |

### 1.5.5 COMMON DATA CLASS: ACD\_NO\_SEG\_DN

Description: Directional Protection Activation Information (w.r.t No Phase Segregation, with dataNs Used for the Standard DO in the Extended LN)

CDC Class: ACD

| Attribute  | Type                            | FC | Enumeration        | Comment                                                                    | X |
|------------|---------------------------------|----|--------------------|----------------------------------------------------------------------------|---|
| general    | BOOLEAN                         | ST |                    | Trip or start has happened                                                 |   |
| dirGeneral | ENUMERATED8<br>(MMS Type: INT8) | ST | FaultDirectionKind | General direction (unknown, forward, backward or both)                     |   |
| q          | Quality                         | ST |                    | Quality of the protection activation information                           |   |
| t          | TimeStamp                       | ST |                    | Timestamp of the last change in state of protection activation information |   |
| dataNs     | VISIBLE_STRING255               | EX |                    | Data name space                                                            |   |

### 1.5.6 COMMON DATA CLASS: ACD\_SEG

Description: Directional Protection Activation Information (w.r.t Phase Segregation)

CDC Class: ACD

| Attribute  | Type                            | FC | Enumeration            | Comment                                                                    | X |
|------------|---------------------------------|----|------------------------|----------------------------------------------------------------------------|---|
| general    | BOOLEAN                         | ST |                        | Trip or start has happened                                                 |   |
| dirGeneral | ENUMERATED8<br>(MMS Type: INT8) | ST | FaultDirectionKind     | General direction (unknown, forward, backward or both)                     |   |
| phsA       | BOOLEAN                         | ST |                        | Trip or start event of Phase A has happened                                |   |
| dirPhsA    | ENUMERATED8<br>(MMS Type: INT8) | ST | PhaseFaultDirectionKin | Phase A direction (unknown, forward or backward)                           |   |
| dphsB      | BOOLEAN                         | ST |                        | Trip or start event of Phase B has happened                                |   |
| dirPhsB    | ENUMERATED8<br>(MMS Type: INT8) | ST | PhaseFaultDirectionKin | Phase B direction (unknown, forward or backward)                           |   |
| dphsC      | BOOLEAN                         | ST |                        | Trip or start event of Phase C has happened                                |   |
| dirPhsC    | ENUMERATED8<br>(MMS Type: INT8) | ST | PhaseFaultDirectionKin | Phase C direction (unknown, forward or backward)                           |   |
| dq         | Quality                         | ST |                        | Quality of the protection activation information                           |   |
| t          | TimeStamp                       | ST |                        | Timestamp of the last change in state of protection activation information |   |

### 1.5.7 COMMON DATA CLASS: ACD\_SEG\_NEU

Description: Directional Protection Activation Information (w.r.t Phase Segregation + Neutral)

CDC Class: ACD

| Attribute  | Type                            | FC | Enumeration | Comment                                                                    | X |
|------------|---------------------------------|----|-------------|----------------------------------------------------------------------------|---|
| general    | BOOLEAN                         | ST |             | Trip or start has happened                                                 |   |
| dirGeneral | ENUMERATED8<br>(MMS Type: INT8) | ST | dir         | General direction (unknown, forward, backward or both)                     |   |
| phsA       | BOOLEAN                         | ST |             | Trip or start event of Phase A has happened                                |   |
| dirPhsA    | ENUMERATED8<br>(MMS Type: INT8) | ST | dir_3       | Phase A direction (unknown, forward or backward)                           |   |
| phsB       | BOOLEAN                         | ST |             | Trip or start event of Phase B has happened                                |   |
| dirPhsB    | ENUMERATED8<br>(MMS Type: INT8) | ST | dir_3       | Phase B direction (unknown, forward or backward)                           |   |
| phsC       | BOOLEAN                         | ST |             | Trip or start event of Phase C has happened                                |   |
| dirPhsC    | ENUMERATED8<br>(MMS Type: INT8) | ST | dir_3       | Phase C direction (unknown, forward or backward)                           |   |
| neut       | BOOLEAN                         | ST |             | Trip or start event with earth current has happened                        |   |
| dirNeut    | ENUMERATED8<br>(MMS Type: INT8) | ST | dir_3       | Earth current direction (unknown, forward or backward)                     |   |
| q          | Quality                         | ST |             | Quality of the protection activation information                           |   |
| t          | TimeStamp                       | ST |             | Timestamp of the last change in state of protection activation information |   |

### 1.5.8 COMMON DATA CLASS: ACT\_NEU

Description: Protection Activation Information (w.r.t Neutral)

CDC Class: ACT

| Attribute | Type      | FC | Enumeration | Comment                                                                    | X |
|-----------|-----------|----|-------------|----------------------------------------------------------------------------|---|
| general   | BOOLEAN   | ST |             | Trip or start has happened                                                 |   |
| neut      | BOOLEAN   | ST |             | Trip or start event with earth current has happened                        |   |
| q         | Quality   | ST |             | Quality of the protection activation information                           |   |
| t         | TimeStamp | ST |             | Timestamp of the last change in state of protection activation information |   |

**1.5.9 COMMON DATA CLASS: ACT\_NO\_SEG**

Description: Protection Activation Information (w.r.t No Phase Segregation)

CDC Class: ACT

| Attribute | Type      | FC | Enumeration | Comment                                                                    | X |
|-----------|-----------|----|-------------|----------------------------------------------------------------------------|---|
| general   | BOOLEAN   | ST |             | Trip or start has happened                                                 |   |
| q         | Quality   | ST |             | Quality of the protection activation information                           |   |
| t         | TimeStamp | ST |             | Timestamp of the last change in state of protection activation information |   |

**1.5.10 COMMON DATA CLASS: ACT\_NO\_SEG\_D\_DN**Description: Protection Activation Information (w.r.t No Phase Segregation, with Description and dataNs  
Used for the Standard DO in the Extended LN)

CDC Class: ACT

| Attribute | Type              | FC | Enumeration | Comment                                                                    | X |
|-----------|-------------------|----|-------------|----------------------------------------------------------------------------|---|
| general   | BOOLEAN           | ST |             | Trip or start has happened                                                 |   |
| q         | Quality           | ST |             | Quality of the protection activation information                           |   |
| t         | TimeStamp         | ST |             | Timestamp of the last change in state of protection activation information |   |
| d         | VISIBLE_STRING255 | DC |             | Description of the status element                                          |   |
| dataNs    | VISIBLE_STRING255 | EX |             | Data name space                                                            |   |

**1.5.11 COMMON DATA CLASS: ACT\_SEG**

Description: Protection Activation Information (w.r.t Phase Segregation)

CDC Class: ACT

| Attribute | Type      | FC | Enumeration | Comment                                                                    | X |
|-----------|-----------|----|-------------|----------------------------------------------------------------------------|---|
| general   | BOOLEAN   | ST |             | Trip or start has happened                                                 |   |
| phsA      | BOOLEAN   | ST |             | Trip or start event of Phase A has happened                                |   |
| phsB      | BOOLEAN   | ST |             | Trip or start event of Phase B has happened                                |   |
| phsC      | BOOLEAN   | ST |             | Trip or start event of Phase C has happened                                |   |
| q         | Quality   | ST |             | Quality of the protection activation information                           |   |
| t         | TimeStamp | ST |             | Timestamp of the last change in state of protection activation information |   |

**1.5.12 COMMON DATA CLASS: ACT\_SEG\_NEU**

Description: Protection Activation Information (w.r.t Phase Segregation + Neutral)

CDC Class: ACT

| Attribute | Type      | FC | Enumeration | Comment                                                                    | X |
|-----------|-----------|----|-------------|----------------------------------------------------------------------------|---|
| general   | BOOLEAN   | ST |             | Trip or start has happened                                                 |   |
| phsA      | BOOLEAN   | ST |             | Trip or start event of Phase A has happened                                |   |
| phsB      | BOOLEAN   | ST |             | Trip or start event of Phase B has happened                                |   |
| phsC      | BOOLEAN   | ST |             | Trip or start event of Phase C has happened                                |   |
| neut      | BOOLEAN   | ST |             | Trip or start event with earth current has happened                        |   |
| q         | Quality   | ST |             | Quality of the protection activation information                           |   |
| t         | TimeStamp | ST |             | Timestamp of the last change in state of protection activation information |   |

**1.5.13 COMMON DATA CLASS: ASG\_SP\_FLOAT**

Description: Analogue Setting for Float

CDC Class: ASG

| Attribute | Type                | FC | Enumeration | Comment                                      | X |
|-----------|---------------------|----|-------------|----------------------------------------------|---|
| setMag    | AnalogueValue_Float | SP |             | Setting value                                |   |
| units     | Unit_No_Multiplier  | CF |             | Units of the attribute representing the data |   |
| minVal    | AnalogueValue_Float | CF |             | Minimum setting value                        |   |
| maxVal    | AnalogueValue_Float | CF |             | Maximum setting value                        |   |
| stepSize  | AnalogueValue_Float | CF |             | Setting step size (increment)                |   |
| d         | VISIBLE_STRING255   | DC |             | Description of the status element            |   |

**1.5.14 COMMON DATA CLASS: ASG\_SP\_INT**

Description: Analogue Setting for Integer

CDC Class: ASG

| Attribute | Type               | FC | Enumeration | Comment                                      | X |
|-----------|--------------------|----|-------------|----------------------------------------------|---|
| setMag    | AnalogueValue_Int  | SP |             | Setting value                                |   |
| units     | Unit_No_Multiplier | CF |             | Units of the attribute representing the data |   |
| sVC       | ScaledValueConfig  | CF |             | Scaled value configuration                   |   |
| minVal    | AnalogueValue_Int  | CF |             | Minimum setting value                        |   |
| maxVal    | AnalogueValue_Int  | CF |             | Maximum setting value                        |   |
| stepSize  | AnalogueValue_Int  | CF |             | Setting step size (increment)                |   |
| d         | VISIBLE_STRING255  | DC |             | Description of the status element            |   |

**1.5.15 COMMON DATA CLASS: ASG\_SP\_RAT**

Description: Analogue Setting for Integer without Unit

CDC Class: ASG

| Attribute | Type               | FC | Enumeration | Comment                                      | X |
|-----------|--------------------|----|-------------|----------------------------------------------|---|
| setMag    | AnalogueValue_Int  | SP |             | Setting value                                |   |
| units     | Unit_No_Multiplier | CF |             | Units of the attribute representing the data |   |
| sVC       | ScaledValueConfig  | CF |             | Scaled value configuration                   |   |
| minVal    | AnalogueValue_Int  | CF |             | Minimum setting value                        |   |
| maxVal    | AnalogueValue_Int  | CF |             | Maximum setting value                        |   |
| stepSize  | AnalogueValue_Int  | CF |             | Setting step size (increment)                |   |
| d         | VISIBLE_STRING255  | DC |             | Description of the status element            |   |

**1.5.16 COMMON DATA CLASS: BCR\_PRIV**

Description: Binary Counter Reading

CDC Class: BCR

| Attribute | Type      | FC | Enumeration | Comment                                                               | X |
|-----------|-----------|----|-------------|-----------------------------------------------------------------------|---|
| actVal    | INT64     | ST |             | Binary counter status represented as an integer                       |   |
| q         | Quality   | ST |             | Quality of counter value                                              |   |
| t         | TimeStamp | ST |             | Time of last counter change                                           |   |
| pulsQty   | FLOAT32   | CF |             | Magnitude of the counted value 'per count' (value = actVal x pulsQty) |   |

### 1.5.17 COMMON DATA CLASS: CMV\_MAG\_ANG\_FLOAT

Description: Complex Measured Value (w.r.t Floating Point Magnitude and Angle)

CDC Class: CMV

| Attribute | Type                        | FC | Enumeration | Comment                                                                                                                                              | X |
|-----------|-----------------------------|----|-------------|------------------------------------------------------------------------------------------------------------------------------------------------------|---|
| cVal      | Vector_MagnitudeAngle_Float | MX |             | Deadbanded complex measured vector. Updated to the current value of instCVal when the value has changed according to the configuration parameter db. |   |
| q         | Quality                     | MX |             | Quality of the measurement value                                                                                                                     |   |
| t         | TimeStamp                   | MX |             | Time deadbanded magnitude last exceeded its db configuration parameter                                                                               |   |
| subEna    | BOOLEAN                     | SV |             | Enable/disable substitution                                                                                                                          |   |
| subCVal   | Vector_MagnitudeAngle_Float | SV |             | Substituted measurement value for instCVal                                                                                                           |   |
| subQ      | Quality                     | SV |             | Value used to substitute the data attribute q                                                                                                        |   |
| subID     | VISIBLE_STRING64            | SV |             | Address of the device that made the substitution                                                                                                     |   |
| blkEna    | BOOLEAN                     | BL |             | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated                                                           |   |
| units     | Unit_Multiplier             | CF |             | Unit of the attribute representing the data                                                                                                          |   |
| db        | INT32U                      | CF |             | Measurement deadband                                                                                                                                 |   |
| rangeC    | RangeConfig_DeadBand        | CF |             | Measurement range configuration attributes                                                                                                           |   |
| dbRef     | FLOAT32                     | CF |             | Defines deadband as an absolute value                                                                                                                |   |

### 1.5.18 COMMON DATA CLASS: CMV\_MAG\_ANG\_FLOAT\_PRIV

Description: Complex Measured Value (Used for Extended DO)

CDC Class: CMV

| Attribute | Type                        | FC | Enumeration | Comment                                                                                                                                              | X |
|-----------|-----------------------------|----|-------------|------------------------------------------------------------------------------------------------------------------------------------------------------|---|
| cVal      | Vector_MagnitudeAngle_Float | MX |             | Deadbanded complex measured vector. Updated to the current value of instCVal when the value has changed according to the configuration parameter db. |   |
| q         | Quality                     | MX |             | Quality of the measurement value                                                                                                                     |   |
| t         | TimeStamp                   | MX |             | Time deadbanded magnitude last exceeded its db configuration parameter                                                                               |   |
| subEna    | BOOLEAN                     | SV |             | Enable/disable substitution                                                                                                                          |   |
| subCVal   | Vector_MagnitudeAngle_Float | SV |             | Substituted measurement value for instCVal                                                                                                           |   |
| subQ      | Quality                     | SV |             | Value used to substitute the data attribute q                                                                                                        |   |
| subID     | VISIBLE_STRING64            | SV |             | Address of the device that made the substitution                                                                                                     |   |
| blkEna    | BOOLEAN                     | BL |             | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated                                                           |   |
| units     | Unit_Multiplier             | CF |             | Unit of the attribute representing the data                                                                                                          |   |
| db        | INT32U                      | CF |             | Measurement deadband                                                                                                                                 |   |
| rangeC    | RangeConfig_DeadBand        | CF |             | Measurement range configuration attributes                                                                                                           |   |
| dbRef     | FLOAT32                     | CF |             | Defines deadband as an absolute value                                                                                                                |   |
| dataNs    | VISIBLE_STRING255           | EX |             | Data name space                                                                                                                                      |   |

### 1.5.19 COMMON DATA CLASS: CMV\_MAG\_FLOAT

Description: Complex Measured Value (w.r.t Floating Point Magnitude)

CDC Class: CMV

| Attribute | Type                   | FC | Enumeration | Comment                                                                                                                                              | X |
|-----------|------------------------|----|-------------|------------------------------------------------------------------------------------------------------------------------------------------------------|---|
| cVal      | Vector_Magnitude_Float | MX |             | Deadbanded complex measured vector. Updated to the current value of instCVal when the value has changed according to the configuration parameter db. |   |

| Attribute | Type                   | FC | Enumeration | Comment                                                                                    | X |
|-----------|------------------------|----|-------------|--------------------------------------------------------------------------------------------|---|
| q         | Quality                | MX |             | Quality of the measurement value                                                           |   |
| t         | TimeStamp              | MX |             | Time deadbanded magnitude last exceeded its db configuration parameter                     |   |
| subEna    | BOOLEAN                | SV |             | Enable/disable substitution                                                                |   |
| subCVal   | Vector_Magnitude_Float | SV |             | Substituted measurement value for instCVal                                                 |   |
| subQ      | Quality                | SV |             | Value used to substitute the data attribute q                                              |   |
| subID     | VISIBLE_STRING64       | SV |             | Address of the device that made the substitution                                           |   |
| blkEna    | BOOLEAN                | BL |             | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated |   |
| units     | Unit_Multiplier        | CF |             | Unit of the attribute representing the data                                                |   |
| db        | INT32U                 | CF |             | Measurement deadband                                                                       |   |
| rangeC    | RangeConfig_DeadBand   | CF |             | Measurement range configuration attributes                                                 |   |
| dbRef     | FLOAT32                | CF |             | Defines deadband as an absolute value                                                      |   |

### 1.5.20 COMMON DATA CLASS: DEL\_SEG\_ANG

Description: Phase to Phase Measurements for a 3-Phase System (w.r.t Phase Segregation + Angle)

CDC Class: DEL

| Attribute | Type              | FC | Enumeration | Comment                                   | X |
|-----------|-------------------|----|-------------|-------------------------------------------|---|
| phsAB     | CMV_MAG_ANG_FLOAT | -- |             | Measurement values for Phase A to Phase B |   |
| phsBC     | CMV_MAG_ANG_FLOAT | -- |             | Measurement values for Phase B to Phase C |   |
| phsCA     | CMV_MAG_ANG_FLOAT | -- |             | Measurement values for Phase C to Phase A |   |

### 1.5.21 COMMON DATA CLASS: DPC\_CTRL

Description: Controllable Double Point (for CSWI.pos)

CDC Class: DPC

| Attribute   | Type                             | FC | Enumeration | Comment                                                                                                                     | X |
|-------------|----------------------------------|----|-------------|-----------------------------------------------------------------------------------------------------------------------------|---|
| ctlVal      | BOOLEAN                          | CO |             | Control value (Off - FALSE, On - TRUE)                                                                                      |   |
| origin      | Originator                       | ST |             | Originator of the last change of the controllable data                                                                      |   |
| stVal       | CODED_ENUM<br>(MMS Type: _BSTR2) | ST | Dbpos       | Status value of the data (Intermediate state, Off, On or Bad-state)                                                         |   |
| q           | Quality                          | ST |             | Quality of the status value                                                                                                 |   |
| t           | TimeStamp                        | ST |             | Timestamp of the last change in state of status value                                                                       |   |
| stSeld      | BOOLEAN                          | ST |             | The controllable data is in the status "Selected"                                                                           |   |
| subEna      | BOOLEAN                          | SV |             | Enable/disable substitution                                                                                                 |   |
| subVal      | CODED_ENUM<br>(MMS Type: _BSTR2) | SV | Dbpos       | Substitution value (Intermediate state, Off, On or Bad-state)                                                               |   |
| subQ        | Quality                          | SV |             | Value used to substitute the data attribute q                                                                               |   |
| subID       | VISIBLE_STRING64                 | SV |             | Address of the device that made the substitution                                                                            |   |
| blkEna      | BOOLEAN                          | BL |             | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated                                  |   |
| ctlModel    | ENUMERATED8<br>(MMS Type: INT8)  | CF | ctlModel    | Control model (Corresponding to the behaviour of the data)                                                                  |   |
| sboTimeout  | INT32U                           | CF |             | Select Before Operate timeout period (in milliseconds)                                                                      |   |
| operTimeout | INT32U                           | CF |             | This attribute specifies the timeout used to supervise an operation according to the control model defined in IEC 61850-7-2 |   |

### 1.5.22 COMMON DATA CLASS: DPC\_STATUS

Description: Controllable Double Point (w.r.t Status Only)

CDC Class: DPC

| Attribute | Type                             | FC | Enumeration | Comment                                                                                    | X |
|-----------|----------------------------------|----|-------------|--------------------------------------------------------------------------------------------|---|
| stVal     | CODED_ENUM<br>(MMS Type: _BSTR2) | ST | Dbpos       | Status value of the data (Intermediate state, Off, On or Bad-state)                        |   |
| q         | Quality                          | ST |             | Quality of the status value                                                                |   |
| t         | TimeStamp                        | ST |             | Timestamp of the last change in state of status value                                      |   |
| subEna    | BOOLEAN                          | SV |             | Enable/disable substitution                                                                |   |
| subVal    | CODED_ENUM<br>(MMS Type: _BSTR2) | SV | Dbpos       | Substitution value (Intermediate state, Off, On or Bad-state)                              |   |
| subQ      | Quality                          | SV |             | Value used to substitute the data attribute q                                              |   |
| subID     | VISIBLE_STRING64                 | SV |             | Address of the device that made the substitution                                           |   |
| blkEna    | BOOLEAN                          | BL |             | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated |   |
| ctlModel  | ENUMERATED8<br>(MMS Type: INT8)  | CF | ctlModel    | Control model (Corresponding to the behaviour of the data)                                 |   |

### 1.5.23 COMMON DATA CLASS: DPC\_STATUS\_D

Description: Controllable Double Point (with Description)

CDC Class: DPC

| Attribute | Type                             | FC | Enumeration | Comment                                                                                    | X |
|-----------|----------------------------------|----|-------------|--------------------------------------------------------------------------------------------|---|
| stVal     | CODED_ENUM<br>(MMS Type: _BSTR2) | ST | Dbpos       | Status value of the data (Intermediate state, Off, On or Bad-state)                        |   |
| q         | Quality                          | ST |             | Quality of the status value                                                                |   |
| t         | TimeStamp                        | ST |             | Timestamp of the last change in state of status value                                      |   |
| subEna    | BOOLEAN                          | SV |             | Enable/disable substitution                                                                |   |
| subVal    | CODED_ENUM<br>(MMS Type: _BSTR2) | SV | Dbpos       | Substitution value (Intermediate state, Off, On or Bad-state)                              |   |
| subQ      | Quality                          | SV |             | Value used to substitute the data attribute q                                              |   |
| subID     | VISIBLE_STRING64                 | SV |             | Address of the device that made the substitution                                           |   |
| blkEna    | BOOLEAN                          | BL |             | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated |   |
| ctlModel  | ENUMERATED8<br>(MMS Type: INT8)  | CF | ctlModel    | Control model (Corresponding to the behaviour of the data)                                 |   |
| d         | VISIBLE_STRING255                | DC |             | Description of the status element                                                          |   |

### 1.5.24 COMMON DATA CLASS: DPL\_PRIV

Description: Device Name Plate for 'Teleprotection' Communications Channel

CDC Class: DPL

| Attribute | Type              | FC | Enumeration | Comment            | X |
|-----------|-------------------|----|-------------|--------------------|---|
| vendor    | VISIBLE_STRING255 | DC |             | Name of the vendor |   |

### 1.5.25 COMMON DATA CLASS: DPL\_STANDARD

Description: Standard Device Name Plate

CDC Class: DPL

| Attribute | Type              | FC | Enumeration | Comment            | X |
|-----------|-------------------|----|-------------|--------------------|---|
| vendor    | VISIBLE_STRING255 | DC |             | Name of the vendor |   |
| hwRev     | VISIBLE_STRING255 | DC |             | Hardware revision  |   |
| swRev     | VISIBLE_STRING255 | DC |             | Software revision  |   |

| Attribute | Type              | FC | Enumeration | Comment                     | X |
|-----------|-------------------|----|-------------|-----------------------------|---|
| serNum    | VISIBLE_STRING255 | DC |             | Serial Number               |   |
| model     | VISIBLE_STRING255 | DC |             | Model Number                |   |
| location  | VISIBLE_STRING255 | DC |             | Physical location of device |   |

### 1.5.26 COMMON DATA CLASS: ENC\_CTRL\_LD\_MOD

Description: Controllable Enumerated Status

CDC Class: ENC

| Attribute   | Type                             | FC | Enumeration | Comment                                                                                                                     | X |
|-------------|----------------------------------|----|-------------|-----------------------------------------------------------------------------------------------------------------------------|---|
| ctlVal      | ENUMERATED32<br>(MMS Type: INT8) | CO | Mod_3       | Control value                                                                                                               |   |
| origin      | Originator                       | ST |             | Originator of the last change of the controllable data                                                                      |   |
| stVal       | ENUMERATED32<br>(MMS Type: INT8) | ST | Mod_3       | Status value of the data                                                                                                    |   |
| q           | Quality                          | ST |             | Quality of the status value                                                                                                 |   |
| t           | TimeStamp                        | ST |             | Timestamp of the last change in state of status value                                                                       |   |
| stSeld      | BOOLEAN                          | ST |             | The controllable data is in the status "Selected"                                                                           |   |
| subEna      | BOOLEAN                          | SV |             | Enable/disable substitution                                                                                                 |   |
| subVal      | ENUMERATED32<br>(MMS Type: INT8) | SV | Mod_3       | Substitution value                                                                                                          |   |
| subQ        | Quality                          | SV |             | Value used to substitute the data attribute q                                                                               |   |
| subID       | VISIBLE_STRING64                 | SV |             | Address of the device that made the substitution                                                                            |   |
| blkEna      | BOOLEAN                          | BL |             | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated                                  |   |
| ctlModel    | ENUMERATED8<br>(MMS Type: INT8)  | CF | ctlModel    | Control model (Corresponding to the behaviour of the data)                                                                  |   |
| sboTimeout  | INT32U                           | CF |             | Select Before Operate timeout period (in milliseconds)                                                                      |   |
| operTimeout | INT32U                           | CF |             | This attribute specifies the timeout used to supervise an operation according to the control model defined in IEC 61850-7-2 |   |
| d           | VISIBLE_STRING255                | DC |             | Description of the status element                                                                                           |   |

### 1.5.27 COMMON DATA CLASS: ENC\_CTRL\_LD\_MOD\_2

Description: Controllable Enumerated Status (Includes Three Status, Used for Child LD.LLN0)

CDC Class: ENC

| Attribute  | Type                             | FC | Enumeration | Comment                                                                                    | X |
|------------|----------------------------------|----|-------------|--------------------------------------------------------------------------------------------|---|
| ctlVal     | ENUMERATED32<br>(MMS Type: INT8) | CO | Mod_2       | Control value                                                                              |   |
| origin     | Originator                       | ST |             | Originator of the last change of the controllable data                                     |   |
| stVal      | ENUMERATED32<br>(MMS Type: INT8) | ST | Mod_2       | Status value of the data                                                                   |   |
| q          | Quality                          | ST |             | Quality of the status value                                                                |   |
| t          | TimeStamp                        | ST |             | Timestamp of the last change in state of status value                                      |   |
| stSeld     | BOOLEAN                          | ST |             | The controllable data is in the status "Selected"                                          |   |
| subEna     | BOOLEAN                          | SV |             | Enable/disable substitution                                                                |   |
| subVal     | ENUMERATED32<br>(MMS Type: INT8) | SV | Mod_2       | Substitution value                                                                         |   |
| subQ       | Quality                          | SV |             | Value used to substitute the data attribute q                                              |   |
| subID      | VISIBLE_STRING64                 | SV |             | Address of the device that made the substitution                                           |   |
| blkEna     | BOOLEAN                          | BL |             | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated |   |
| ctlModel   | ENUMERATED8<br>(MMS Type: INT8)  | CF | ctlModel    | Control model (Corresponding to the behaviour of the data)                                 |   |
| sboTimeout | INT32U                           | CF |             | Select Before Operate timeout period (in milliseconds)                                     |   |

| Attribute   | Type              | FC | Enumeration | Comment                                                                                                                     | X |
|-------------|-------------------|----|-------------|-----------------------------------------------------------------------------------------------------------------------------|---|
| operTimeout | INT32U            | CF |             | This attribute specifies the timeout used to supervise an operation according to the control model defined in IEC 61850-7-2 |   |
| d           | VISIBLE_STRING255 | DC |             | Description of the status element                                                                                           |   |

### 1.5.28 COMMON DATA CLASS: ENC\_MOD\_TWO\_STATUS

Description: Controllable Enumerated Status

CDC Class: ENC

| Attribute | Type                             | FC | Enumeration | Comment                                                                                    | X |
|-----------|----------------------------------|----|-------------|--------------------------------------------------------------------------------------------|---|
| stVal     | ENUMERATED32<br>(MMS Type: INT8) | ST | Mod_2       | Status value of the mode used for LN which have two status                                 |   |
| q         | Quality                          | ST |             | Quality of the status value                                                                |   |
| t         | TimeStamp                        | ST |             | Timestamp of the last change in state of status value                                      |   |
| subEna    | BOOLEAN                          | SV |             | Enable/disable substitution                                                                |   |
| subVal    | ENUMERATED32<br>(MMS Type: INT8) | SV | Mod_2       | Substitution value                                                                         |   |
| subQ      | Quality                          | SV |             | Value used to substitute the data attribute q                                              |   |
| subID     | VISIBLE_STRING64                 | SV |             | Address of the device that made the substitution                                           |   |
| blkEna    | BOOLEAN                          | BL |             | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated |   |
| ctlModel  | ENUMERATED8<br>(MMS Type: INT8)  | CF | ctlModel    | Control model (Corresponding to the behaviour of the data)                                 |   |

### 1.5.29 COMMON DATA CLASS: ENG\_SET\_WD\_CLCINTVTYP

Description: Enumerated Status Setting (for ClcIntvTyp)

CDC Class: ENG

| Attribute | Type                            | FC | Enumeration | Comment       | X |
|-----------|---------------------------------|----|-------------|---------------|---|
| setVal    | ENUMERATED8<br>(MMS Type: INT8) | SP | ClcIntvTyp  | Setting value |   |

### 1.5.30 COMMON DATA CLASS: ENG\_SET\_WD\_CLCMOD

Description: Enumerated Status Setting (for ClcMod)

CDC Class: ENG

| Attribute | Type                            | FC | Enumeration | Comment       | X |
|-----------|---------------------------------|----|-------------|---------------|---|
| setVal    | ENUMERATED8<br>(MMS Type: INT8) | SP | ClcMod      | Setting value |   |

### 1.5.31 COMMON DATA CLASS: ENG\_SET\_WD\_CLCMTH

Description: Enumerated Status Setting (for ClcMth)

CDC Class: ENG

| Attribute | Type                            | FC | Enumeration | Comment       | X |
|-----------|---------------------------------|----|-------------|---------------|---|
| setVal    | ENUMERATED8<br>(MMS Type: INT8) | SP | ClcMth      | Setting value |   |

### 1.5.32 COMMON DATA CLASS: ENS\_AUTORECST

Description: Enumerated Status

CDC Class: ENS

| Attribute | Type                            | FC | Enumeration | Comment                                                                                    | X |
|-----------|---------------------------------|----|-------------|--------------------------------------------------------------------------------------------|---|
| stVal     | ENUMERATED8<br>(MMS Type: INT8) | ST | AutoRecSt   | The element status                                                                         |   |
| q         | Quality                         | ST |             | The quality of the status value                                                            |   |
| t         | TimeStamp                       | ST |             | Timestamp of the last change in state                                                      |   |
| subEna    | BOOLEAN                         | SV |             | Substitution enabled/disabled                                                              |   |
| subVal    | ENUMERATED8<br>(MMS Type: INT8) | SV | AutoRecSt   | Substitution value                                                                         |   |
| subQ      | Quality                         | SV |             | Value used to substitute the data attribute q                                              |   |
| subID     | VISIBLE_STRING64                | SV |             | Address of the device that made the substitution                                           |   |
| blkEna    | BOOLEAN                         | BL |             | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated |   |

### 1.5.33 COMMON DATA CLASS: ENS\_BEH\_FOUR\_STATUS

Description: Enumerated Behaviour Status (with 4 Status)

CDC Class: ENS

| Attribute | Type                            | FC | Enumeration | Comment                                                                                    | X |
|-----------|---------------------------------|----|-------------|--------------------------------------------------------------------------------------------|---|
| stVal     | ENUMERATED8<br>(MMS Type: INT8) | ST | Beh_4       | The element status                                                                         |   |
| q         | Quality                         | ST |             | The quality of the status value                                                            |   |
| t         | TimeStamp                       | ST |             | Timestamp of the last change in state                                                      |   |
| subEna    | BOOLEAN                         | SV |             | Substitution enabled/disabled                                                              |   |
| subVal    | ENUMERATED8<br>(MMS Type: INT8) | SV | Beh_4       | Substitution value                                                                         |   |
| subQ      | Quality                         | SV |             | Value used to substitute the data attribute q                                              |   |
| subID     | VISIBLE_STRING64                | SV |             | Address of the device that made the substitution                                           |   |
| blkEna    | BOOLEAN                         | BL |             | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated |   |

### 1.5.34 COMMON DATA CLASS: ENS\_BEH\_FOUR\_STATUS\_DN

Description: Enumerated Status

CDC Class: ENS

| Attribute | Type                            | FC | Enumeration | Comment                                                                                    | X |
|-----------|---------------------------------|----|-------------|--------------------------------------------------------------------------------------------|---|
| stVal     | ENUMERATED8<br>(MMS Type: INT8) | ST | Beh_4       | The element status                                                                         |   |
| q         | Quality                         | ST |             | The quality of the status value                                                            |   |
| t         | TimeStamp                       | ST |             | Timestamp of the last change in state                                                      |   |
| subEna    | BOOLEAN                         | SV |             | Substitution enabled/disabled                                                              |   |
| subVal    | ENUMERATED8<br>(MMS Type: INT8) | SV | Beh_4       | Substitution value                                                                         |   |
| subQ      | Quality                         | SV |             | Value used to substitute the data attribute q                                              |   |
| subID     | VISIBLE_STRING64                | SV |             | Address of the device that made the substitution                                           |   |
| blkEna    | BOOLEAN                         | BL |             | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated |   |
| dataNs    | VISIBLE_STRING255               | EX |             | Data name space                                                                            |   |

### 1.5.35 COMMON DATA CLASS: ENS\_BEH\_THREE\_STATUS

Description: Enumerated Behaviour Status (with 3 Status)

CDC Class: ENS

| Attribute | Type                            | FC | Enumeration | Comment                                                                                    | X |
|-----------|---------------------------------|----|-------------|--------------------------------------------------------------------------------------------|---|
| stVal     | ENUMERATED8<br>(MMS Type: INT8) | ST | Beh_3       | The element status                                                                         |   |
| q         | Quality                         | ST |             | The quality of the status value                                                            |   |
| t         | TimeStamp                       | ST |             | Timestamp of the last change in state                                                      |   |
| subEna    | BOOLEAN                         | SV |             | Substitution enabled/disabled                                                              |   |
| subVal    | ENUMERATED8<br>(MMS Type: INT8) | SV | Beh_3       | Substitution value                                                                         |   |
| subQ      | Quality                         | SV |             | Value used to substitute the data attribute q                                              |   |
| subID     | VISIBLE_STRING64                | SV |             | Address of the device that made the substitution                                           |   |
| blkEna    | BOOLEAN                         | BL |             | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated |   |

### 1.5.36 COMMON DATA CLASS: ENS\_BEH\_THREE\_STATUS\_DN

Description: Enumerated Status (with 3 Status and dataNs Used for the Beh in the Extended LN)

CDC Class: ENS

| Attribute | Type                            | FC | Enumeration | Comment                                                                                    | X |
|-----------|---------------------------------|----|-------------|--------------------------------------------------------------------------------------------|---|
| stVal     | ENUMERATED8<br>(MMS Type: INT8) | ST | Beh_3       | The element status                                                                         |   |
| q         | Quality                         | ST |             | The quality of the status value                                                            |   |
| t         | TimeStamp                       | ST |             | Timestamp of the last change in state                                                      |   |
| subEna    | BOOLEAN                         | SV |             | Substitution enabled/disabled                                                              |   |
| subVal    | ENUMERATED8<br>(MMS Type: INT8) | SV | Beh_3       | Substitution value                                                                         |   |
| subQ      | Quality                         | SV |             | Value used to substitute the data attribute q                                              |   |
| subID     | VISIBLE_STRING64                | SV |             | Address of the device that made the substitution                                           |   |
| blkEna    | BOOLEAN                         | BL |             | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated |   |
| dataNs    | VISIBLE_STRING255               | EX |             | Data name space                                                                            |   |

### 1.5.37 COMMON DATA CLASS: ENS\_CBCAP

Description: Enumerated Status (w.r.t CB Operating Capability)

CDC Class: ENS

| Attribute | Type                            | FC | Enumeration             | Comment                                                                                    | X |
|-----------|---------------------------------|----|-------------------------|--------------------------------------------------------------------------------------------|---|
| stVal     | ENUMERATED8<br>(MMS Type: INT8) | ST | BreakerOpCapabilityKind | The element status                                                                         |   |
| q         | Quality                         | ST |                         | The quality of the status value                                                            |   |
| t         | TimeStamp                       | ST |                         | Timestamp of the last change in state                                                      |   |
| subEna    | BOOLEAN                         | SV |                         | Substitution enabled/disabled                                                              |   |
| subVal    | ENUMERATED8<br>(MMS Type: INT8) | SV | BreakerOpCapabilityKind | Substitution value                                                                         |   |
| subQ      | Quality                         | SV |                         | Value used to substitute the data attribute q                                              |   |
| subID     | VISIBLE_STRING64                | SV |                         | Address of the device that made the substitution                                           |   |
| blkEna    | BOOLEAN                         | BL |                         | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated |   |

### 1.5.38 COMMON DATA CLASS: ENS\_CLK\_SRC\_KIND

Description: Enumerated Status for Time Src Type

CDC Class: ENS

| Attribute | Type                            | FC | Enumeration     | Comment                                          | X |
|-----------|---------------------------------|----|-----------------|--------------------------------------------------|---|
| stVal     | ENUMERATED8<br>(MMS Type: INT8) | ST | ClockSourceKind | The element status                               |   |
| q         | Quality                         | ST |                 | The quality of the status value                  |   |
| t         | TimeStamp                       | ST |                 | Timestamp of the last change in state            |   |
| subEna    | BOOLEAN                         | SV |                 | Substitution enabled/disabled                    |   |
| subVal    | ENUMERATED8<br>(MMS Type: INT8) | SV | ClockSourceKind | Substitution value                               |   |
| subQ      | Quality                         | SV |                 | Value used to substitute the data attribute q    |   |
| subID     | VISIBLE_STRING64                | SV |                 | Address of the device that made the substitution |   |
| dataNs    | VISIBLE_STRING255               | EX |                 | Data name space                                  |   |

### 1.5.39 COMMON DATA CLASS: ENS\_CLK\_SYNC\_KIND

Description: Enumerated Status for Clock Sync Type

CDC Class: ENS

| Attribute | Type                            | FC | Enumeration   | Comment                                                                                    | X |
|-----------|---------------------------------|----|---------------|--------------------------------------------------------------------------------------------|---|
| stVal     | ENUMERATED8<br>(MMS Type: INT8) | ST | ClockSyncKind | The element status                                                                         |   |
| q         | Quality                         | ST |               | The quality of the status value                                                            |   |
| t         | TimeStamp                       | ST |               | Timestamp of the last change in state                                                      |   |
| subEna    | BOOLEAN                         | SV |               | Substitution enabled/disabled                                                              |   |
| subVal    | ENUMERATED8<br>(MMS Type: INT8) | SV | ClockSyncKind | Substitution value                                                                         |   |
| subQ      | Quality                         | SV |               | Value used to substitute the data attribute q                                              |   |
| subID     | VISIBLE_STRING64                | SV |               | Address of the device that made the substitution                                           |   |
| blkEna    | BOOLEAN                         | BL |               | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated |   |
| dataNs    | VISIBLE_STRING255               | EX |               | Data name space                                                                            |   |

### 1.5.40 COMMON DATA CLASS: ENS\_CLK\_SYNC\_LK

Description: Enumerated Status for ClockSyncLockingKind

CDC Class: ENS

| Attribute | Type                            | FC | Enumeration       | Comment                                                                                    | X |
|-----------|---------------------------------|----|-------------------|--------------------------------------------------------------------------------------------|---|
| stVal     | ENUMERATED8<br>(MMS Type: INT8) | ST | ClockSyncLockKind | The element status                                                                         |   |
| q         | Quality                         | ST |                   | The quality of the status value                                                            |   |
| t         | TimeStamp                       | ST |                   | Timestamp of the last change in state                                                      |   |
| subEna    | BOOLEAN                         | SV |                   | Substitution enabled/disabled                                                              |   |
| subVal    | ENUMERATED8<br>(MMS Type: INT8) | SV | ClockSyncLockKind | Substitution value                                                                         |   |
| subQ      | Quality                         | SV |                   | Value used to substitute the data attribute q                                              |   |
| subID     | VISIBLE_STRING64                | SV |                   | Address of the device that made the substitution                                           |   |
| blkEna    | BOOLEAN                         | BL |                   | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated |   |

**1.5.41 COMMON DATA CLASS: ENS\_HEALTH**

Description: Enumerated Status

CDC Class: ENS

| Attribute | Type                            | FC | Enumeration | Comment                                                                                    | X |
|-----------|---------------------------------|----|-------------|--------------------------------------------------------------------------------------------|---|
| stVal     | ENUMERATED8<br>(MMS Type: INT8) | ST | HealthKind  | The element status                                                                         |   |
| q         | Quality                         | ST |             | The quality of the status value                                                            |   |
| t         | TimeStamp                       | ST |             | Timestamp of the last change in state                                                      |   |
| subEna    | BOOLEAN                         | SV |             | Substitution enabled/disabled                                                              |   |
| subVal    | ENUMERATED8<br>(MMS Type: INT8) | SV | HealthKind  | Substitution value                                                                         |   |
| subQ      | Quality                         | SV |             | Value used to substitute the data attribute q                                              |   |
| subID     | VISIBLE_STRING64                | SV |             | Address of the device that made the substitution                                           |   |
| blkEna    | BOOLEAN                         | BL |             | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated |   |

**1.5.42 COMMON DATA CLASS: ENS\_HEALTH\_DN**

Description: Enumerated Status (with dataNs Used for the Health in the Extended LN)

CDC Class: ENS

| Attribute | Type                            | FC | Enumeration | Comment                                                                                    | X |
|-----------|---------------------------------|----|-------------|--------------------------------------------------------------------------------------------|---|
| stVal     | ENUMERATED8<br>(MMS Type: INT8) | ST | HealthKind  | The element status                                                                         |   |
| q         | Quality                         | ST |             | The quality of the status value                                                            |   |
| t         | TimeStamp                       | ST |             | Timestamp of the last change in state                                                      |   |
| subEna    | BOOLEAN                         | SV |             | Substitution enabled/disabled                                                              |   |
| subVal    | ENUMERATED8<br>(MMS Type: INT8) | SV | HealthKind  | Substitution value                                                                         |   |
| subQ      | Quality                         | SV |             | Value used to substitute the data attribute q                                              |   |
| subID     | VISIBLE_STRING64                | SV |             | Address of the device that made the substitution                                           |   |
| blkEna    | BOOLEAN                         | BL |             | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated |   |
| dataNs    | VISIBLE_STRING255               | EX |             | Data name space                                                                            |   |

**1.5.43 COMMON DATA CLASS: ENS\_PHASE\_SEL**

Description: Enumerated Status

CDC Class: ENS

| Attribute | Type                            | FC | Enumeration   | Comment                                                                                    | X |
|-----------|---------------------------------|----|---------------|--------------------------------------------------------------------------------------------|---|
| stVal     | ENUMERATED8<br>(MMS Type: INT8) | ST | FaultLoopKind | The element status                                                                         |   |
| q         | Quality                         | ST |               | The quality of the status value                                                            |   |
| t         | TimeStamp                       | ST |               | Timestamp of the last change in state                                                      |   |
| subEna    | BOOLEAN                         | SV |               | Substitution enabled/disabled                                                              |   |
| subVal    | ENUMERATED8<br>(MMS Type: INT8) | SV | FaultLoopKind | Substitution value                                                                         |   |
| subQ      | Quality                         | SV |               | Value used to substitute the data attribute q                                              |   |
| subID     | VISIBLE_STRING64                | SV |               | Address of the device that made the substitution                                           |   |
| blkEna    | BOOLEAN                         | BL |               | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated |   |

#### 1.5.44 COMMON DATA CLASS: ENS\_SWI\_TYPE

Description: Enumerated Status

CDC Class: ENS

| Attribute | Type                            | FC | Enumeration | Comment                                                                                    | X |
|-----------|---------------------------------|----|-------------|--------------------------------------------------------------------------------------------|---|
| stVal     | ENUMERATED8<br>(MMS Type: INT8) | ST | SwType      | The element status                                                                         |   |
| q         | Quality                         | ST |             | The quality of the status value                                                            |   |
| t         | TimeStamp                       | ST |             | Timestamp of the last change in state                                                      |   |
| subEna    | BOOLEAN                         | SV |             | Substitution enabled/disabled                                                              |   |
| subVal    | ENUMERATED8<br>(MMS Type: INT8) | SV | SwType      | Substitution value                                                                         |   |
| subQ      | Quality                         | SV |             | Value used to substitute the data attribute q                                              |   |
| subID     | VISIBLE_STRING64                | SV |             | Address of the device that made the substitution                                           |   |
| blkEna    | BOOLEAN                         | BL |             | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated |   |

#### 1.5.45 COMMON DATA CLASS: ENS\_SWOPCAP

Description: Enumerated Status

CDC Class: ENS

| Attribute | Type                            | FC | Enumeration | Comment                                                                                    | X |
|-----------|---------------------------------|----|-------------|--------------------------------------------------------------------------------------------|---|
| stVal     | ENUMERATED8<br>(MMS Type: INT8) | ST | SwOpCap     | The element status                                                                         |   |
| q         | Quality                         | ST |             | The quality of the status value                                                            |   |
| t         | TimeStamp                       | ST |             | Timestamp of the last change in state                                                      |   |
| subEna    | BOOLEAN                         | SV |             | Substitution enabled/disabled                                                              |   |
| subVal    | INT32<br>(MMS Type: INT8)       | SV | SwOpCap     | Substitution value                                                                         |   |
| subQ      | Quality                         | SV |             | Value used to substitute the data attribute q                                              |   |
| blkEna    | BOOLEAN                         | BL |             | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated |   |
| subID     | VISIBLE_STRING64                | SV |             | Address of the device that made the substitution                                           |   |

#### 1.5.46 COMMON DATA CLASS: INC\_MOD\_STD

Description: Standard Controllable Integer Status (w.r.t Mode)

CDC Class: INC

| Attribute | Type                            | FC | Enumeration | Comment                                                                                    | X |
|-----------|---------------------------------|----|-------------|--------------------------------------------------------------------------------------------|---|
| stVal     | INT32                           | ST |             | Status value of the data                                                                   |   |
| q         | Quality                         | ST |             | Quality of the status value                                                                |   |
| t         | TimeStamp                       | ST |             | Timestamp of the last change in state of status value                                      |   |
| subEna    | BOOLEAN                         | SV |             | Enable/disable substitution                                                                |   |
| subVal    | INT32                           | SV |             | Substitution value                                                                         |   |
| subQ      | Quality                         | SV |             | Value used to substitute the data attribute q                                              |   |
| subID     | VISIBLE_STRING64                | SV |             | Address of the device that made the substitution                                           |   |
| blkEna    | BOOLEAN                         | BL |             | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated |   |
| ctlModel  | ENUMERATED8<br>(MMS Type: INT8) | CF | ctlModel    | Control model (Corresponding to the behaviour of the data)                                 |   |

**1.5.47 COMMON DATA CLASS: ING\_SET\_TM**

Description: Integer Status Setting

CDC Class: ING

| Attribute | Type   | FC | Enumeration | Comment                       | X |
|-----------|--------|----|-------------|-------------------------------|---|
| setVal    | INT32  | SP |             | Setting value                 |   |
| minVal    | INT32  | CF |             | Minimum setting value         |   |
| maxVal    | INT32  | CF |             | Maximum setting value         |   |
| stepSize  | INT32U | CF |             | Setting step size (increment) |   |

**1.5.48 COMMON DATA CLASS: ING\_SET\_WD**

Description: Integer Status Setting

CDC Class: ING

| Attribute | Type  | FC | Enumeration | Comment       | X |
|-----------|-------|----|-------------|---------------|---|
| setVal    | INT32 | SP |             | Setting value |   |

**1.5.49 COMMON DATA CLASS: INS\_BASIC**

Description: Integer Status (w.r.t Mandatory Options Only)

CDC Class: INS

| Attribute | Type             | FC | Enumeration | Comment                                                                                    | X |
|-----------|------------------|----|-------------|--------------------------------------------------------------------------------------------|---|
| stVal     | INT32            | ST |             | The element status                                                                         |   |
| q         | Quality          | ST |             | The quality of the status value                                                            |   |
| t         | TimeStamp        | ST |             | Timestamp of the last change in state                                                      |   |
| subEna    | BOOLEAN          | SV |             | Substitution enabled/disabled                                                              |   |
| subVal    | INT32            | SV |             | Substitution value                                                                         |   |
| subQ      | Quality          | SV |             | Value used to substitute the data attribute q                                              |   |
| subID     | VISIBLE_STRING64 | SV |             | Address of the device that made the substitution                                           |   |
| blkEna    | BOOLEAN          | BL |             | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated |   |

**1.5.50 COMMON DATA CLASS: INS\_BASIC\_PRIV**

Description: Integer Status (Private in IEC61850V2.0)

CDC Class: INS

| Attribute | Type              | FC | Enumeration | Comment                                                                                    | X |
|-----------|-------------------|----|-------------|--------------------------------------------------------------------------------------------|---|
| stVal     | INT32             | ST |             | The element status                                                                         |   |
| q         | Quality           | ST |             | The quality of the status value                                                            |   |
| t         | TimeStamp         | ST |             | Timestamp of the last change in state                                                      |   |
| subEna    | BOOLEAN           | SV |             | Substitution enabled/disabled                                                              |   |
| subVal    | INT32             | SV |             | Substitution value                                                                         |   |
| subQ      | Quality           | SV |             | Value used to substitute the data attribute q                                              |   |
| subID     | VISIBLE_STRING64  | SV |             | Address of the device that made the substitution                                           |   |
| blkEna    | BOOLEAN           | BL |             | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated |   |
| dataNs    | VISIBLE_STRING255 | EX |             | Data name space                                                                            |   |

**1.5.51 COMMON DATA CLASS: LPL\_LLNO**

Description: Logical Node 0 Name Plate

CDC Class: LPL

| Attribute | Type              | FC | Enumeration | Comment                                                          | X |
|-----------|-------------------|----|-------------|------------------------------------------------------------------|---|
| vendor    | VISIBLE_STRING255 | DC |             | Name of the vendor                                               |   |
| swRev     | VISIBLE_STRING255 | DC |             | Software revision                                                |   |
| ldNs      | VISIBLE_STRING255 | EX |             | Logical Device name space                                        |   |
| d         | VISIBLE_STRING255 | DC |             | Description                                                      |   |
| configRev | VISIBLE_STRING255 | DC |             | Uniquely identifies the configuration of a local device instance |   |

**1.5.52 COMMON DATA CLASS: LPL\_LLNO\_MEA**

Description: Measurements Logical Node 0 Name Plate

CDC Class: LPL

| Attribute | Type              | FC | Enumeration | Comment                                                          | X |
|-----------|-------------------|----|-------------|------------------------------------------------------------------|---|
| vendor    | VISIBLE_STRING255 | DC |             | Name of the vendor                                               |   |
| swRev     | VISIBLE_STRING255 | DC |             | Software revision                                                |   |
| ldNs      | VISIBLE_STRING255 | EX |             | Logical Device name space                                        |   |
| configRev | VISIBLE_STRING255 | DC |             | Uniquely identifies the configuration of a local device instance |   |

**1.5.53 COMMON DATA CLASS: LPL\_LN**

Description: Standard Logical Node Name Plate

CDC Class: LPL

| Attribute | Type              | FC | Enumeration | Comment            | X |
|-----------|-------------------|----|-------------|--------------------|---|
| vendor    | VISIBLE_STRING255 | DC |             | Name of the vendor |   |
| swRev     | VISIBLE_STRING255 | DC |             | Software revision  |   |
| d         | VISIBLE_STRING255 | DC |             | Description        |   |

**1.5.54 COMMON DATA CLASS: LPL\_LN\_PRIV**

Description: Logical Node Name Plate (w.r.t GE Grid Solutions Extended)

CDC Class: LPL

| Attribute | Type              | FC | Enumeration | Comment                 | X |
|-----------|-------------------|----|-------------|-------------------------|---|
| vendor    | VISIBLE_STRING255 | DC |             | Name of the vendor      |   |
| swRev     | VISIBLE_STRING255 | DC |             | Software revision       |   |
| lnNs      | VISIBLE_STRING255 | EX |             | Logical Node name space |   |
| d         | VISIBLE_STRING255 | DC |             | Description             |   |
| dataNs    | VISIBLE_STRING255 | EX |             | Data name space         |   |

**1.5.55 COMMON DATA CLASS: MV\_FLOAT**

Description: Measured Value (w.r.t Floating Point Value)

CDC Class: MV

| Attribute | Type                | FC | Enumeration | Comment                                                                                                                                                                                                | X |
|-----------|---------------------|----|-------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---|
| mag       | AnalogueValue_Float | MX |             | Deadbanded magnitude of the instantaneous value of a measured value or harmonic value. Updated to the current value of instMag when the value has changed according to the configuration parameter db. |   |
| q         | Quality             | MX |             | Quality of the measurement value                                                                                                                                                                       |   |
| t         | TimeStamp           | MX |             | Time deadbanded magnitude last exceeded its db configuration parameter                                                                                                                                 |   |

| Attribute | Type                 | FC | Enumeration | Comment                                                                                    | X |
|-----------|----------------------|----|-------------|--------------------------------------------------------------------------------------------|---|
| subEna    | BOOLEAN              | SV |             | Enable/disable substitution                                                                |   |
| subMag    | AnalogueValue_Float  | SV |             | Substituted measurement value for instMag                                                  |   |
| subQ      | Quality              | SV |             | Value used to substitute the data attribute q                                              |   |
| subID     | VISIBLE_STRING64     | SV |             | Address of the device that made the substitution                                           |   |
| blkEna    | BOOLEAN              | BL |             | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated |   |
| units     | Unit_Multiplier      | CF |             | Unit of the attribute representing the data                                                |   |
| db        | INT32U               | CF |             | Measurement deadband                                                                       |   |
| rangeC    | RangeConfig_DeadBand | CF |             | Measurement range configuration attributes                                                 |   |
| dbRef     | FLOAT32              | CF |             | Defines deadband size as an absolute value                                                 |   |

### 1.5.56 COMMON DATA CLASS: MV\_FLOAT\_D

Description: Measured Value (w.r.t Floating Point Value with Description)

CDC Class: MV

| Attribute | Type                 | FC | Enumeration | Comment                                                                                                                                                                                                | X |
|-----------|----------------------|----|-------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---|
| mag       | AnalogueValue_Float  | MX |             | Deadbanded magnitude of the instantaneous value of a measured value or harmonic value. Updated to the current value of instMag when the value has changed according to the configuration parameter db. |   |
| q         | Quality              | MX |             | Quality of the measurement value                                                                                                                                                                       |   |
| t         | TimeStamp            | MX |             | Time deadbanded magnitude last exceeded its db configuration parameter                                                                                                                                 |   |
| subEna    | BOOLEAN              | SV |             | Enable/disable substitution                                                                                                                                                                            |   |
| subMag    | AnalogueValue_Float  | SV |             | Substituted measurement value for instMag                                                                                                                                                              |   |
| subQ      | Quality              | SV |             | Value used to substitute the data attribute q                                                                                                                                                          |   |
| subID     | VISIBLE_STRING64     | SV |             | Address of the device that made the substitution                                                                                                                                                       |   |
| blkEna    | BOOLEAN              | BL |             | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated                                                                                                             |   |
| units     | Unit_Multiplier      | CF |             | Unit of the attribute representing the data                                                                                                                                                            |   |
| db        | INT32U               | CF |             | Measurement deadband                                                                                                                                                                                   |   |
| rangeC    | RangeConfig_DeadBand | CF |             | Measurement range configuration attributes                                                                                                                                                             |   |
| dbRef     | FLOAT32              | CF |             | Defines deadband size as an absolute value                                                                                                                                                             |   |
| d         | VISIBLE_STRING255    | DC |             | Description of the status element                                                                                                                                                                      |   |

### 1.5.57 COMMON DATA CLASS: MV\_FLOAT\_D\_PRIV

Description: Measured Value

CDC Class: MV

| Attribute | Type                | FC | Enumeration | Comment                                                                                                                                                                                                | X |
|-----------|---------------------|----|-------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---|
| mag       | AnalogueValue_Float | MX |             | Deadbanded magnitude of the instantaneous value of a measured value or harmonic value. Updated to the current value of instMag when the value has changed according to the configuration parameter db. |   |
| q         | Quality             | MX |             | Quality of the measurement value                                                                                                                                                                       |   |
| t         | TimeStamp           | MX |             | Time deadbanded magnitude last exceeded its db configuration parameter                                                                                                                                 |   |
| subEna    | BOOLEAN             | SV |             | Enable/disable substitution                                                                                                                                                                            |   |
| subMag    | AnalogueValue_Float | SV |             | Substituted measurement value for instMag                                                                                                                                                              |   |
| subQ      | Quality             | SV |             | Value used to substitute the data attribute q                                                                                                                                                          |   |
| subID     | VISIBLE_STRING64    | SV |             | Address of the device that made the substitution                                                                                                                                                       |   |
| blkEna    | BOOLEAN             | BL |             | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated                                                                                                             |   |
| units     | Unit                | CF |             | Unit of the attribute representing the data                                                                                                                                                            |   |
| db        | INT32U              | CF |             | Measurement deadband                                                                                                                                                                                   |   |

| Attribute | Type                 | FC | Enumeration | Comment                                    | X |
|-----------|----------------------|----|-------------|--------------------------------------------|---|
| rangeC    | RangeConfig_DeadBand | CF |             | Measurement range configuration attributes |   |
| dbRef     | FLOAT32              | CF |             | Defines deadband size as an absolute value |   |
| d         | VISIBLE_STRING255    | DC |             | Description of the status element          |   |
| dataNs    | VISIBLE_STRING255    | EX |             | Data name space                            |   |

### 1.5.58 COMMON DATA CLASS: MV\_FLOAT\_PRIV

Description: Measured Value (Used for Extended DO)

CDC Class: MV

| Attribute | Type                 | FC | Enumeration | Comment                                                                                                                                                                                                | X |
|-----------|----------------------|----|-------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---|
| mag       | AnalogueValue_Float  | MX |             | Deadbanded magnitude of the instantaneous value of a measured value or harmonic value. Updated to the current value of instMag when the value has changed according to the configuration parameter db. |   |
| q         | Quality              | MX |             | Quality of the measurement value                                                                                                                                                                       |   |
| t         | TimeStamp            | MX |             | Time deadbanded magnitude last exceeded its db configuration parameter                                                                                                                                 |   |
| subEna    | BOOLEAN              | SV |             | Enable/disable substitution                                                                                                                                                                            |   |
| subMag    | AnalogueValue_Float  | SV |             | Substituted measurement value for instMag                                                                                                                                                              |   |
| subQ      | Quality              | SV |             | Value used to substitute the data attribute q                                                                                                                                                          |   |
| subID     | VISIBLE_STRING64     | SV |             | Address of the device that made the substitution                                                                                                                                                       |   |
| blkEna    | BOOLEAN              | BL |             | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated                                                                                                             |   |
| units     | Unit                 | CF |             | Unit of the attribute representing the data                                                                                                                                                            |   |
| db        | INT32U               | CF |             | Measurement deadband                                                                                                                                                                                   |   |
| rangeC    | RangeConfig_DeadBand | CF |             | Measurement range configuration attributes                                                                                                                                                             |   |
| dbRef     | FLOAT32              | CF |             | Defines deadband size as an absolute value                                                                                                                                                             |   |
| dataNs    | VISIBLE_STRING255    | EX |             | Data name space                                                                                                                                                                                        |   |

### 1.5.59 COMMON DATA CLASS: ORG\_SRC\_REF

Description: Object Reference Settings

CDC Class: ORG

| Attribute | Type            | FC | Enumeration | Comment                                   | X |
|-----------|-----------------|----|-------------|-------------------------------------------|---|
| setSrcRef | ObjectReference | SP |             | The value of the object reference setting |   |

### 1.5.60 COMMON DATA CLASS: SEQ\_MAG\_ANG

Description: Sequence Components of a Measurement Value (w.r.t Magnitudes + Angles)

CDC Class: SEQ

| Attribute | Type                            | FC | Enumeration | Comment                                                            | X |
|-----------|---------------------------------|----|-------------|--------------------------------------------------------------------|---|
| c1        | CMV_MAG_ANG_FLOAT               | -- |             | Sequence component 1 (For semantic meaning see seqT)               |   |
| c2        | CMV_MAG_ANG_FLOAT               | -- |             | Sequence component 2 (For semantic meaning see seqT)               |   |
| c3        | CMV_MAG_ANG_FLOAT               | -- |             | Sequence component 3 (For semantic meaning see seqT)               |   |
| seqT      | ENUMERATED8<br>(MMS Type: INT8) | MX | seqT        | Sequence quantity measurement type (Pos-Neg-Zero or Dir-Quad-Zero) |   |

### 1.5.61 COMMON DATA CLASS: SPC\_CONTROL

Description: Controllable Single Point

CDC Class: SPC

| Attribute   | Type                            | FC | Enumeration | Comment                                                                                                                     | X |
|-------------|---------------------------------|----|-------------|-----------------------------------------------------------------------------------------------------------------------------|---|
| ctlVal      | BOOLEAN                         | CO |             | Control value (Off - FALSE, On - TRUE)                                                                                      |   |
| origin      | Originator                      | ST |             | Originator of the last change of the controllable data                                                                      |   |
| stVal       | BOOLEAN                         | ST |             | Status value of the data                                                                                                    |   |
| q           | Quality                         | ST |             | Quality of the status value                                                                                                 |   |
| t           | TimeStamp                       | ST |             | Timestamp of the last change in state of status value                                                                       |   |
| stSeld      | BOOLEAN                         | ST |             | The controllable data is in the status "Selected"                                                                           |   |
| subEna      | BOOLEAN                         | SV |             | Enable/disable substitution                                                                                                 |   |
| subVal      | BOOLEAN                         | SV |             | Substitution value (True or False)                                                                                          |   |
| subQ        | Quality                         | SV |             | Value used to substitute the data attribute q                                                                               |   |
| subID       | VISIBLE_STRING64                | SV |             | Address of the device that made the substitution                                                                            |   |
| blkEna      | BOOLEAN                         | BL |             | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated                                  |   |
| ctlModel    | ENUMERATED8<br>(MMS Type: INT8) | CF | ctlModel    | Control model (Corresponding to the behaviour of the data)                                                                  |   |
| sboTimeout  | INT32U                          | CF |             | Select Before Operate timeout period (in milliseconds)                                                                      |   |
| operTimeout | INT32U                          | CF |             | This attribute specifies the timeout used to supervise an operation according to the control model defined in IEC 61850-7-2 |   |

### 1.5.62 COMMON DATA CLASS: SPC\_CTRL\_PRIV

Description: Controllable Single Point (With Namespace)

CDC Class: SPC

| Attribute   | Type                            | FC | Enumeration | Comment                                                                                                                     | X |
|-------------|---------------------------------|----|-------------|-----------------------------------------------------------------------------------------------------------------------------|---|
| ctlVal      | BOOLEAN                         | CO |             | Control value (Off - FALSE, On - TRUE)                                                                                      |   |
| origin      | Originator                      | ST |             | Originator of the last change of the controllable data                                                                      |   |
| stVal       | BOOLEAN                         | ST |             | Status value of the data                                                                                                    |   |
| q           | Quality                         | ST |             | Quality of the status value                                                                                                 |   |
| t           | TimeStamp                       | ST |             | Timestamp of the last change in state of status value                                                                       |   |
| stSeld      | BOOLEAN                         | ST |             | The controllable data is in the status "Selected"                                                                           |   |
| subEna      | BOOLEAN                         | SV |             | Enable/disable substitution                                                                                                 |   |
| subVal      | BOOLEAN                         | SV |             | Substitution value (True or False)                                                                                          |   |
| subQ        | Quality                         | SV |             | Value used to substitute the data attribute q                                                                               |   |
| subID       | VISIBLE_STRING64                | SV |             | Address of the device that made the substitution                                                                            |   |
| blkEna      | BOOLEAN                         | BL |             | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated                                  |   |
| ctlModel    | ENUMERATED8<br>(MMS Type: INT8) | CF | ctlModel    | Control model (Corresponding to the behaviour of the data)                                                                  |   |
| sboTimeout  | INT32U                          | CF |             | Select Before Operate timeout period (in milliseconds)                                                                      |   |
| operTimeout | INT32U                          | CF |             | This attribute specifies the timeout used to supervise an operation according to the control model defined in IEC 61850-7-2 |   |
| dataNs      | VISIBLE_STRING255               | EX |             | Data name space                                                                                                             |   |

**1.5.63 COMMON DATA CLASS: SPC\_STATUS**

Description: Controllable Single Point (w.r.t Status Only)

CDC Class: SPC

| Attribute | Type                            | FC | Enumeration | Comment                                                                                    | X |
|-----------|---------------------------------|----|-------------|--------------------------------------------------------------------------------------------|---|
| stVal     | BOOLEAN                         | ST |             | Status value of the data                                                                   |   |
| q         | Quality                         | ST |             | Quality of the status value                                                                |   |
| t         | TimeStamp                       | ST |             | Timestamp of the last change in state of status value                                      |   |
| subEna    | BOOLEAN                         | SV |             | Enable/disable substitution                                                                |   |
| subVal    | BOOLEAN                         | SV |             | Substitution value (True or False)                                                         |   |
| subQ      | Quality                         | SV |             | Value used to substitute the data attribute q                                              |   |
| subID     | VISIBLE_STRING64                | SV |             | Address of the device that made the substitution                                           |   |
| blkEna    | BOOLEAN                         | BL |             | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated |   |
| ctlModel  | ENUMERATED8<br>(MMS Type: INT8) | CF | ctlModel    | Control model (Corresponding to the behaviour of the data)                                 |   |

**1.5.64 COMMON DATA CLASS: SPG\_SP**

Description: Single Point Setting

CDC Class: SPG

| Attribute | Type    | FC | Enumeration | Comment                                | X |
|-----------|---------|----|-------------|----------------------------------------|---|
| setVal    | BOOLEAN | SP |             | Setting value (Off - FALSE, On - TRUE) |   |

**1.5.65 COMMON DATA CLASS: SPG\_WD**

Description: Single Point Setting

CDC Class: SPG

| Attribute | Type              | FC | Enumeration | Comment                                | X |
|-----------|-------------------|----|-------------|----------------------------------------|---|
| setVal    | BOOLEAN           | SP |             | Setting value (Off - FALSE, On - TRUE) |   |
| d         | VISIBLE_STRING255 | DC |             | Description of the status element      |   |

**1.5.66 COMMON DATA CLASS: SPS\_D**

Description: Standard Single Point Status (with Description)

CDC Class: SPS

| Attribute | Type              | FC | Enumeration | Comment                                                                                    | X |
|-----------|-------------------|----|-------------|--------------------------------------------------------------------------------------------|---|
| stVal     | BOOLEAN           | ST |             | The element status (TRUE or FALSE)                                                         |   |
| q         | Quality           | ST |             | The quality of the status value                                                            |   |
| t         | TimeStamp         | ST |             | Timestamp of the last change in state                                                      |   |
| subEna    | BOOLEAN           | SV |             | Substitution enabled/disabled                                                              |   |
| subVal    | BOOLEAN           | SV |             | Substitution value (TRUE or FALSE)                                                         |   |
| subQ      | Quality           | SV |             | Value used to substitute the data attribute q                                              |   |
| subID     | VISIBLE_STRING64  | SV |             | Address of the device that made the substitution                                           |   |
| blkEna    | BOOLEAN           | BL |             | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated |   |
| d         | VISIBLE_STRING255 | DC |             | Description of the status element                                                          |   |

**1.5.67 COMMON DATA CLASS: SPS\_WD**

Description: Single Point Status (without Description)

CDC Class: SPS

| Attribute | Type             | FC | Enumeration | Comment                                                                                    | X |
|-----------|------------------|----|-------------|--------------------------------------------------------------------------------------------|---|
| stVal     | BOOLEAN          | ST |             | The element status (TRUE or FALSE)                                                         |   |
| q         | Quality          | ST |             | The quality of the status value                                                            |   |
| t         | TimeStamp        | ST |             | Timestamp of the last change in state                                                      |   |
| subEna    | BOOLEAN          | SV |             | Substitution enabled/disabled                                                              |   |
| subVal    | BOOLEAN          | SV |             | Substitution value (TRUE or FALSE)                                                         |   |
| subQ      | Quality          | SV |             | Value used to substitute the data attribute q                                              |   |
| subID     | VISIBLE_STRING64 | SV |             | Address of the device that made the substitution                                           |   |
| blkEna    | BOOLEAN          | BL |             | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated |   |

**1.5.68 COMMON DATA CLASS: SPS\_WD\_PRIV**

Description: Single Point Status (without Description with Name Space)

CDC Class: SPS

| Attribute | Type              | FC | Enumeration | Comment                                                                                    | X |
|-----------|-------------------|----|-------------|--------------------------------------------------------------------------------------------|---|
| stVal     | BOOLEAN           | ST |             | The element status (TRUE or FALSE)                                                         |   |
| q         | Quality           | ST |             | The quality of the status value                                                            |   |
| t         | TimeStamp         | ST |             | Timestamp of the last change in state                                                      |   |
| subEna    | BOOLEAN           | SV |             | Substitution enabled/disabled                                                              |   |
| subVal    | BOOLEAN           | SV |             | Substitution value (TRUE or FALSE)                                                         |   |
| subQ      | Quality           | SV |             | Value used to substitute the data attribute q                                              |   |
| subID     | VISIBLE_STRING64  | SV |             | Address of the device that made the substitution                                           |   |
| blkEna    | BOOLEAN           | BL |             | If TRUE, the operator-blocked quality flag is set, and the process value no longer updated |   |
| dataNs    | VISIBLE_STRING255 | EX |             | Data name space                                                                            |   |

**1.5.69 COMMON DATA CLASS: TSG\_SP**

Description: Time Setting Group

CDC Class: TSG

| Attribute | Type              | FC | Enumeration | Comment                                                              | X |
|-----------|-------------------|----|-------------|----------------------------------------------------------------------|---|
| setCal    | CalendarTime      | SP |             | The value of a time setting, if the time is set with a calendar time |   |
| dataNs    | VISIBLE_STRING255 | EX |             | Data name space                                                      |   |

**1.5.70 COMMON DATA CLASS: VSS\_WD**

Description: Visible String Status (without Description)

CDC Class: VSS

| Attribute | Type              | FC | Enumeration | Comment                               | X |
|-----------|-------------------|----|-------------|---------------------------------------|---|
| stVal     | VISIBLE_STRING255 | ST |             | The element status                    |   |
| q         | Quality           | ST |             | The quality of the status value       |   |
| t         | TimeStamp         | ST |             | Timestamp of the last change in state |   |

**1.5.71 COMMON DATA CLASS: WYE\_NEU\_ANG\_D\_PRIV**

Description: Phase to Ground Measurements for a 3-Phase System

CDC Class: WYE

| Attribute | Type              | FC | Enumeration | Comment                              | X |
|-----------|-------------------|----|-------------|--------------------------------------|---|
| neut      | CMV_MAG_ANG_FLOAT | -- |             | Measurement values for neutral input |   |
| d         | VISIBLE_STRING255 | DC |             | Description of the status element    |   |
| dataNs    | VISIBLE_STRING255 | EX |             | Data name space                      |   |

**1.5.72 COMMON DATA CLASS: WYE\_RES\_ANG\_D\_NS**

Description: Phase to Ground Measurements for a 3-Phase System

CDC Class: WYE

| Attribute | Type              | FC | Enumeration | Comment                              | X |
|-----------|-------------------|----|-------------|--------------------------------------|---|
| neut      | CMV_MAG_ANG_FLOAT | -- |             | Measurement values for neutral input |   |
| d         | VISIBLE_STRING255 | DC |             | Description of the status element    |   |
| dataNs    | VISIBLE_STRING255 | EX |             | Data name space                      |   |

**1.5.73 COMMON DATA CLASS: WYE\_SEG**

Description: Phase to Ground Measurements for a 3-Phase System (w.r.t Phase Segregation)

CDC Class: WYE

| Attribute | Type          | FC | Enumeration | Comment                        | X |
|-----------|---------------|----|-------------|--------------------------------|---|
| phsA      | CMV_MAG_FLOAT | -- |             | Measurement values for Phase A |   |
| phsB      | CMV_MAG_FLOAT | -- |             | Measurement values for Phase B |   |
| phsC      | CMV_MAG_FLOAT | -- |             | Measurement values for Phase C |   |

**1.5.74 COMMON DATA CLASS: WYE\_SEG\_ANG\_D**

Description: Phase to Ground Measurements for a 3-Phase System

CDC Class: WYE

| Attribute | Type              | FC | Enumeration | Comment                           | X |
|-----------|-------------------|----|-------------|-----------------------------------|---|
| phsA      | CMV_MAG_ANG_FLOAT | -- |             | Measurement values for Phase A    |   |
| phsB      | CMV_MAG_ANG_FLOAT | -- |             | Measurement values for Phase B    |   |
| phsC      | CMV_MAG_ANG_FLOAT | -- |             | Measurement values for Phase C    |   |
| d         | VISIBLE_STRING255 | DC |             | Description of the status element |   |

**1.5.75 COMMON DATA CLASS: WYE\_SEG\_ANG\_D\_PRIV**

Description: Phase to Ground Measurements for a 3-Phase System

CDC Class: WYE

| Attribute | Type              | FC | Enumeration | Comment                           | X |
|-----------|-------------------|----|-------------|-----------------------------------|---|
| phsA      | CMV_MAG_ANG_FLOAT | -- |             | Measurement values for Phase A    |   |
| phsB      | CMV_MAG_ANG_FLOAT | -- |             | Measurement values for Phase B    |   |
| phsC      | CMV_MAG_ANG_FLOAT | -- |             | Measurement values for Phase C    |   |
| d         | VISIBLE_STRING255 | DC |             | Description of the status element |   |
| dataNs    | VISIBLE_STRING255 | EX |             | Data name space                   |   |

**1.5.76 COMMON DATA CLASS: WYE\_SEG\_ANG\_NEU\_D\_PRIV**

Description: Phase to Ground Measurements for a 3-Phase System (Used for Extended DO)

CDC Class: WYE

| Attribute | Type              | FC | Enumeration | Comment                              | X |
|-----------|-------------------|----|-------------|--------------------------------------|---|
| phsA      | CMV_MAG_ANG_FLOAT | -- |             | Measurement values for Phase A       |   |
| phsB      | CMV_MAG_ANG_FLOAT | -- |             | Measurement values for Phase B       |   |
| phsC      | CMV_MAG_ANG_FLOAT | -- |             | Measurement values for Phase C       |   |
| neut      | CMV_MAG_FLOAT     | -- |             | Measurement values for neutral input |   |
| d         | VISIBLE_STRING255 | DC |             | Description of the status element    |   |
| dataNs    | VISIBLE_STRING255 | EX |             | Data name space                      |   |

**1.5.77 COMMON DATA CLASS: WYE\_SEG\_ANG\_NEU\_D\_PRIV\_1**

Description: Phase to Ground Measurements for a 3-Phase System (Used for Private Data)

CDC Class: WYE

| Attribute | Type              | FC | Enumeration | Comment                              | X |
|-----------|-------------------|----|-------------|--------------------------------------|---|
| phsA      | CMV_MAG_ANG_FLOAT | -- |             | Measurement values for Phase A       |   |
| phsB      | CMV_MAG_ANG_FLOAT | -- |             | Measurement values for Phase B       |   |
| phsC      | CMV_MAG_ANG_FLOAT | -- |             | Measurement values for Phase C       |   |
| neut      | CMV_MAG_ANG_FLOAT | -- |             | Measurement values for neutral input |   |
| d         | VISIBLE_STRING255 | DC |             | Description of the status element    |   |
| dataNs    | VISIBLE_STRING255 | EX |             | Data name space                      |   |

**1.5.78 COMMON DATA CLASS: WYE\_SEG\_ANG\_NEU\_RES\_D**

Description: Phase to Ground Measurements for a 3-Phase System (w.r.t Phase Segregation + Neutral + Residual + Description)

CDC Class: WYE

| Attribute | Type              | FC | Enumeration | Comment                                            | X |
|-----------|-------------------|----|-------------|----------------------------------------------------|---|
| phsA      | CMV_MAG_ANG_FLOAT | -- |             | Measurement values for Phase A                     |   |
| phsB      | CMV_MAG_ANG_FLOAT | -- |             | Measurement values for Phase B                     |   |
| phsC      | CMV_MAG_ANG_FLOAT | -- |             | Measurement values for Phase C                     |   |
| neut      | CMV_MAG_ANG_FLOAT | -- |             | Measurement values for neutral input               |   |
| res       | CMV_MAG_ANG_FLOAT | -- |             | Measurement values for the residual system current |   |
| d         | VISIBLE_STRING255 | DC |             | Description of the status element                  |   |

**1.5.79 COMMON DATA CLASS: WYE\_SEG\_ANG\_RES\_D\_PRIV**

Description: Phase to Ground Measurements for a 3-Phase system (Used for Extended DO)

CDC Class: WYE

| Attribute | Type              | FC | Enumeration | Comment                                            | X |
|-----------|-------------------|----|-------------|----------------------------------------------------|---|
| phsA      | CMV_MAG_ANG_FLOAT | -- |             | Measurement values for Phase A                     |   |
| phsB      | CMV_MAG_ANG_FLOAT | -- |             | Measurement values for Phase B                     |   |
| phsC      | CMV_MAG_ANG_FLOAT | -- |             | Measurement values for Phase C                     |   |
| res       | CMV_MAG_ANG_FLOAT | -- |             | Measurement values for the residual system current |   |
| d         | VISIBLE_STRING255 | DC |             | Description of the status element                  |   |
| dataNs    | VISIBLE_STRING255 | EX |             | Data name space                                    |   |

### 1.5.80 COMMON DATA CLASS: WYE\_SEG\_ANG\_RES\_D\_PRIV

Description: Phase to Ground Measurements for a 3-Phase System (Used for Extended DO)

CDC Class: WYE

| Attribute | Type              | FC | Enumeration | Comment                                            | X |
|-----------|-------------------|----|-------------|----------------------------------------------------|---|
| phsA      | CMV_MAG_ANG_FLOAT | -- |             | Measurement values for Phase A                     |   |
| phsB      | CMV_MAG_ANG_FLOAT | -- |             | Measurement values for Phase B                     |   |
| phsC      | CMV_MAG_ANG_FLOAT | -- |             | Measurement values for Phase C                     |   |
| res       | CMV_MAG_ANG_FLOAT | -- |             | Measurement values for the residual system current |   |
| d         | VISIBLE_STRING255 | DC |             | Description of the status element                  |   |
| dataNs    | VISIBLE_STRING255 | EX |             | Data name space                                    |   |

### 1.5.81 COMMON DATA CLASS: WYE\_SEG\_D

Description: Phase to Ground Measurements for a 3-Phase System (w.r.t Phase Segregation + Description)

CDC Class: WYE

| Attribute | Type              | FC | Enumeration | Comment                           | X |
|-----------|-------------------|----|-------------|-----------------------------------|---|
| phsA      | CMV_MAG_FLOAT     | -- |             | Measurement values for Phase A    |   |
| phsB      | CMV_MAG_FLOAT     | -- |             | Measurement values for Phase B    |   |
| phsC      | CMV_MAG_FLOAT     | -- |             | Measurement values for Phase C    |   |
| d         | VISIBLE_STRING255 | DC |             | Description of the status element |   |

## 1.6 COMMON DATA ATTRIBUTE TYPE DEFINITIONS

Common data attribute types, known herein as components, are defined for use in the Common Data Classes defined in the sections above.

### 1.6.1 COMPONENT: ANALOGUEVALUE\_FLOAT

Comment: General Analogue Value (w.r.t Floating Point Value)

Parent Type: AnalogueValue

| Attribute | Type    | Enumeration | Comment              | X |
|-----------|---------|-------------|----------------------|---|
| f         | FLOAT32 |             | Floating point value |   |

### 1.6.2 COMPONENT: ANALOGUEVALUE\_INT

Comment: General Analogue Value (w.r.t Integer)

Parent Type: AnalogueValue

| Attribute | Type  | Enumeration | Comment                     | X |
|-----------|-------|-------------|-----------------------------|---|
| i         | INT32 |             | 32 bit signed integer value |   |

### 1.6.3 COMPONENT: CALENDARTIME

Comment: CalendarTime Type is Used to Define a Time Setting in Reference to the Calendar

Parent Type:

| Attribute | Type                            | Enumeration | Comment    | X |
|-----------|---------------------------------|-------------|------------|---|
| day       | INT8U                           |             | The day    |   |
| hr        | INT8U                           |             | The hour   |   |
| mn        | INT8U                           |             | The minute |   |
| month     | ENUMERATED8<br>(MMS Type: INT8) | month       | The month  |   |

| Attribute | Type                            | Enumeration | Comment                                                      | X |
|-----------|---------------------------------|-------------|--------------------------------------------------------------|---|
| occ       | INT16U                          |             | Occurrence of a calendar element                             |   |
| occPer    | ENUMERATED8<br>(MMS Type: INT8) | occPer      | The repetition period of a calendar-based time setting       |   |
| occType   | ENUMERATED8<br>(MMS Type: INT8) | occType     | The kind of calendar element that is used for the occurrence |   |
| weekDay   | ENUMERATED8<br>(MMS Type: INT8) | weekDay     | The weekday                                                  |   |

#### 1.6.4 COMPONENT: ORIGINATOR

Comment: Originator of the Last Change of Data Attribute Representing the Value of a Controllable Data Object

Parent Type:

| Attribute | Type                            | Enumeration | Comment                                                                                                                                                       | X |
|-----------|---------------------------------|-------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------|---|
| orCat     | ENUMERATED8<br>(MMS Type: INT8) | orCategory  | Originator category (Not-supported, bay-control, station-control, remote-control, automatic-bay, automatic-station, automatic-remote, maintenance or process) |   |
| orIdent   | OCTET_STRING64                  |             | Originator identification (Null value indicates unknown or not reported)                                                                                      |   |

#### 1.6.5 COMPONENT: RANGECONFIG\_DEADBAND

Comment: Measurement Range Configuration

Parent Type: RangeConfig

| Attribute | Type                | Enumeration | Comment                                                                              | X |
|-----------|---------------------|-------------|--------------------------------------------------------------------------------------|---|
| lLim      | AnalogueValue_Float |             | Low range limit                                                                      |   |
| hLim      | AnalogueValue_Float |             | High range limit                                                                     |   |
| lLim      | AnalogueValue_Float |             | Low Low range limit                                                                  |   |
| max       | AnalogueValue_Float |             | Maximum process measurement for which values of i and f are considered within limits |   |
| min       | AnalogueValue_Float |             | Minimum process measurement for which values of i and f are considered within limits |   |
| hhLim     | AnalogueValue_Float |             | High High range limit                                                                |   |

#### 1.6.6 COMPONENT: SCALEDVALUECONFIG

Comment: Configuration of Analogue Value

Parent Type:

| Attribute | Type    | Enumeration | Comment                                                                      | X |
|-----------|---------|-------------|------------------------------------------------------------------------------|---|
| offset    | FLOAT32 |             | The offset of to apply to the integer analogue value                         |   |
| scaleFact | FLOAT32 |             | Scaling factor to apply to integer analogue values (i.e. via multiplication) |   |

### 1.6.7 COMPONENT: UNIT

Comment: SI Unit Definitions

Parent Type:

| Attribute  | Type                            | Enumeration | Comment                                                              | X |
|------------|---------------------------------|-------------|----------------------------------------------------------------------|---|
| multiplier | ENUMERATED8<br>(MMS Type: INT8) | multiplier  | Multiplier value, the default of which is 0<br>(i.e. multiplier = 1) |   |
| SIUnit     | ENUMERATED8<br>(MMS Type: INT8) | SIUnit      | SI Unit                                                              |   |

### 1.6.8 COMPONENT: UNIT\_MULTIPLIER

Comment: SI Unit Definitions

Parent Type: Unit

| Attribute  | Type                            | Enumeration | Comment                                                              | X |
|------------|---------------------------------|-------------|----------------------------------------------------------------------|---|
| multiplier | ENUMERATED8<br>(MMS Type: INT8) | multiplier  | Multiplier value, the default of which is 0<br>(i.e. multiplier = 1) |   |
| SIUnit     | ENUMERATED8<br>(MMS Type: INT8) | SIUnit      | SI Unit                                                              |   |

### 1.6.9 COMPONENT: UNIT\_NO\_MULTIPLIER

Comment: SI Unit Definitions

Parent Type: Unit

| Attribute | Type                            | Enumeration | Comment | X |
|-----------|---------------------------------|-------------|---------|---|
| SIUnit    | ENUMERATED8<br>(MMS Type: INT8) | SIUnit      | SI Unit |   |

### 1.6.10 COMPONENT: VECTOR\_MAGNITUDE\_FLOAT

Comment: Complex Vector (w.r.t Floating Point Magnitude Value)

Parent Type: Vector

| Attribute | Type                | Enumeration | Comment                            | X |
|-----------|---------------------|-------------|------------------------------------|---|
| mag       | AnalogueValue_Float |             | The magnitude of the complex value |   |

### 1.6.11 COMPONENT: VECTOR\_MAGNITUDEANGLE\_FLOAT

Comment: Complex Vector (w.r.t Floating Point Magnitude and Angle Values)

Parent Type: Vector

| Attribute | Type                | Enumeration | Comment                                              | X |
|-----------|---------------------|-------------|------------------------------------------------------|---|
| mag       | AnalogueValue_Float |             | The magnitude of the complex value                   |   |
| ang       | AnalogueValue_Float |             | The angle of the complex value (the unit is degrees) |   |

## 1.7 ENUMERATED TYPE DEFINITIONS

The following sub-sections specify the enumerations that are associated to some Common Data Class attributes. The definition of the enumerations are according to IEC 61850-7-3 and IEC 61850-7-4 unless otherwise stated.

### 1.7.1 ENUMERATED TYPE: ADDCAUSE

Description: AddCause

| Ordinal | Semantic                       |
|---------|--------------------------------|
| 0       | Unknown                        |
| 1       | Not-supported                  |
| 2       | Blocked-by-switching-hierarchy |
| 3       | Select-failed                  |
| 4       | Invalid-position               |
| 5       | Position-reached               |
| 6       | Parameter-change-in-execution  |
| 7       | Step-limit                     |
| 8       | Blocked-by-Mode                |
| 9       | Blocked-by-process             |
| 10      | Blocked-by-interlocking        |
| 11      | Blocked-by-synchrocheck        |
| 12      | Command-already-in-execution   |
| 13      | Blocked-by-health              |
| 14      | 1-of-n-control                 |
| 15      | Abortion-by-cancel             |
| 16      | Time-limit-over                |
| 17      | Abortion-by-trip               |
| 18      | Object-not-selected            |
| 19      | Object-already-selected        |
| 20      | No-access-authority            |
| 21      | Ended-with-overshoot           |
| 22      | Abortion-due-to-deviation      |
| 23      | Abortion-by-communication-loss |
| 24      | Blocked-by-command             |
| 25      | None                           |
| 26      | Inconsistent-parameters        |
| 27      | Locked-by-other-client         |
| 20      | No-access-authority            |
| 21      | Ended-with-overshoot           |
| 22      | Abortion-due-to-deviation      |
| 23      | Abortion-by-communication-loss |
| 24      | Blocked-by-command             |
| 25      | None                           |
| 26      | Inconsistent-parameters        |
| 27      | Locked-by-other-client         |

### 1.7.2 ENUMERATED TYPE: AUTORECST

Description: Auto-Reclose Status

| Ordinal | Semantic   |
|---------|------------|
| 1       | Ready      |
| 2       | InProgress |

| Ordinal | Semantic           |
|---------|--------------------|
| 3       | Successful         |
| 4       | WaitingForTrip     |
| 5       | TripFromProtection |
| 6       | FaultDisappeared   |
| 7       | WaitToComplete     |
| 8       | CBclosed           |
| 9       | CycleUnsuccessful  |
| 10      | Unsuccessful       |
| 11      | Aborted            |

### 1.7.3 ENUMERATED TYPE: BEH\_3

Description: Behaviour Including 3 States

| Ordinal | Semantic     |
|---------|--------------|
| 1       | on           |
| 3       | test         |
| 4       | test/blocked |

### 1.7.4 ENUMERATED TYPE: BEH\_4

Description: Behaviour Including 4 States

| Ordinal | Semantic     |
|---------|--------------|
| 1       | on           |
| 3       | test         |
| 4       | test/blocked |
| 5       | off          |

### 1.7.5 ENUMERATED TYPE: BREAKEROPCAPABILITYKIND

Description: CB Operating Capability

| Ordinal | Semantic                   |
|---------|----------------------------|
| 1       | None                       |
| 2       | Open                       |
| 3       | Close-Open                 |
| 4       | Open-Close-Open            |
| 5       | Close-Open-Close-Open      |
| 6       | Open-Close-Open-Close-Open |
| 7       | more                       |

### 1.7.6 ENUMERATED TYPE: CLCINTVTYP

Description: Calculation Interval Type

| Ordinal | Semantic  |
|---------|-----------|
| 1       | MS        |
| 2       | PER_CYCLE |
| 3       | CYCLE     |
| 4       | DAY       |
| 5       | WEEK      |
| 6       | MONTH     |
| 7       | YEAR      |
| 8       | EXTERNAL  |

### 1.7.7 ENUMERATED TYPE: CLCMOD

Description: Calculation Mode

| Ordinal | Semantic |
|---------|----------|
| 1       | TOTAL    |
| 2       | PERIOD   |
| 3       | SLIDING  |

### 1.7.8 ENUMERATED TYPE: CLCMTH

Description: Calculation Method of Statistical Data Objects

| Ordinal | Semantic         |
|---------|------------------|
| 1       | UNSPECIFIED      |
| 2       | TRUE_RMS         |
| 3       | PEAK_FUNDAMENTAL |
| 4       | RMS_FUNDAMENTAL  |
| 5       | MIN              |
| 6       | MAX              |
| 7       | AVG              |
| 8       | SDV              |
| 9       | PREDICTION       |
| 10      | RATE             |

### 1.7.9 ENUMERATED TYPE: CLOCKSOURCEKIND

Description: Literals of ClockSourceKind

| Ordinal | Semantic            |
|---------|---------------------|
| 1       | Unknown             |
| 2       | SNTP                |
| 3       | PTP                 |
| 4       | IRIG-B              |
| 5       | Substation internal |

### 1.7.10 ENUMERATED TYPE: CLOCKSYNCKIND

Description: Literals of ClockSyncKind

| Ordinal | Semantic        |
|---------|-----------------|
| 0       | InternalClock   |
| 1       | LocalAreaClock  |
| 2       | GlobalAreaClock |

### 1.7.11 ENUMERATED TYPE: CLOCKSYNCKLOCKKIND

Description: Literals of ClockSyncLockingKind

| Ordinal | Semantic              |
|---------|-----------------------|
| 1       | Locked                |
| 2       | Unlocked10s           |
| 3       | Unlocked100s          |
| 4       | Unlocked1000s         |
| 5       | UnlockedMoreThan1000s |

### 1.7.12 ENUMERATED TYPE: CTLMODEL

Description: Control Model

| Ordinal | Semantic                      |
|---------|-------------------------------|
| 0       | status-only                   |
| 1       | direct-with-normal-security   |
| 2       | sbo-with-normal-security      |
| 3       | direct-with-enhanced-security |
| 4       | sbo-with-enhanced-security    |

### 1.7.13 ENUMERATED TYPE: DBPOS

Description: Switch Positions

| Ordinal | Semantic     |
|---------|--------------|
| 0       | intermediate |
| 1       | off          |
| 2       | on           |
| 3       | bad          |

### 1.7.14 ENUMERATED TYPE: FAULTDIRECTIONKIND

Description: Direction

| Ordinal | Semantic |
|---------|----------|
| 0       | unknown  |
| 1       | forward  |
| 2       | backward |
| 3       | both     |

### 1.7.15 ENUMERATED TYPE: FAULTLOOPKIND

Description: (RFLO) Designates the Kind of Fault Loop

| Ordinal | Semantic       |
|---------|----------------|
| 1       | PhaseAtoGround |
| 2       | PhaseBtoGround |
| 3       | PhaseCtoGround |
| 4       | PhaseAtoB      |
| 5       | PhaseBtoC      |
| 6       | PhaseCtoA      |
| 7       | Others         |

### 1.7.16 ENUMERATED TYPE: HEALTHKIND

Description: Literals of HealthKind

| Ordinal | Semantic |
|---------|----------|
| 1       | Ok       |
| 2       | Warning  |
| 3       | Alarm    |

**1.7.17 ENUMERATED TYPE: MOD\_2**

Description: Mode Including 2 States

| Ordinal | Semantic |
|---------|----------|
| 1       | on       |
| 5       | off      |

**1.7.18 ENUMERATED TYPE: MOD\_3**

Description: Mode Including 3 States

| Ordinal | Semantic     |
|---------|--------------|
| 1       | on           |
| 3       | test         |
| 4       | test/blocked |

**1.7.19 ENUMERATED TYPE: MONTH**

Description: The Month

| Ordinal | Semantic  |
|---------|-----------|
| 0       | reserved  |
| 1       | January   |
| 2       | February  |
| 3       | March     |
| 4       | April     |
| 5       | May       |
| 6       | June      |
| 7       | July      |
| 8       | August    |
| 9       | September |
| 10      | October   |
| 11      | November  |
| 12      | December  |

**1.7.20 ENUMERATED TYPE: MULTIPLIER**

Description: Exponents of the Multiplier Value in Base 10

| Ordinal | Semantic |
|---------|----------|
| -24     | y        |
| -21     | z        |
| -18     | a        |
| -15     | f        |
| -12     | p        |
| -9      | n        |
| -6      | μ        |
| -3      | m        |
| -2      | c        |
| -1      | d        |
| 0       |          |
| 1       | da       |
| 2       | h        |
| 3       | k        |
| 6       | M        |

| Ordinal | Semantic |
|---------|----------|
| 9       | G        |
| 12      | T        |
| 15      | P        |
| 18      | E        |
| 21      | Z        |
| 24      | Y        |

#### 1.7.21 ENUMERATED TYPE: OCCPER

Description: The Repetition Period of a Calendar-Based Time Setting

| Ordinal | Semantic |
|---------|----------|
| 0       | Hour     |
| 1       | Day      |
| 2       | Week     |
| 3       | Month    |
| 4       | Year     |

#### 1.7.22 ENUMERATED TYPE: OCCTYPE

Description: The Kind of Calendar Element that is Used for the Occurrence

| Ordinal | Semantic   |
|---------|------------|
| 0       | Time       |
| 1       | WeekDay    |
| 2       | WeekOfYear |
| 3       | DayOfMonth |
| 4       | DayOfYear  |

#### 1.7.23 ENUMERATED TYPE: ORCATEGORY

Description: orCategory

| Ordinal | Semantic          |
|---------|-------------------|
| 0       | not-supported     |
| 1       | bay-control       |
| 2       | station-control   |
| 3       | remote-control    |
| 4       | automatic-bay     |
| 5       | automatic-station |
| 6       | automatic-remote  |
| 7       | maintenance       |
| 8       | process           |

#### 1.7.24 ENUMERATED TYPE: PHASEFAULTDIRECTIONKIND

Description: Direction for Phase/Neutral

| Ordinal | Semantic |
|---------|----------|
| 0       | unknown  |
| 1       | forward  |
| 2       | backward |

**1.7.25 ENUMERATED TYPE: SEQT**

Description: Sequence Measurement Type

| Ordinal | Semantic      |
|---------|---------------|
| 0       | pos-neg-zero  |
| 1       | dir-quad-zero |

**1.7.26 ENUMERATED TYPE: SIUNIT**

Description: SI Units Derived from ISO/IEC 1000

| Ordinal | Semantic |
|---------|----------|
| -16     | years    |
| -15     | months   |
| -14     | weeks    |
| -13     | V/s      |
| -12     | mins     |
| -11     | hours    |
| -10     | days     |
| -9      | °F       |
| -8      | ratio    |
| -7      | miles    |
| -6      | inches   |
| -5      | feet     |
| -4      | df/dt    |
| -3      | hz/s     |
| -2      | %        |
| -1      | pu       |
| 1       |          |
| -16     | years    |
| -15     | months   |
| -14     | weeks    |
| -13     | V/s      |
| -12     | mins     |
| -11     | hours    |
| -10     | days     |
| -9      | °F       |
| -8      | ratio    |
| -7      | miles    |
| -6      | inches   |
| -5      | feet     |
| -4      | df/dt    |
| -3      | hz/s     |
| -2      | %        |
| -1      | pu       |
| 1       |          |
| 2       | m        |
| 3       | kg       |
| 4       | s        |
| 5       | A        |
| 6       | K        |
| 7       | mol      |
| 8       | cd       |

| Ordinal | Semantic          |
|---------|-------------------|
| 9       | deg               |
| 10      | rad               |
| 11      | sr                |
| 21      | Gy                |
| 22      | Bq                |
| 23      | °C                |
| 24      | Sv                |
| 25      | F                 |
| 26      | C                 |
| 27      | S                 |
| 28      | H                 |
| 29      | V                 |
| 30      | ohm               |
| 31      | J                 |
| 32      | N                 |
| 33      | Hz                |
| 34      | lx                |
| 35      | Lm                |
| 36      | Wb                |
| 37      | T                 |
| 38      | W                 |
| 39      | Pa                |
| 41      | m <sup>2</sup>    |
| 42      | m <sup>3</sup>    |
| 43      | m/s               |
| 44      | m/s <sup>2</sup>  |
| 45      | m <sup>3</sup> /s |
| 46      | m/m <sup>3</sup>  |
| 47      | M                 |
| 48      | kg/m <sup>3</sup> |
| 49      | m <sup>2</sup> /s |
| 50      | W/m K             |
| 51      | J/K               |
| 52      | ppm               |
| 53      | 1/s               |
| 54      | rad/s             |
| 55      | W/m <sup>2</sup>  |
| 56      | J/m <sup>2</sup>  |
| 57      | S/m               |
| 58      | K/s               |
| 59      | Pa/s              |
| 60      | J/kg K            |
| 61      | VA                |
| 62      | Watts             |
| 63      | VAr               |
| 64      | phi               |
| 65      | cos(phi)          |
| 66      | Vs                |
| 67      | V <sup>2</sup>    |
| 68      | As                |
| 69      | A <sup>2</sup>    |

| Ordinal | Semantic         |
|---------|------------------|
| 70      | A <sup>2</sup> t |
| 71      | VAh              |
| 72      | Wh               |
| 73      | VArh             |
| 74      | V/Hz             |
| 75      | Hz/s             |
| 76      | char             |
| 77      | char/s           |
| 78      | kgm <sup>2</sup> |
| 79      | dB               |
| 80      | J/Wh             |
| 81      | W/s              |
| 82      | l/s              |
| 83      | dBm              |
| 84      | h                |
| 85      | min              |

### 1.7.27 ENUMERATED TYPE: SWOPCAP

Description: Switch Operating Capability

| Ordinal | Semantic       |
|---------|----------------|
| 1       | None           |
| 2       | Open           |
| 3       | Close          |
| 4       | Open and Close |

### 1.7.28 ENUMERATED TYPE: SWTYPE

Description: Switch Type

| Ordinal | Semantic                   |
|---------|----------------------------|
| 1       | Load Break                 |
| 2       | Disconnecter               |
| 3       | Earthing Switch            |
| 4       | High Speed Earthing Switch |

### 1.7.29 ENUMERATED TYPE: WEEKDAY

Description: The Weekday

| Ordinal | Semantic  |
|---------|-----------|
| 0       | reserved  |
| 1       | Monday    |
| 2       | Tuesday   |
| 3       | Wednesday |
| 4       | Thursday  |
| 5       | Friday    |
| 6       | Saturday  |
| 7       | Sunday    |

## 1.8 MMS DATA-TYPE CONVERSIONS

The following table shows the relationships between the Part 7 and Part 8-1 data types. The definitions presented above use Part 7 data types, however these are subject to 'translation' when exposed over an MMS (Part 8-1) interface:

| Part 7 Type       | MMS Type       | Part 7 Description                                   |
|-------------------|----------------|------------------------------------------------------|
| BOOLEAN           | Bool           | Logical TRUE/FALSE value                             |
| BSTR16            | Bstring16      | Bit-string -16 bits                                  |
| BVstring13        | BVstring13     | Variable bit string (up to 13 bits)                  |
| Check             | BVstring2      | Control Object check flags                           |
| CODED_ENUM        | Byte           | Coded enumeration                                    |
| CODED_ENUM2       | Byte           | Coded enumeration (2)                                |
| EntryTime         | Btime6         | 8.1 Section 8.1.3.7                                  |
| ENUMERATED16      | Short          | 16 bit enumerated value                              |
| ENUMERATED32      | Long           | 32 bit enumerated value                              |
| ENUMERATED8       | Byte           | 8 bit enumerated value                               |
| FLOAT32           | Float          | 32 bit floating point value                          |
| FLOAT64           | Double         | 64 bit floating point value                          |
| INT128            | Int64          | 128 bit signed integer value                         |
| INT16             | Short          | 16 bit signed integer value                          |
| INT16U            | Ushort         | 16 bit unsigned integer value                        |
| INT24U            | Ulong          | 24 bit unsigned integer value                        |
| INT32             | Long           | 32 bit signed integer value                          |
| INT32U            | Ulong          | 32 bit unsigned integer value                        |
| INT64             | Int64          | 64 bit signed integer value                          |
| INT8              | Byte           | 8 bit signed integer value                           |
| INT8U             | Ubyte          | 8 bit unsigned integer value                         |
| ObjectReference   | Vstring129     | Object Reference (129 character string)              |
| OCTET_STRING6     | Ostring6       | 6 character string (8 bits per character)            |
| OCTET_STRING64    | OVstring64     | 64 character string (8 bits per character)           |
| OCTET_STRING8     | OVstring8      | 8 character string (8 bits per character)            |
| Quality           | BVstring13     | IEC61850 Quality                                     |
| TimeStamp         | Utctime        | IEC61850 Time stamp                                  |
| UNICODE_STRING255 | UTF8Vstring255 | 255 character string (16 bits per unicode character) |
| UTC_TM            | Utctime        | UTC Timestamp                                        |
| VISIBLE_STRING129 | Vstring129     | 129 character string                                 |
| VISIBLE_STRING255 | Vstring255     | 255 character string                                 |
| VISIBLE_STRING64  | Vstring64      | 64 character string                                  |
| VISIBLE_STRING65  | Vstring65      | 65 character string                                  |
| VISIBLE_STRING97  | Vstring97      | 97 character string                                  |



GE VERNOVA