

TRANSFIX DGA 500

Transformer Health Monitoring & Diagnostics

The TRANSFIX™ DGA 500 is an on-line monitoring unit that measures individual dissolved gas and moisture and provides both on-line monitoring and key exploratory diagnostics. It uses the now well known PAS technology (Photo Acoustic Spectroscopy) made popular due to its accuracy, repeatability and lack of consumable through its bigger brother the Kelman™ DGA 900.

When a transformer's insulation system is overstressed, gases are produced that dissolve in the transformer's insulating oil. Dissolved Gas-in-oil Analysis (DGA) and moisture measurements are recognized as the most important tests for condition assessment of transformers and the best early indicators of developing faults.

All types of incipient faults are covered by the monitoring of hydrogen gas levels. Slowly eroding paper faults can be exposed through the monitoring of carbon monoxide. Various degrees of thermal faults, including arcing, can be detected and identified, often leading to a transformer repair rather than a much more costly transformer rebuild.

In particular, the TRANSFIX DGA 500 enables the well known Duval's triangle DGA diagnostic described in Appendix B of IEC Standard 60599. It uses the value of 3 gases (Acetylene, Ethylene and Methane) and is suitable for identifying various degrees/temperature of thermal faults as well as the presence of high-energy electrical discharge faults.

Key Benefits

- Ability to perform Duval's triangle DGA diagnostic
- Easily replaceable with a full nine gas unit
- Communicates data to allow remote diagnostic
- No carrier or calibration consumable gases required
- Available with AC or AC/DC power supply

Applications



Power Utilities

- Middle of the road solution for medium-criticality transformers
- Monitoring together with remote exploratory diagnostic



Industrial Plants

- Reduces the risk of process interruption due to power failure
- Minimizes costly production downtime



GE VERNOVA



Cutting Edge Technology

- Five gases plus moisture in a single monitor
- Automated headspace gas extraction and state of the art photo-acoustic spectroscopy (PAS) measurement technology
- No carrier or consumable calibration gases required
- Capable of sampling frequency up to once per hour or user defined sample rates

Ease Of Use

- Easy installation: no outages required, reducing expense and inconvenience for user
- Easily swappable for a high end Kelman DGA 900 nine gas monitor, once serious issues are detected
- Over two year's worth of data stored internally at six-hourly sampling rate

Configurable Alerts

- Six user configurable alarm relay contacts
- Alarms can be set on gas or moisture ppm levels or on rate of change (ROC)
- Alarms can be set or changed locally or remotely using Perception™ software
- Caution and alarm modes can be used to automatically increase sampling frequency

Integrated Solution


- Integrated load CT allows DGA results to be analysed against the loading of the transformer
- Extensive remote communications options
- Integrates into GE Vernova's Perception software

Duval's Triangle & Perception Software

The Duval Triangle diagnostic method for transformer DGA results was developed by Michel Duval, and is described in IEC standard 60599.

Concentrations (ppm) of methane (CH₄), ethylene (C₂H₄), and acetylene (C₂H₂) are expressed as percentages of the total (CH₄ + C₂H₄ + C₂H₂) and plotted as a point (% CH₄, % C₂H₄, % C₂H₂) in a triangular coordinate system on a triangular chart which has been subdivided into fault zones. The fault zone in which the point is located designates the most likely fault type which produced that combination of gas concentrations.

The Duval Triangle method, like any other DGA diagnostic method, should be applied only when there is some suspicion of a fault, based on an abnormal increase in dissolved gases and H₂ in particular. It is part of the list of diagnostic methods available in GE Vernova's Perception software, depending on the various gas concentration data that are available.



Technical Specifications

MEASUREMENTS
Sensor
Automated headspace gas extraction
Photo-acoustic spectroscopy (PAS) gas measurement
Thin film capacitive moisture sensor
Measurements
Hydrogen (H ₂): 5-5,000 ppm
Carbon Monoxide (CO): 2-50,000 ppm
Acetylene (C ₂ H ₂): 0.5-50,000 ppm
Ethylene (C ₂ H ₄): 2-50,000 ppm
Methane (CH ₄): 2-50,000 ppm
Moisture (H ₂ O): 0-100% RS (given in ppm)
Accuracy
Gases*: ±5 % or ±LDL (Lower Detection Limit), whichever is greater
Moisture: ±3 % RH
Frequency
Configurable from once per hour to once every 4 weeks
Faster sampling automatically triggered upon alert level reached
FEATURES
Display
3 x sunlight visible LED arrays
Internal backlit LCD, 4 lines x 20 characters

Digital Output
USB port (type B connector) for local connection to laptop computer for configuring the system
Ethernet (RJ45) is standard
Serial output (RS-485) and fibre-optic LAN options
GSM/GPRS or CDMA/LTE modem options
Digital Protocols
Modbus® is standard
DNP3 or IEC 61850 options
Analogue Outputs
8 channel configurable analogue output, 4-20mA, available as an option
Alarms
6 alarm setting screens/scenarios available which can set alarms based on gas level, gas rate of change and moisture level
6 dry contact relays (type C, SPDT), NO/NC, 3A @250Vac, 3A @ 30Vdc, 200mA @ 125Vdc, 150mA@ 300Vdc
Separate Service Alarm
OPTIONS
Mounting stand and Sun canopy
Optional external sampling port for glass syringe with Luer stop cock
ENVIRONMENT
Conditions
Operating Ambient Temperature** -40 °C to +55 °C (-40 °F to +131 °F): AC version
-25 °C to +55 °C (-13 °F to +131 °F): AC/DC version

Operating Ambient Humidity 0-95 % RH, non-condensing
Oil Temperature at Valve*** -20 °C to +120 °C (-4 °F to +248 °F)
Enclosure
IP55 certified
304 Stainless Steel, Powder Coated (RAL9002)
Power Requirements AC Version
Nom: 115-230 Vac Range: 103-126/207-253 Vac, 47-63 Hz, 8A max
Power Requirements AC/DC Version**
Nom: 100-230 Vac, Range: 90-253 Vac, 45-65Hz, 5A max
Nom: 100-220 Vdc, Range: 90-242 Vdc, 45-65Hz, 5A max
Mechanical
760 mm (30") x 560 mm (22") x 352 mm (14")
Shipping weight 78 Kg (172 lb)
* Gas accuracy quoted is accuracy of the sensor during calibration
** Operating temperature range reduced at -25 °C to +55 °C when using AC/DC version - PSU is type tested to -40 for startup
*** Based on testing carried out using VOLTESSO™ 35 mineral oil, over a ¼" pipe run of 10 metres or less from oil supply or return valve to monitor connection point and on transformer oil supply valve volumes of 200 ml or less. For oil temperatures colder than -20 °C GE Vernova recommend the use of heat trace cabling on piping

Grid Solutions
Lissie Industrial Estate East
Unit 1, 7 Lissie Walk
Lisburn BT28 2LU
United Kingdom
Tel: +44 (0) 2892 622915

For more information visit
governova.com/grid-solutions



GE, the GE monogram, Kelman, TRANSFIX and Perception are trademarks of the General Electric Company used under trademark license.

IEEE is a registered trademark of the Institute of Electrical and Electronics Engineers Inc.

Modbus is a registered trademark of Schneider Automation, Inc. VOLTESSO is a registered trademark of Exxon Mobil Corporation.

GE Vernova reserves the right to make changes to specifications of products described at any time without notice and without obligation to notify any person of such changes.

©2025 GE Vernova and/or its affiliates. All rights reserved.

